

prosense® SCU Series Universal Signal Conditioner

SCU-7900 Signal Conditioner



Part No. SCU-7900



The SCU-7900 Universal Signal Conditioner from AutomationDirect provides the flexibility to accurately measure AC RMS current or AC RMS voltage. The selectable input can measure AC supply voltage up to 300 VAC RMS or AC current transformers up to 5A RMS. The measured AC voltage or current input can be converted to numerous selectable unipolar or bipolar DC current or voltage output ranges or custom configured with two-point field scalability. The isolated universal supply voltage input eliminates the need for separate transformers or power supplies. Isolation is also provided between input and output.

The SCU-7900 is easily configured with the SCU-PDM2 menu-structured LCD programming/display module (a computer running special calibration software is not required, and there are no confusing DIP switches or jumpers to set). Automatic scrolling Help text identifies each menu item. The detachable programming/display

module can store and transfer configuration parameters from one signal conditioner to another, minimizing set-up time in multiple unit applications. Programming is available in seven different languages, and the programming/display module can be password protected to prevent unauthorized changes to the configuration. When not used for configuration, the programming/display module can remain on the signal conditioner to display the input signal value, engineering units, and output signal. A process simulation function allows manual manipulation of the input signal to control the output signal for trouble-shooting and checkout.

Features

- Accurate measurement of AC RMS voltage up to 300 VAC RMS or AC RMS current to 5 A RMS (Not suitable for VFD or non-sine wave sources.)
- Selectable input and output ranges and two-point field scalability
- Universal supply voltage, 21.6 to 253 VAC or 19.2 to 300 VDC, polarity insensitive
- 3-way isolation between input, output, and power
- Easy-to-use detachable LCD programming/display module SCU-PDM2 (Sold separately and required for programming)
- Transfer configuration settings from one signal conditioner to another with SCU-PDM2
- Integral 35mm DIN rail mounting adapter
- Removable screw terminal blocks are keyed to ensure correct installation
- cULus and CE marked
- 5 year warranty



| SCU-7900 Universal Signal Conditioner | | | | |
|---------------------------------------|--|----------|--------------|----------|
| Part No. | Description | Quantity | Weight (lbs) | Price |
| SCU-7900 | ProSense AC signal conditioner, isolated, AC current, AC voltage input, current or voltage output, 21.6-253 VAC/19.2-300 VDC operating voltage, 35mm DIN rail mount, removable screw terminal plugs. | 1 | 0.34 | \$241.00 |

SCU-7900 Signal Conditioner

| SCU-7900 Universal Signal Conditioner Technical Specifications | | |
|--|--|--|
| General Specifications | | |
| Power | AC Power | 21.6 to 253 VAC, 50/60 Hz |
| | DC Power | 19.2 to 300 VDC |
| Consumption | $\leq 2.5\text{W}$ | |
| Fuse | 400 mA slow blow / 250 VAC (Not user replaceable) | |
| Isolation Voltage, Test/Working | 2.3 kVAC / 250 VAC (reinforced) / 500 VAC (basic) | |
| Configuration Interface | Programming/display module, SCU-PDM2 (sold separately) or SCU-PDM1 (discontinued and replaced by SCU-PDM2) | |
| Signal Dynamics, Input/Output | 20bit / 18bit | |
| Signal/noise Ratio | Min. 60 dB | |
| Output Referred Common Mode Rejection Ratio | 0.02 ppm/VHz | |
| Response Time (0 to 90%, 100 to 10%) | < 0.75 sec | |
| Calibration Temperature | 20 to 28°C [68 to 82.4°F] | |
| Accuracy | The greater of the general and basic values (See Accuracy Table 1) | |
| EMC Immunity | $\leq \pm 0.5\%$ of span | |
| Extended EMC Immunity: NAMUR NE 21, A criterion, burst | $\leq \pm 1\%$ of span | |
| Environmental Conditions | Operating Temperature | -20 to +60°C [-4 to 140°F] |
| | Storage Temperature | -20 to +85°C [-4 to 185°F] |
| | Operating and Storage Humidity | 95% relative humidity (non-condensing) |
| Approvals | UL: E197592, UL 508/C22.2 No. 14 CE: EMC 2014/30/EU LVD 2014/35/EU RoHS2 2011/65/EU amended by 2015/863 | |
| Construction | IP 20, case body is black high impact plastic. Pollution degree 2. | |
| Connections | Wire strip length | 7.5 mm [0.3 in] |
| | Wire gauge | 26 - 14 AWG standard wire |
| | Torque | 0.5 N-m [4.5 inch-lbs] |
| Weight | 250g [8.8 oz], 285 g [10.1 oz] with programming module | |
| Dimensions (HxWxD) | 109 x 23.5 x 104mm [4.3 x 0.93 x 4.1 in], 109 x 23.5 x 116mm [4.3 x 0.93 x 4.6 in] with programming module | |

Accuracy Table 1

| General Values | | |
|-----------------------|--------------------------|-----------------------------------|
| Input Type | Absolute Accuracy | Temperature Coefficient |
| All | $\leq \pm 0.3\%$ of span | $\leq \pm 0.01\%$ of span/°C |
| Basic Values | | |
| Input Type | Basic Accuracy | Temperature Coefficient |
| Current | 1.5 mA | 50 $\mu\text{A}/^\circ\text{C}$ |
| Voltage | 1.5 mVAC | 50 $\mu\text{VAC}/^\circ\text{C}$ |

SCU-7900 Signal Conditioner


Input/Output Specifications

| Model | SCU-7900 |
|--|--|
| Input | |
| Current input ranges | 0...0.5; 0...1; 0...2.5 & 0...5 Arms / 40...400 Hz |
| Maximum input limit | 6A @ 40°C [104°F] |
| Current input resistance | Nom. < 0.07 Ω |
| Input voltage drop, nom. | Nom. < 0.35 V |
| Voltage input ranges | 0...0.5, 0...1, 0...2.83, 0...5, 0...120, 0...230 & 0...300 Vrms / 40...400 Hz |
| Voltage input resistance | Nom. 3 MΩ 100 pF |
| Output | |
| Current output (direct or inverted action) | 0...20, 4...20, S4...20, ±10, ±20 mA |
| Load (max.), current output | ≤ 800Ω |
| Current limit | ≤ 28mA (unipolar) / ± 28mA (bipolar) |
| Passive 2-wire programmable ranges | 0 to 20 and 4 to 20mA (direct or inverted action) |
| External 2-wire loop supply | 3.5 to 30VDC |
| Load stability | ≤ 0.001% of span / 100Ω |
| Response time, programmable | 0.0 to 60.0 sec |
| Voltage output (direct or inverted action) | 0/0.2...1, 0/1...5, 0/2...10, ±1, ±5, ±10V |
| Load (min.), voltage output | ≥ 500kΩ |
| Response time, programmable | 0.0 to 60.0 sec |



Wiring Diagram

Model SCU-7900





Supply:



Inputs:






Outputs:



SCU-7900 Signal Conditioner

Dimensions

mm [inches]



See our website www.AutomationDirect.com for complete Engineering drawings.

SCU Series Universal Signal Conditioner Accessories

Programming/Display Module SCU-PDM2



Application:

- The AutomationDirect SCU-PDM2 module easily connects to the front of the Universal Signal Conditioners and is used as a display and to enter or adjust the programming of the module.
- Can be moved from one module to another and download the configuration of the first transmitter to subsequent transmitters.
- Fixed display for visualization of process data and status.
- Required for programming all SCU Series Universal Signal Conditioner models.

Technical characteristics:


- LCD display with 4 lines; Line 1 (H = 5mm, 0.20 in) shows input signal, line 2 (H = 3.5 mm, 0.14 in) shows units, line 3 (H = 3.5 mm, 0.14 in) shows analog output or user defined text and line 4 shows communication and relay status.
- Programming access can be blocked by assigning a password. The password is saved in the transmitter in order to ensure against unauthorized modifications to the configuration.
- Not capable of standalone or remote operation.
- For Use With: SCU-3100, SCU-1400, SCU-1600, SCU-8400, SCU-7900, SCU-2200, SCU-2501, SCU-2502, SCU-2503

Mounting/Installation:

- Snap SCU-PDM2 onto the front of the universal signal conditioners.
- Can be installed or removed whether the signal conditioner is powered or not.

Selectable Engineering Units

| | | | | | |
|---------|--------|---------------------|------|-----|-----|
| °C | hp | kW | mA | PH | MHz |
| °F | hPa | kWh | mbar | rPM | P/m |
| % | Hz | l | mils | s | P/h |
| A | in | l/h | min | S | P/d |
| bar | in/h | l/min | mm | t | |
| cm | in/min | l/s | mm/s | t/h | |
| ft | in/s | m | mol | uA | |
| ft/h | ips | m/h | MPa | um | |
| ft/min | K | m/min | mV | uS | |
| ft/s | kA | m/s | MW | V | |
| g | kg | m/s ² | MWh | W | |
| gal/h | kJ | m ³ | N | Wh | |
| gal/min | kPa | m ³ /h | Ohm | yd | |
| GW | kV | m ³ /min | Pa | KHz | |



External Cold Junction Compensation Connector



Installation:

- Remove terminal block included with SCU-1400, SCU-1600 or SCU-3100 signal conditioner and replace with SCU-CJC1.

Part No. SCU-CJC1

See our website www.AutomationDirect.com for complete Engineering drawings.

| SCU Series Signal Conditioner Accessories | | | | |
|---|--|---|-------------|---------|
| Part No. | Description | | Weight (lb) | Price |
| <u>SCU-PDM2</u> | ProSense detachable programming/display module, for use with SCU series signal conditioners. | 1 | 0.04 | \$59.00 |
| <u>SCU-CJC1</u> | ProSense external cold junction compensation (CJC) connector, for use with SCU-3100, SCU-1400, SCU-1600 signal conditioners. | 1 | 0.02 | \$18.00 |