

Stride MQTT Gateway



Features

- Convert Modbus RTU/TCP to MQTT
- IIoT MQTT protocol with SSL/TLS
- Configurable via web page
- Hardware watchdog function
- Full electrical isolation
- Add this to your MQTT cloud, compatible with AWS, Mosquitto and more
- Wired or Wi-Fi models available



Stride MQTT Gateway Models				
Part Number	Ethernet	RS-485	WiFi	Price
<u>SGW-MQ1611</u>	✓	✓		\$275.00
<u>SGW-MQ1611-WF</u>	✓	✓	✓	\$279.00

Ethernet Specifications	
Connector	RJ-45
Ethernet Port Speed	10/100Mbps auto-detected
Protocol	MQTT, Modbus TCP
Simultaneous Ethernet Connections	8

WiFi Specifications (Model SGW-MQ1611-WF Only)	
WiFi Standards	802.11 a/b/g/n/ac
Frequency Bands	2.4/5.5 GHz
Antenna	Internal

RS-485 Specifications	
Connector	Removable screw terminals, 5.08 mm pitch
Baud rate	Up to 115.2 kbps
Parity	Even, odd or none
Stop bit	1 or 2
Number of Serial Devices	32 max.
Switching Time TX/RX (RS-485)	150µs
Termination Resistance	120Ω

Network Ports	
Web User Interface: HTTP (Unsecure)	80
Modbus	502 (default, software configurable)
MQTT	Software configurable, determined by MQTT Broker



RoHS



RoHS Compliant

Stride MQTT Gateway

Electrical Specifications

Power Supply Connector	Removable screw terminals, 5.08 mm pitch
Input Voltage Range	10–30 VDC
Current Consumption	max 300mA @ 24VDC
Isolation	
Power Supply / RS-485	1500VAC, 50Hz, 1 min.
Ethernet / RS-485	1000VAC, 50Hz, 1 min.
Ethernet / Power Supply	1500VAC, 50Hz, 1 min.
Reverse Polarity Protection	Yes

Mechanical Specifications

Material	Self-extinguishing plastic
Mounting	35mm DIN rail (EN50022 and EN50035)
Weight	Approximately 200g

Environmental Specifications


Operating Temperature	0 to +60°C [32 to 140°F]
Storage Temperature	-20 to +70°C [-4 to +158°F]
Humidity	0–90%, noncondensing
Maximum Altitude	2000m
IP Rating	IP20
Installation	Indoor
Category of Installation	II
Pollution Degree	2
EMC	
Immunity	EN61000-6-2
Emission	EN61000-6-4
Agency Approvals	CE, FCC, RoHS



NOTE: Installation of the Wi-Fi model in a metal cabinet is not recommended, as the cabinet may block the Wi-Fi signal.

Dimensions

mm [inches]



See our website: www.AutomationDirect.com for complete engineering drawings.

