



# Audible Signal Devices


## 22.5 mm Panel-mount Electrical Buzzers with Acknowledgment Function

### Buzzer without sound output holes

- Mount in 22.5 mm hole
- LED permanent light with continuous tone
- 80 decibels volume at one meter
- Lightly press to silence the audible signal
- Potential-free output for transmission of the acknowledgment signal to the control unit
- Positive and negative logic



### Wiring Diagram



450 Series Buzzer Specifications		
Part Number	45010055	45030055
Price	\$164.00	\$164.00
Drawing Link	PDF	PDF
Description	Buzzer element with acknowledgment function	
LED Indicator Color	Red	Yellow
Voltage	24V /DC	
Current Consumption	≤ 0mA	
Tone Frequency	3kHz	
Maximum Volume	80dB @ 1m	
Max. Output (acknowledgment)	Solid State 30V, 100mA	
Tone Type	Continuous	
Life Duration	> 50,000h	
Operating Temperature	-4 to 122°F [-20 to 50°C]	
Protection	IP65	
Weight	40g [1.41 oz]	
Housing Material	Cap: Polycarbonate. Body: Black Polycarbonate	
Connection	Connector plug with screwable connection max. 0.5 mm² (20AWG)	
Agency Approvals	cULus file E164155, CE, RoHS	

To obtain the most current agency approval information, see the Agency Approval Checklist section on the specific part number's web page.

