



Audible Signal Devices

22.5 mm Panel-mount Electrical Buzzers



Features

- Mount in 22.5 mm hole
- Eighteen models available
- Continuous and pulse-tone models
- 80 to 100 decibels
- Buzzer without sound output holes
- Low current consumption
- IP65 protection rating



107 Series Buzzer Specifications

Part Number	10700060	10700070	10700075	10700077	10701060	10701070	10701075	10701077
Price	\$38.50	\$33.50	Retired	Retired	\$38.50	\$33.50	Retired	Retired
Drawing Link	PDF	PDF	PDF	PDF	PDF	PDF	PDF	PDF
Description	Buzzer							
Voltage	115–230 VAC	12/24 VAC/VDC	24 VAC/VDC	115 VAC/VDC	115–230 VAC	12/24 VAC/VDC	24 VAC/VDC	115 VAC/VDC
Current Consumption	12mA	8mA	≤ 8mA		12mA	8mA	≤ 8mA	
Tone Frequency	2.4 kHz							
Maximum Volume	80dB @ 10cm							
Tone Type	Continuous				Pulse		Pulse, approx.1Hz	
Life Duration	> 5000h							
Operating Temperature	-4 to 122°F [-20 to 50°C]							
Protection	IP65							
Weight	20g [0.70 oz]		30g [1.06 oz]		20g [0.70 oz]		30g [1.06 oz]	
Housing Material	Glass fiber reinforced polyamide							
Connection	Connector with max wire 1.5 mm² (16 AWG), 0.3 N torque							
Agency Approvals	cULUS File E164155, CE							

109 Series Buzzer Specifications

Part Number	10900075	10900077	10901075	10901077
Price	\$69.00	\$78.00	\$69.00	\$78.00
Drawing Link	PDF	PDF	PDF	PDF
Description	Buzzer			
Voltage	24V AC/DC	115V AC/DC	24V AC/DC	115V AC/DC
Current Consumption	≤ 25mA			
Tone Frequency	2.1 kHz			
Maximum Volume	80dB @ 1m			
Tone Type	Continuous		Pulse, approx. 1Hz	
Life Duration	> 5000h			
Operating Temperature	-4 to 122°F [-20 to 50°C]			
Protection	IP65			
Weight	44g [1.55 oz]	47g [1.66 oz]	44g [1.55 oz]	47g [1.66 oz]
Housing Material	ABS(PC) Polycarbonate (black)			
Connection	Connector with max wire 1.5 mm² (16 AWG), 0.3 N torque			
Agency Approvals	cULus File E164155, CE			





Audible Signal Devices

22.5 mm Panel-mount Electrical Buzzers

Buzzer without sound output holes

- Mount in 22.5 mm hole
- 8 selectable tones
- Adjustable volume, 100 decibels maximum at one meter



110 Series Buzzer Specifications		
Part Number	11000067	11000075
Price	\$116.00	\$105.00
Drawing Link	PDF	PDF
Description	Buzzer Element with selectable tones	
Voltage	115VAC	24V AC/DC
Current Consumption	≤ 40mA	≤ 80mA
Tone Frequency	1.6 and 3.4 kHz	
Maximum Volume	100dB @ 1m	
Tone Type	Multi-tonal, 8 selectable tones	
Life Duration	> 5000h	
Operating Temperature	-4 to 122°F [-20 to 50°C]	
Protection	IP65	
Weight	79g [2.79 oz]	64g [2.26 oz]
Housing Material	ABS/(PC) Polycarbonate (black)	
Connection	Connector with max wire 1.5 mm² (16 AWG), 0.3 N torque	
Agency Approvals	cULus File E164155, CE	

Note: Refer to insert for available tones.


Buzzer with LED Indicator

- Mount in 22.5 mm hole
- LED permanent light indicator
- Continuous tone
- Simple connection with connector plug
- 80 decibels volume at one meter



150 Series Buzzer with LED Indicator Specifications				
Part Number	15010055	15010067	15030055	15030067
Price	\$82.00	\$89.00	\$82.00	\$89.00
Drawing Link	PDF	PDF	PDF	PDF
Description	Buzzer element with LED indicator			
LED Indicator	Red		Yellow	
Voltage	24VDC	115VAC	24VDC	115VAC
Current Consumption	≤ 50mA	≤ 20mA	≤ 50mA	≤ 20mA
Tone Frequency	2.8 kHz			
Maximum Volume	80dB @ 1m			
Tone Type	Continuous			
Life Duration	Up to 50,000h			
Operating Temperature	-4 to 122°F [-20 to 50°C]			
Protection	IP65			
Weight	30g [1.06 oz]			
Housing Material	Cap: Polycarbonate. Base: ABS/(PC) Polycarbonate (black)			
Connection	Connector with max wire 1.5 mm² (16 AWG), 0.3 N torque			
Agency Approvals	cULus File E164155, CE			

Wiring Diagram



Note: Buzzer will not sound without light energized.