



How to Select your WERMA Signal Device

STEP 1


Select the required panel or freestanding beacon or buzzer for your application

STEP 2


Select the required beacon height/depth for your application from either the panel beacons and buzzers or free-standing beacons.



Installation Beacons and Buzzers



Freestanding Beacons



*Bracket mount also available



How to Select your WERMA Signal Device

STEP 3

Select the correct mount for your application

Panel Mounting

Series: 230, 231, 206, 207, 208

PG 29 Mounting

Series: 815, 816, 817

Base Mounting

Series: 200, 201, 202, 210, 211, 212, 220, 221, 222, 826, 827, 828, 829

Bracket Mounting

Series: 203, 204, 205, 213, 214, 215, 223, 224, 225

Tube Mounting
Series: 209, 219

STEP 4

Where appropriate, select a mounting accessory for your PG29, base-mounted, or tube-mounted beacon.



Anti-twist washer for beacons with 37mm PG29 mounting

Order no. [97581522](#)



Tube adapter for beacons with 37mm PG29 mounting

Order no. [97581201](#)



Galvanized Wire Guard - for use with 826, 827, 828 and 829 series industrial signal beacons

Order no. [97582603](#)



Plastic Bracket for wall mounting - for use with 826, 827, 828 and 829 series industrial signal beacons

Order no. [97582605](#)



Plastic Base with integrated tube for use with 209 and 219 series beacons

Order no. [97520901](#)



Cable gland (M25x1.5, plastic) for use with 209 and 219 series industrial signal beacons

Order no. [97520902](#)



Surface mounting enclosure for 1 beacon with 37mm PG29 mounting

Order no. [97581503](#)



Surface mounting enclosure for 2 beacons with 37mm PG29 mounting

Order no. [97581507](#)



Surface mounting enclosure for 3 beacons with 37mm PG29 mounting

Order no. [97581508](#)



Surface mounting base for beacons with 37mm PG29 mounting

Order no. [97581202](#)

Tube Ø 25mm, all anodized

Order no. [97584510](#)
100mm long [97584025](#)
250mm long [97584040](#)
400mm long [97584060](#)
600mm long [97584080](#)
800mm long [97584003](#)
1000 mm long



Base for Tube, plastic
Order no. [97584090](#)

Base for Tube, metal
Order no. [97584091](#)

Foldaway Base
Order no. [96000030](#)

Tube Ø 25mm, plastic, only for Foldaway Base, 45mm long
Order no. [96000031](#)



Contact box with a side cable exit
Order no. [97584001](#)



Contact box with magnetic base and side cable exit
Order no. [97584004](#)



Bracket for base mounting with concealed cable entry

Order no. [96000014](#)



Bracket for tube mounting

Order no. [96000001](#)



WERMA Signaling Overview

Description

WERMA offers a wide range of signaling devices for either installation panel or surface mount applications. Modern designs and the latest LED technology provide exceptionally clear and bright signalling.

Installation Beacon Connections and Audible Signal Devices

WERMA installation beacons are designed for mounting in panels or enclosures. A characteristic of this beacon type is that the rear fixture uses a central nut.

- Permanent, blinking, flashing, or LED beacons
- High protection rating IP65
- Beacons in 29, 57/58, and 75mm beacon diameters
- Audible modules with sight/sound combinations
- Signal modules come in common voltages (24V AC/DC, 115VAC, and 230VAC)
- Five colors
- For installation in 22.5 or 34mm cutouts

Freestanding Beacons

WERMA freestanding beacons offer a range of modules including: permanent, blinking, flashing, LED EVS, and LED rotating.

- Base, bracket or tube mounting
- Incandescent, LED, or Xenon light sources
- High protection rating IP65
- 57/58/75/98mm beacon diameters available
- Tall lens option available
- Signal modules in common voltages (24V AC/DC, 115VAC, and 230VAC)
- Five colors available

Beacon Accessories

Accessories for installation and freestanding beacons:

- Tube adapter, mounting base, surface-mounting enclosures, washers, for installation beacons
- Wire guard, bracket, wall-mount bracket, base and tube, and cable gland for freestanding beacons

