



M.G.M. ELECTRIC MOTORS BAX IE2 HIGH EFFICIENCY AC INDUCTION MOTOR, GENERAL PURPOSE, INVERTER RATED AND BRAKE, 1/2HP, 3-PHASE, 230/460 VAC, 1800RPM, TEFC, IEC 71 FRAME, ALUMINUM, C-FACE/REMOVABLE RIGID BASE (B34) MOUNT, INTEGRATED BRAKE ASSEMBLY INCLUDED

18I6

AutomationDirect.com  
1-800-633-0405



3rd  
ANGLE

NOT TO  
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY  
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED  
FOR PART DESIGN

UNLESS OTHERWISE  
SPECIFIED UNITS ARE:

inch  
[mm]

LATEST VERSION  
6/3/2024

SHEET 1 OF 1