



5-PORT (4-WAY), 3-POSITION, CENTER PRESSURE, 90 DEG HAND LEVER, SPRING RETURN, 1/8IN FEMALE NPT INLET(S), 1/8IN FEMALE NPT OUTLET(S), 1/8IN FEMALE NPT EXHAUST(S), CV=0.55.

METAL WORK MANUAL VALVE

7010001100U

AutomationDirect.com
1-800-633-0405



3rd
ANGLE

NOT TO
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED
FOR PART DESIGN

UNLESS OTHERWISE
SPECIFIED UNITS ARE:

mm
[inch]

LATEST VERSION
2/8/2024

SHEET 1 OF 1