



FINGER-SAFE, 380A, 1-POLE, LINE SIDE: 1 OPENINGS ACCEPT 500 MCM TO 4 AWG CU/AL, LOAD SIDE: 1 OPENINGS ACCEPT 500 MCM TO 4 AWG CU/AL, DIN RAIL OR PANEL MOUNT, UL 1953 LISTED.

PENN UNION OPEN SPLICER/REDUCER BLOCK

ASRB-11-500-1

AutomationDirect.com
1-800-633-0405



3rd
ANGLE

NOT TO
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY
DUE TO MANUFACTURER'S VARIANCES

INCH UNITS USED FOR
PART DESIGN

UNLESS OTHERWISE
SPECIFIED UNITS ARE:

inch
[mm]

LATEST VERSION
6/25/2024

SHEET 1 OF 1