



ENDRESS+HAUSER PICOMAG LIQUID FLOW METER, MAGNETIC-INDUCTIVE, 2IN FEMALE NPT, 0 TO 198.1 GPM, 14 TO 158 DEG F, +/- 3.436E10 LITERS, 20 TO 10,000 µS/cm, OUTPUT: SWITCH, PULSE, ANALOG, DISCRETE INPUT, IO-LINK, OUTPUT 2: SWITCH, ANALOG, DISCRETE INPUT, EPDM RUBBER SEAL(s)

DMA50-AAADA1

AutomationDirect.com
1-800-633-0405



3rd
ANGLE

NOT TO
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED
FOR PART DESIGN

UNLESS OTHERWISE SPECIFIED UNITS ARE: **mm** [inch]

MODEL
REV.

DRAWING DATE
12/8/2025

SHEET 1 OF 1