


FINGER-SAFE, 115A, 1-POLE, LINE SIDE: 1 OPENING ACCEPTS 2 AWG TO 18 AWG,
LOAD SIDE: 1 OPENING ACCEPTS 6 AWG TO 10 AWG & 6 OPENINGS ACCEPT 6
AWG TO 14 AWG, DIN RAIL OR PANEL MOUNT, UL 1059 RECOGNIZED.

GLADIATOR ENCLOSED TERMINAL BLOCK

GPB2-115P1-6L

AutomationDirect.com
1-800-633-0405



3rd
ANGLE
NOT TO
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED
FOR PART DESIGN

UNLESS OTHERWISE
SPECIFIED UNITS ARE:
mm
[inch]

LATEST VERSION
8/5/2024

SHEET 1 OF 1