



TECHNICAL SPECIFICATIONS


| | |
|--------------------------|-----|
| SLPC [MM] | 175 |
| US [USEFUL STROKE] | 175 |
| MS [MECHANICAL STROKE] | 179 |
| L [TOTAL LENGTH] | 347 |



ISOMETRIC VIEW



EXTENDED



RETRACTED

PROSENSE POTENTIOMETER LINEAR POSITION SENSOR, PIVOTING SLIDE, 175MM STROKE, 38MM DIAMETER X 278MM BODY, ROD EYES MOUNT, 8MM DIN 43650 FORM C.

LCR-38P-0175-C5-C1

AutomationDirect.com
1-800-633-0405



3rd
ANGLE

NOT TO
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED
FOR PART DESIGN

UNLESS OTHERWISE
SPECIFIED UNITS ARE:

mm
[inch]

LATEST VERSION
1/15/2025

SHEET 1 OF 1