



# TECHNICAL SPECIFICATIONS

|                          |     |
|--------------------------|-----|
| SLPC [MM]                | 550 |
| US [ USEFUL STROKE ]     | 550 |
| MS [ MECHANICAL STROKE ] | 554 |
| L [ TOTAL LENGTH ]       | 689 |



ISOMETRIC VIEW



PROSENSE POTENTIOMETER LINEAR POSITION SENSOR, FIXED SLIDE, 550MM STROKE, 33 X 33 X 630MM BODY, CHANNEL MOUNT, 18MM DIN 43650 FORM A.

**LSR-33P-0550-D5-C1**

AutomationDirect.com  
1-800-633-0405



3rd  
ANGLE

NOT TO  
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY  
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED  
FOR PART DESIGN

UNLESS OTHERWISE  
SPECIFIED UNITS ARE:

mm  
[inch]

LATEST VERSION  
1/14/2025

SHEET 1 OF 1