





# TECHNICAL SPECIFICATIONS

SLPC [MM]	100
US [ USEFUL STROKE ]	100
MS [ MECHANICAL STROKE ]	104
L [ TOTAL STROKE ]	392



ISOMETRIC VIEW



PROSENSE POTENTIOMETER LINEAR POSITION SENSOR, SPRING LOADED SLIDE, 100MM STROKE, 33 X 33 X 197MM BODY, CHANNEL MOUNT, 8MM DIN 43650 FORM C.

**LSSR-33P-0100-B5-C2**

AutomationDirect.com  
1-800-633-0405



3rd  
ANGLE

NOT TO  
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY  
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED  
FOR PART DESIGN

UNLESS OTHERWISE  
SPECIFIED UNITS ARE:

**mm**  
[inch]

LATEST VERSION  
1/14/2025

SHEET 1 OF 1