




SECTION A-A



Ø 25.00<sup>+0.009</sup><sub>-0.004</sub>  
[0.984<sup>+0.0004</sup><sub>-0.0002</sub>]



HARDWARE INCLUDED	
TYPE	QTY
SPACER: 34.0 OD X 25.7 ID X 3.4T	2
ROUNDED KEY: 8.0W X 7.0 T X 25.0 LONG	2
ROUNDED KEY: 8.0W X 7.0 T X 40.0 LONG	2
RETAINING RING: FREE Ø 23.1 X 1.1 THICK	2

IRONHORSE GEARBOX DOUBLE OUTPUT SHAFT

WGA-50M-D-IEC

AutomationDirect.com  
1-800-633-0405



3rd  
ANGLE

NOT TO  
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY  
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED  
FOR PART DESIGN

UNLESS OTHERWISE  
SPECIFIED UNITS ARE:

mm  
[inch]

LATEST VERSION  
1/2/2025

SHEET 1 OF 1