



# Accessories

## Replacement Relays

Replacement 24VDC relays are offered for use with the **ZIPLink** relay modules [ZL-RRL16F-24-1/-2](#).

Sold in packages of 4.



**ZL-RELAY-F24X4**  
**\$24.00**

ZL-RELAY-F24x4 24VDC Relay Specifications			
Contact		Coil	
<b>Current Rating</b>	30VDC @ 8A 250VAC @ 8A General Use	<b>Input Voltage Range</b>	24VDC (-20%/+30%)
		<b>Maximum Continuous Coil Voltage</b>	31.2 VDC
<b>Contact Type</b>	1 Form C (SPDT)	<b>Rated Current per Coil</b>	16.7 mA (±10%) @ 24VDC
<b>Contact Voltage (per point)</b>	250VAC / 30VDC	<b>Coil Resistance</b>	1440Ω (±10%)
<b>Maximum Power Inductive</b>	2000VA General Use	<b>Power Consumption per Coil</b>	0.4 W
<b>Maximum Power Resistive</b>	AC 2000VA, DC 240W	<b>Pick Up Current Max. per Coil</b>	15mA
<b>Maximum Switching Voltage</b>	250VAC, 300VDC	<b>Drop-Out Voltage Min.</b>	1.2 VDC
<b>Minimum Load</b>	10mA @ 5VDC	<b>Pick-Up Voltage Max.</b>	19.2 VDC
<b>Contact Resistance</b>	100mΩ Max @ 1A, 6VDC	<b>Off to On/On to Off Response Time</b>	12ms/8ms
<b>Contact Material</b>	AgNi (Silver Nickel Alloy)	<b>Weight (lbs)</b>	0.11