



TABLE OF CONTENTS

Introduction

BRX Introduction	ii
Conventions Used.....	iii
BRX Overview	iv
BRX Platform	v

Chapter 1: General Installation and Wiring Guidelines

Safety Guidelines	1-2
Introduction to the BRX Mechanical Design	1-5
Dimensions and Installation.....	1-6
Mounting Guidelines.....	1-10
Wiring Guidelines	1-15
I/O Module Wiring Options	1-24
System Wiring Strategies	1-26

Chapter 2: BX ME Wiring

BX ME Micro PLC Unit (MPU) Overview	2-2
BX-DM1E-M Wiring	2-4
BX-DM1E-M-D Wiring	2-6

Chapter 3: BX 10/10E Wiring

BX 10/10E Micro PLC Unit (MPU) Overview	3-2
BX 10 Micro PLC Units (MPUs)	3-8
BX 10E Micro PLC Units (MPUs)	3-31

Chapter 4: BX 18/18E Wiring

BX 18/18E Micro PLC Units (MPUs) Overview	4-2
BX 18 Micro PLC Units (MPUs)	4-9
BX 18E Micro PLC Units (MPUs)	4-50

Chapter 5: BX 36/36E Wiring

BX 36/36E Micro PLC Units (MPUs) Overview	5-2
BX 36 Micro PLC Units (MPUs)	5-9
BX 36E Micro PLC Units (MPUs)	5-50

Chapter 6: BRX Pluggable Option Module (POM)

Overview	6-2
BX-P-SER2-TERM	6-4
BX-P-SER4-TERM	6-5
BX-P-SER2-RJ12	6-6
BX-P-ECOMLT	6-7
BX-P-USB-B	6-8

Chapter 7: BRX Digital I/O Expansion Modules

Overview	7-2
Module Types	7-3
Wiring Termination Options	7-5
General Specifications	7-8
Module Installation	7-8
BX-08NF3 Sinking/Sourcing 3–5 VDC Input	7-9
BX-xxND3 Sinking/Sourcing 12–24 VDC Input	7-10
BX-xxNB 12–24 VAC Input	7-13
BX-xxNA 120–240 VAC Input	7-15
BX-08SIM Simulator Input	7-17
BX-xxTD1 Sinking 12–24 VDC Output	7-18
BX-xxTD2 Sourcing 12–24 VDC Output	7-21
BX-xxTR Relay Output	7-24
BX-05TRS Relay Output	7-26
BX-xxTA 120–240 VAC Output	7-27
BX-08CD3R Combination DC Input/Relay Output	7-29
BX-xxCD3D1 Combination DC Input/Sinking DC Output	7-31
BX-xxCD3D2 Combination DC Input/Sourcing DC Output	7-34

Chapter 8: BRX Analog I/O Expansion Modules

Overview	8-2
Module Types	8-2
Wiring Termination Options	8-4
General Specifications	8-6
Dimensional Information	8-6
Module Installation	8-7
Module Configuration	8-8
Analog Tips and Troubleshooting	8-9
BX-04ADM-1 Analog Current Sinking Input	8-16
BX-xxAD-1 Analog Current Sinking Input	8-20
BX-xxAD-2B Analog Voltage Input	8-27
BX-xxTHM Thermocouple Input	8-34

BX-06RTD Resistance Temperature Detector Input	8-40
BX-08NTC Thermistor Input	8-46
BX-4RTD4DA-1 Combination RTD Input/Current Output	8-51
BX-4THM4DA-1 Combination Thermocouple Input/Current Output	8-56
BX-xxDA-1 Analog Current Source Output	8-61
BX-xxDA-2B Analog Voltage Output	8-66
BX-xADxDA-1 Combination Analog Current Input/Output.....	8-71
BX-xADxDA-2B Combination Analog Voltage Input/Output.....	8-75

Chapter 9: BRX Motion Control and Communications Expansion Modules

Overview	9-2
Module Types	9-2
Wiring Termination Options	9-3
General Specifications	9-4
Dimensional Information	9-4
Module Installation	9-5
BX-HSIO High Speed Input/Output Modules.....	9-6
BX-SERIO Serial Communications Module	9-8
Module Configuration.....	9-10

Chapter 10: BRX Do-more! CPU Specifications

The BRX Platform	10-2
Do-more! Designer Software	10-3
BRX Do-more! CPU Common Specifications	10-3
Battery Replacement	10-10
microSD Slot	10-11
Customizing the Logo Window	10-12
Replacing Access Covers.....	10-13
RS-232/485 Port Specifications	10-14
Ethernet Port Specifications.....	10-16
POM Slot.....	10-16

Chapter 11: BRX Do-more! Motion Control and High-speed I/O

Overview	11-2
BRX Wiring Examples: High-Speed Inputs	11-5
BRX Wiring Examples: High-speed Outputs	11-9
Available High-Speed Input and Output Features.....	11-15
Access Setup High Speed I/O page	11-16
BRX High-Speed Examples	11-47
BRX High-speed Instructions	11-66

Chapter 12: BRX Do-more! Serial Communications

Overview	12-2
Troubleshooting Serial Communications.....	12-4
Communications Design	12-5
USB Communications.....	12-9
Serial Communications.....	12-10
General Serial Specifications	12-10
Serial Port Setup and Programming.....	12-15
Serial Protocols	12-18

Chapter 13: BRX Do-more! Ethernet Communications

Overview	13-2
Troubleshooting Ethernet Communications.....	13-6
Communications Design	13-8
Ethernet	13-13
Ethernet Protocols.....	13-21

Chapter 14: BRX Remote I/O: BX-DMIO, BX-EBC100 & GS-EDRV100

What it is.....	14-2
BX-DMIO & BX-EBC100 I/O Controllers	14-3
AC Power Wiring (BX-DMIO-M & BX-EBC100-M).....	14-6
DC Power Wiring (BX-DMIO-M-D & BX-EBC100-M-D).....	14-7
Ethernet Communications.....	14-8
DIP Switch Specifications	14-8
Status Indicators	14-9
Supported Modules.....	14-10
Configuration.....	14-11
GS-EDRV100.....	14-21

Chapter 15: BX-MBIO Modbus I/O Controller

Overview	15-2
BX-MBIO I/O Controllers.....	15-3
Configuration.....	15-8
DIP Switch Specifications	15-8
Status Indicators	15-9
Modbus Protocol Function Codes Supported by BX-MBIO	15-10
Modbus Protocol Exception Responses	15-13
Modbus RTU, Serial Communications.....	15-15
Modbus TCP, Ethernet Communications	15-20
BX-MBIO Configuration	15-20
Troubleshooting with Modbus Poll.....	15-33
Additional BX-EBC100 and BX-MBIO Modbus Mapping Information.....	15-45

Appendix A: BRX Do-more! Maintenance and Troubleshooting

Hardware MaintenanceA-2
Diagnostics.....A-3
CPU IndicatorsA-5
PWR IndicatorA-6
RUN IndicatorA-7
ERR IndicatorA-7
Communications ProblemsA-7
I/O TroubleshootingA-8
Noise TroubleshootingA-10

Appendix B: EU Directives (CE)

European Union (EU) DirectivesB-2
Basic EMC Installation GuidelinesB-5

Appendix C: BRX MPU Power Budgeting

BRX MPU Power BudgetC-2

Appendix D: Error Codes and System Locations

Do-more! Designer Errors and System Locations..... D-2

Appendix E: NetEdit—Ethernet Setup Utility for HOST Automation Products

Basic Ethernet wiring and setup E-2
NetEdit 3 Software E-4

Appendix F: Tips & Tricks

Tips & Tricks..... F-2

Appendix G: OnliAppendixe Resources

Online Resources G-2

