

Disconnect Handle Applications for Disconnect Enclosures

Designed to house the following available at AutomationDirect.com

- AutomationDirect.com NEMA 1/12 Flexible shaft handle for Molded Case Circuit Breakers (MCCBs). Series F_S0_C flex handle mechanisms are available in four sizes to actuate all AutomationDirect MCCBs from 15 amps up to 600 amps. **F0S03C, F0S06C, F1S03C, F1S06C, F3S03C, F3S06C, F4S04C, and F4S06C**
- Socomec Disconnect switches with cable, flange-mounted cable operator and handles. Handles **37299002** and **37299003**, cable operator **37299903**, and cables **37299992** (3ft) or **37299993** (5ft)
- Fuji Electric NEMA 12 flexible shaft handle for Molded Case Circuit Breakers (MCCBs). Series BW9F flex handle mechanisms are available in four sizes to actuate all Fuji Electric MCCBs from 15 Amps to 800 Amps. **BW9F0CA-15A, BW9F0CA-20A, BW9F0GA-15A, BW9F0GA-20A, BW9F0HA-15A, BW9F0HA-20A, BW9F0JA-15A, and BW9F0JA-20A.**
- Gladiator Molded Case Circuit Breakers (MCCBs) flange mounted cable operator and handles. See Gladiator sections for handles and cable options. **GCBX1-FHC-N3R4-M, GCBX1-FHC-N4X-M, GCBX5-FHC-N3R4-M, and GCBX5-FHC-N4X-M**

Available at AutomationDirect.com

Disconnect Enclosure Series	AutomationDirect F_S0_C Series	Socomec 37299002 and 37299003	Fuji BW9F series	Gladiator GCBX
N412_CD Series	✓	✓	✓	✓
N412_CDSS Series	✓	✓	✓	✓
N412_CDSSA Series	✓	✓	✓	✓
N412_CSTD Series	✓	✓	✓	✓
N412_CSSSTD Series	✓	✓	✓	✓
SDN_PL Series	✓	✓	✓	✓
SN4 Series	✓	✓	✓	✓
ABN12 Series	✗	✗	✗	✗
SSN4X Series	✓	✓	✓	✓
SSN4X_A Series	✓	✓	✓	✓
WRD-XM_FS4 Series	✓	✓	✓	✓
WRD-XM_FSD4 Series	✓	✓	✓	✓

Designed to house other brands

- Allen-Bradley** Bulletin 1494V and 140U disconnect switches with flange-mounted variable-depth operating mechanisms and Bulletin 1494V flange-mounted variable-depth operating mechanisms for circuit breakers. These enclosures will not accept Allen-Bradley Bulletin 1494F disconnect devices or Bulletin 1494D circuit breaker operators
- ABB Controls** flange-mounted variable-depth operating mechanisms for disconnect switches and circuit breakers
- Eaton / Cutler-Hammer** Type C361 flange-mounted variable depth
- Eaton / Cutler-Hammer** Type C361 flange-mounted variable-depth operating mechanisms with disconnect switches and Type C371 flange-mounted variable depth operating mechanisms for circuit breakers; also Flex Shaft™ handle mechanisms for circuit breakers
- General Electric** Type STDA flange handles and variable depth operating
- General Electric** Type STDA flange handles and variable depth operating mechanisms for disconnect switches and circuit breakers; also Spectra Flex™ cable operators for circuit breakers
- SIEMENS** I-T-E Max-Flex flange-mounted variable depth operating handle for disconnect switches and circuit breakers
- Square D** Class 9422 disconnect switches with flange-mounted variable depth operating mechanisms or cable Industry Standards mechanisms and Class 9422 flange-mounted variable depth operating mechanisms or cable mechanisms for circuit breakers. These enclosures will not accept Square D Class 9422 bracket-mounted disconnect devices, Class 9422TG1, or TG2 devices.

Other Brands

Disconnect Enclosures Series	Square D 9422 series	Allen-Bradley 1494F and 1494D series	Allen-Bradley 1494V, 1494C, 140U, 194RC series	ABB Controls	Eaton/Cutler-Hammer C361 and C371 series	General Electric STDA series	Siemens I-T-E Max-Flex Series
N412_CD Series	✓	✗	✓	✓	✓	✓	✓
N412_CDSS Series	✓	✗	✓	✓	✓	✓	✓
N412_CDSSA Series	✓	✗	✓	✓	✓	✓	✓
N412_CSTD Series	✓	✗	✓	✓	✓	✓	✓
N412_CSSSTD Series	✓	✗	✓	✓	✓	✓	✓
SDN_PL Series	✓	✗	✓	✓	✓	✓	✓
SN4 Series	✓	✗	✓	✓	✓	✓	✓
ABN12 Series	✗	✓	✗	✗	✗	✗	✗
SSN4X Series	✓	✗	✓	✓	✓	✓	✓
SSN4X_A Series	✓	✗	✓	✓	✓	✓	✓
WRD-XM_FS4 Series	✓	✗	✓	✓	✓	✓	✓
WRD-XM_FSD4 Series	✓	✗	✓	✓	✓	✓	✓

NEMA 4, 4X, 12, and 13 Ultimate Series Single-Door Wall-Mount Right-Flanged Disconnect



Construction

- CD enclosures have 14-gauge carbon steel bodies and doors
- Large tub opening for better access
- Concealed hinges
- Interchangeable and easily removable doors
- Ground stud located in door
- Doors sealed with poured-in-place polyurethane gasket
- Mounting holes in rear
- Studs for mounting optional subpanel
- Door latching system installed on door with a slotted insert defeater mechanism
- Latching system interlocks with the disconnect handle (not included) for added safety

Finish

- ANSI 61 gray polyester powder inside and out over phosphatized surfaces
- Painted steel subpanels are white polyester powder over phosphatized surfaces
- Galvanized and stainless steel subpanels are a conductive finish (unpainted)

Listings

- UL 508 4, 12, and 13 [UL File E64791]
- NEMA/EEMAC 4, 12, and 13



Notes: Disconnect switch or circuit breakers, operating handle, operating mechanism must be ordered separately.

Operator adapter plates are not required with this enclosure series.

Make sure the disconnect device you are using will fit the enclosure size you choose.

Shipping Schedule

Same day 1 - 5 days 1 - 7 days 1 - 15 days 1 - 20 days

Color indicates shipping lead time in business days.

NEMA 4, 4X, and 12 Ultimate Series Single-Door Wall-Mount Right-Flanged Disconnect

Part Number	Price	Enclosure Size HxWxD	Painted Steel Subpanel	Galvanized Subpanel	Stainless Steel Subpanel
N412202208CD	\$639.00	20.00 x 22.00 x 8.89 [508 x 559 x 226]	NP2020C	NP2020CG	NP2020SSC
N412242208CD	\$694.00	24.00 x 22.00 x 8.89 [610 x 559 x 226]	NP2420C	NP2420CG	NP2420SSC
N412242608CD	\$716.00	24.00 x 26.00 x 8.89 [610 x 660 x 226]	NP2424C	NP2424CG	NP2424SSC
N412302608CD	\$779.00	30.00 x 26.00 x 8.89 [762 x 660 x 226]	NP3024C	NP3024CG	NP3024SSC
N412362608CD	\$876.00	36.00 x 26.00 x 8.89 [914 x 660 x 226]	NP3624C	NP3624CG	NP3624SSC
N412363208CD	\$1,011.00	36.00 x 32.00 x 8.89 [914 x 813 x 226]	NP3630C	NP3630CG	NP3630SSC
N412423212CD	\$1,089.00	42.00 x 32.00 x 12.89 [1067 x 813 x 327]	NP4230C	—	—
N412423812CD	\$1,190.00	42.00 x 38.00 x 12.89 [1067 x 965 x 327]	NP4236C	NP4236CG	NP4236SSC
N412483812CD	\$1,284.00	48.00 x 38.00 x 12.89 [1219 x 965 x 327]	NP4836C	NP4836CG	NP4836SSC
N412603812CD	\$1,472.00	60.00 x 38.00 x 12.89 [1524 x 965 x 327]	NP6036C	NP6036CG	NP6036SSC

Notes: Subpanels must be ordered separately.
Dimensions in inches [millimeters].
Letters in table correspond to letters on dimensional drawings.

NEMA 4, 4X, 12, and 13 Ultimate Series Single-Door Wall-Mount Right-Flanged Disconnect



Construction

- Stainless Steel
- CDSS enclosures have 14-gauge 304 stainless steel bodies and doors
- CDSSA enclosures have 14-gauge 316L stainless steel bodies and doors
- Large tub opening for better access
- Concealed hinges
- Interchangeable and easily removable doors
- Ground stud located in door
- Doors sealed with poured-in-place polyurethane gasket
- Mounting holes in rear
- Studs for mounting optional subpanel
- Door latching system installed on door with a slotted insert defeater mechanism
- Latching system interlocks with the disconnect handle (not included) for added safety

Finish

- Cover and outside of enclosure have a #3 intermediate polished Finish
- Painted steel subpanels are white polyester powder over phosphatized surfaces
- Galvanized and stainless steel subpanels are a conductive finish (unpainted)

Listings

- UL 508 4, 4X, 12, and 13[UL File E64791]
- NEMA/EEMAC 4, 4X, 12, and 13



Notes: Disconnect switch or circuit breakers, operating handle, operating mechanism must be ordered separately.

Operator adapter plates are not required with this enclosure series.

Make sure the disconnect device you are using will fit the enclosure size you choose.

NEMA 4, 4X, 12, and 13 Ultimate Series Single-Door Wall-Mount Right-Flanged Disconnect



Shipping Schedule

Same day 1 - 5 days 1 - 7 days 1-10 days 1 - 15 days 1 - 20 days

Color indicates shipping lead time in business days.

Ultimate Series Single-Door Wall-Mount 304 Stainless Steel Disconnect

Part Number	Price	Enclosure Size HxWxD	Painted Steel Subpanel	Galvanized Subpanel	Stainless Steel Subpanel
<u>N412202208CDSS</u>	Retired	20.00 x 22.00 x 8.87 [508 x 559 x 225]	<u>NP2020C</u>	<u>NP2020CG</u>	<u>NP2020SSC</u>
<u>N412242208CDSS</u>	\$1,579.00	24.00 x 22.00 x 8.87 [610 x 559 x 225]	<u>NP2420C</u>	<u>NP2420CG</u>	<u>NP2420SSC</u>
<u>N412242608CDSS</u>	Retired	24.00 x 26.00 x 8.89 [610 x 660 x 226]	<u>NP2424C</u>	<u>NP2424CG</u>	<u>NP2424SSC</u>
<u>N412302608CDSS</u>	Retired	30.00 x 26.00 x 8.89 [762 x 660 x 226]	<u>NP3024C</u>	<u>NP3024CG</u>	<u>NP3024SSC</u>
<u>N412362608CDSS</u>	\$1,750.00	36.00 x 26.00 x 8.89 [914 x 660 x 226]	<u>NP3624C</u>	<u>NP3624CG</u>	<u>NP3624SSC</u>
<u>N412363208CDSS</u>	Retired	36.00 x 32.00 x 8.89 [914 x 813 x 226]	<u>NP3630C</u>	<u>NP3630CG</u>	<u>NP3630SSC</u>
<u>N412423212CDSS</u>	Retired	42.00 x 32.00 x 12.88 [1067 x 813 x 327]	<u>NP4230C</u>	—	—
<u>N412423812CDSS</u>	\$2,777.00	42.00 x 38.00 x 12.88 [1067 x 965 x 327]	<u>NP4236C</u>	<u>NP4236CG</u>	<u>NP4236SSC</u>
<u>N412483812CDSS</u>	Retired	48.00 x 38.00 x 12.88 [1219 x 965 x 327]	<u>NP4836C</u>	<u>NP4836CG</u>	<u>NP4836SSC</u>
<u>N412603812CDSS</u>	Retired	60.00 x 38.00 x 12.88 [1524 x 965 x 327]	<u>NP6036C</u>	<u>NP6036CG</u>	<u>NP6036SSC</u>

Notes: Subpanels must be ordered separately.
Dimensions in inches [millimeters]

Ultimate Series Single-Door Wall-Mount 316L Stainless Steel Disconnect


Part Number	Price	Enclosure Size HxWxD	Painted Steel Subpanel	Galvanized Subpanel	Stainless Steel Subpanel
<u>N412202208CDSSA</u>	\$1,764.00	20.00 x 22.00 x 8.87 [508 x 559 x 225]	<u>NP2020C</u>	<u>NP2020CG</u>	<u>NP2020SSC</u>
<u>N412242208CDSSA</u>	Retired	24.00 x 22.00 x 8.87 [610 x 559 x 225]	<u>NP2420C</u>	<u>NP2420CG</u>	<u>NP2420SSC</u>
<u>N412242608CDSSA</u>	Retired	24.00 x 26.00 x 8.89 [610 x 660 x 226]	<u>NP2424C</u>	<u>NP2424CG</u>	<u>NP2424SSC</u>
<u>N412302608CDSSA</u>	\$2,151.00	30.00 x 26.00 x 8.89 [762 x 660 x 226]	<u>NP3024C</u>	<u>NP3024CG</u>	<u>NP3024SSC</u>
<u>N412362608CDSSA</u>	Retired	36.00 x 26.00 x 8.89 [914 x 660 x 226]	<u>NP3624C</u>	<u>NP3624CG</u>	<u>NP3624SSC</u>
<u>N412363208CDSSA</u>	Retired	36.00 x 32.00 x 8.89 [914 x 813 x 226]	<u>NP3630C</u>	<u>NP3630CG</u>	<u>NP3630SSC</u>
<u>N412423212CDSSA</u>	\$3,242.00	42.00 x 32.00 x 12.88 [1067 x 813 x 327]	<u>NP4230C</u>	—	—
<u>N412423812CDSSA</u>	Retired	42.00 x 38.00 x 12.88 [1067 x 965 x 327]	<u>NP4236C</u>	<u>NP4236CG</u>	<u>NP4236SSC</u>
<u>N412483812CDSSA</u>	Retired	48.00 x 38.00 x 12.88 [1219 x 965 x 327]	<u>NP4836C</u>	<u>NP4836CG</u>	<u>NP4836SSC</u>
<u>N412603812CDSSA</u>	\$3,849.00	60.00 x 38.00 x 12.88 [1524 x 965 x 327]	<u>NP6036C</u>	<u>NP6036CG</u>	<u>NP6036SSC</u>

Notes: Subpanels must be ordered separately.
Dimensions in inches [millimeters].
Letters in table correspond to letters on dimensional drawings.

NEMA 4, 4X, 12, and 13 Ultimate Series Single-Door Wall-Mount Right-Flanged Disconnect



Dimensions



NEMA 4, 12, and 13 Ultimate Series Single-Door Wall-Mount Slope-Top Right-Flanged Disconnect



Construction

- CD enclosures have 14-gauge carbon steel bodies and doors
- Large tub opening for better access
- Concealed hinges
- Interchangeable and easily removable doors
- Ground stud located in door
- Doors sealed with poured-in-place polyurethane gasket
- Mounting holes in rear
- Studs for mounting optional subpanel
- Door latching system installed on door with a slotted insert defeater mechanism
- Latching system interlocks with the disconnect handle (not included) for added safety
- 20° sloped top

Finish

- ANSI 61 gray polyester powder inside and out over phosphatized surfaces
- Painted steel subpanels are white polyester powder over phosphatized surfaces
- Galvanized and stainless steel subpanels are a conductive finish (unpainted)

Listings

- UL 508 4, 12, and 13 [UL File E64791]
- NEMA/EEMAC 4, 12, and 13



Notes: Disconnect switch or circuit breakers, operating handle, operating mechanism must be ordered separately.
Operator adapter plates are not required with this enclosure series.
Make sure the disconnect device you are using will fit the enclosure size you choose.

Shipping Schedule

Same day	1 - 5 days	1 - 7 days	1 - 15 days	1 - 20 days
----------	------------	------------	-------------	-------------

Color indicates shipping lead time in business days.

NEMA 4, 12, and 13 Ultimate Series Single-Door Wall-Mount Slope-Top Right-Flanged Disconnect

Part Number	Price	Enclosure Size HxWxD	Painted Steel Subpanel	Galvanized Subpanel	Stainless Steel Subpanel
<u>N412202208CSTD</u>	Retired	23.36 x 22.00 x 8.89 [593 x 559 x 226]	<u>NP2020C</u>	<u>NP2020CG</u>	<u>NP2020SSC</u>
<u>N412242208CSTD</u>	Retired	27.36 x 22.00 x 8.89 [695 x 559 x 226]	<u>NP2420C</u>	<u>NP2420CG</u>	<u>NP2420SSC</u>
<u>N412242608CSTD</u>	Retired	27.35 x 26.00 x 8.89 [695 x 660 x 226]	<u>NP2424C</u>	<u>NP2424CG</u>	<u>NP2424SSC</u>
<u>N412302608CSTD</u>	Retired	33.36 x 26.00 x 8.89 [847 x 660 x 226]	<u>NP3024C</u>	<u>NP3024CG</u>	<u>NP3024SSC</u>
<u>N412363210CSTD</u>	Retired	40.09 x 32.00 x 10.89 [1018 x 813 x 277]	<u>NP3630C</u>	<u>NP3630CG</u>	<u>NP3630SSC</u>
<u>N412423212CSTD</u>	Retired	46.87 x 32.00 x 12.89 [1190 x 813 x 327]	<u>NP4230C</u>	—	—
<u>N412483812CSTD</u>	Retired	52.87 x 38.00 x 12.89 [1343 x 965 x 327]	<u>NP4836C</u>	<u>NP4836CG</u>	<u>NP4836SSC</u>
<u>N412603812CSTD</u>	Retired	64.87 x 38.00 x 12.89 [1648 x 965 x 327]	<u>NP6036C</u>	<u>NP6036CG</u>	<u>NP6036SSC</u>

Notes: Subpanels must be ordered separately.
Dimensions in inches [millimeters].
Letters in table correspond to letters on dimensional drawings.

NEMA 4, 4X, 12, and 13 Ultimate Series Stainless Steel Single-Door Wall-Mount Slope-Top Disconnect



Construction

- CD enclosures have 14-gauge 304 stainless steel bodies and doors
- Large tub opening for better access
- Concealed hinges
- Interchangeable and easily removable doors
- Ground stud located in door
- Doors sealed with poured-in-place polyurethane gasket
- Mounting holes in rear
- Studs for mounting optional subpanel
- Door latching system installed on door with a slotted insert defeater mechanism
- Latching system interlocks with the disconnect handle (not included) for added safety
- 20° sloped top

Finish

- Cover and outside enclosure have #3 intermediate polished finish
- Painted steel subpanels are white polyester powder over phosphatized surfaces
- Galvanized and stainless steel subpanels are a conductive finish (unpainted)

Listings

- UL 508 4, 4X, 12, and 13[UL File E64791]
- NEMA/EEMAC 4, 4X, 12, and 13



Notes: Disconnect switch or circuit breakers, operating handle, operating mechanism must be ordered separately.
Operator adapter plates are not required with this enclosure series.
Make sure the disconnect device you are using will fit the enclosure size you choose.

Shipping Schedule

Same day	1 - 5 days	1 - 7 days	1 - 15 days	1 - 20 days
----------	------------	------------	-------------	-------------

Color indicates shipping lead time in business days.

NEMA 4, 4X, 12, and 13 Ultimate Single-Door Wall-Mount Slope-Top Disconnect

Part Number	Price	Enclosure Size HxWxD	Painted Steel Subpanel	Galvanized Subpanel	Stainless Steel Subpanel
N412242608CSSSTD	\$1,434.00	27.35 x 26.00 x 8.89 [695 x 660 x 226]	NP2424C	NP2424CG	NP2424SSC
N412302608CSSSTD	\$1,693.00	33.36 x 26.00 x 8.89 [847 x 660 x 226]	NP3024C	NP3024CG	NP3024SSC
N412363208CSSSTD	\$2,495.00	39.36 x 32.00 x 8.89 [1000 x 813 x 226]	NP3630C	NP3630CG	NP3630SSC
N412483816CSSSTD	\$4,429.00	54.32 x 38.00 x 16.89 [1380 x 965 x 429]	NP4836C	NP4836CG	NP4836SSC
N412603816CSSSTD	\$5,637.00	66.32 x 38.00 x 16.89 [1685 x 965 x 429]	NP6036C	NP6036CG	NP6036SSC



Notes: Subpanels must be ordered separately.
Dimensions in inches [millimeters].

Letters in table correspond to letters on dimensional drawings.

Ultimate Series Single-Door Wall-Mount Slope-Top Disconnect



Dimensions



NEMA 12 and 13 Single-Door Wall-Mount Right-Flanged Disconnect with Handle



Construction

- 14-gauge steel bodies and doors
- Plasma welded seams
- Rolled lip around all sides of opening keeps out liquids and contaminants
- Remove doors easily by pulling continuous hinge pin
- Polyurethane poured-in-place gasket
- External mounting feet
- Collar studs for mounting optional subpanel
- Ground stud in door
- Instructions provided for locating and installing disconnect switches, circuit breakers and operating mechanisms
- Enclosures provided with padlocking, defeater handle and latching system

Finish


- ANSI 61 gray polyester powder inside and out over phosphatized surfaces
- Painted steel and perforated subpanels white polyester powder over phosphatized surfaces
- Galvanized panels are a conductive finish (unpainted)

Listings

- UL 508 12 and 13 [UL File E64791]
- NEMA/EEMAC 12 and 13



Dimensions



Notes: Disconnect switch or circuit breakers, operating handle, operating mechanism must be ordered separately.

Operator adapter plates are not required with this enclosure series.

4.50in [114mm] Handle and latching hardware are included.

Make sure the disconnect device you are using will fit the enclosure size you choose.

NOTES:

1. SUBPANELS ARE MADE FROM 12 GA STEEL.
2. SUBPANELS HAVE FLANGES ALONG ALL SIDES WHEN EITHER DIMENSION EXCEEDS 17".
3. CATALOG NUMBER SDN12603812A HAS A LARGER CUTOUT IN THE ENCLOSURE FLANGE TO ACCOMMODATE ALLEN-BRADLEY 1494V-H2 AND I-T-E FHOHN OPERATING HANDLES.

NEMA 12 and 13 Single-Door Wall-Mount Right-Flanged Disconnect with Handle

Shipping Schedule

Same day 1 - 5 days 1 - 7 days 1 - 10 days 1 - 15 days 1 - 20 days

Color indicates shipping lead time in business days.



NEMA 12 and 13 Single-Door Wall-Mount Right-Flanged Disconnect with Handle

Part Number	Price	Enclosure Size HxWxD	Painted Steel Subpanel	Galvanized Subpanel	Perforated Subpanel	Stainless Steel Subpanel
SDN12202108PL	\$652.00	20.00 x 21.38 x 8.88 [508 x 543 x 226]	NP2020	NP2020G	NP2020PP	NP2020SS
SDN12202110PL	Retired	20.00 x 21.38 x 10.88 [508 x 543 x 276]	NP2020	NP2020G	NP2020PP	NP2020SS
SDN12242108PL	\$692.00	24.00 x 21.38 x 8.88 [610 x 543 x 226]	NP2420	NP2420G	NP2420PP	NP2420SS
SDN12242110PL	Retired	24.00 x 21.38 x 10.88 [610 x 543 x 276]	NP2420	NP2420G	NP2420PP	NP2420SS
SDN12242508PL	Retired	24.00 x 25.38 x 8.88 [610 x 645 x 226]	NP2424	NP2424G	NP2424PP	NP2420SS
SDN12242510PL	\$771.00	24.00 x 25.38 x 10.88 [610 x 645 x 276]	NP2424	NP2424G	NP2424PP	NP2420SS
SDN12302108PL	Retired	30.00 x 21.38 x 8.88 [762 x 543 x 226]	NP3020	NP3020G	—	NP3020SS
SDN12302110PL	Retired	30.00 x 21.38 x 10.88 [762 x 543 x 276]	NP3020	NP3020G	—	NP3020SS
SDN12302508PL	Retired	30.00 x 25.38 x 8.88 [762 x 645 x 226]	NP3024	NP3024G	NP3024PP	NP3024SS
SDN12302510PL	\$843.00	30.00 x 25.38 x 10.88 [762 x 645 x 276]	NP3024	NP3024G	NP3024PP	NP3024SS
SDN12302612PL	\$882.00	30.00 x 25.38 x 12.88 [762 x 645 x 327]	NP3024	NP3024G	NP3024PP	NP3024SS
SDN12362508PL	\$881.00	36.00 x 25.38 x 8.88 [914 x 645 x 226]	NP3624	NP3624G	NP3624PP	NP3624SS
SDN12362510PL	\$929.00	36.00 x 25.38 x 10.88 [914 x 645 x 276]	NP3624	NP3624G	NP3624PP	NP3624SS
SDN12363108PL	\$966.00	36.00 x 31.38 x 8.88 [914 x 797 x 226]	NP3630	NP3630G	NP3630PP	NP3630SS
SDN12363110PL	Retired	36.00 x 31.38 x 10.88 [914 x 797 x 276]	NP3630	NP3630G	NP3630PP	NP3630SS
SDN12363116PL	Retired	36.00 x 31.37 x 16.88 [914 x 797 x 429]	NP3630	NP3630G	NP3630PP	NP3630SS
SDN12363212PL	\$1,060.00	36.00 x 31.37 x 12.88 [914 x 797 x 327]	NP3630	NP3630G	NP3630PP	NP3630SS
SDN12423108PL	\$1,047.00	42.00 x 31.38 x 8.88 [1067 x 797 x 226]	NP4230	NP4230G	NP4230PP	NP4230SS
SDN12423110PL	\$1,096.00	42.00 x 31.38 x 10.88 [1067 x 797 x 276]	NP4230	NP4230G	NP4230PP	NP4230SS
SDN12423212PL	Retired	42.00 x 31.38 x 12.88 [1067 x 797 x 327]	NP4230	NP4230G	NP4230PP	NP4230SS
SDN12423708PL	\$1,107.00	42.00 x 37.37 x 8.88 [1067 x 949 x 226]	NP4236	NP4236G	NP4236PP	NP4236SS
SDN12423710PL	Retired	42.00 x 37.37 x 10.88 [1067 x 949 x 276]	NP4236	NP4236G	NP4236PP	NP4236SS
SDN12423812PL	\$1,265.00	42.00 x 37.37 x 12.88 [1067 x 949 x 327]	NP4236	NP4236G	NP4236PP	NP4236SS
SDN12483708PL**	Retired	48.00 x 37.37 x 8.88 [1219 x 949 x 226]	NP4836	NP4836G	NP4836PP	NP4836SS
SDN12483710PL**	\$1,307.00	48.00 x 37.38 x 10.88 [1219 x 949 x 276]	NP4836	NP4836G	NP4836PP	NP4836SS
SDN12483812PL**	\$1,369.00	48.00 x 37.38 x 12.88 [1219 x 949 x 327]	NP4836	NP4836G	NP4836PP	NP4836SS
SDN12483816PL**	\$1,490.00	48.00 x 37.38 x 16.88 [1219 x 949 x 429]	NP4836	NP4836G	NP4836PP	NP4836SS
SDN12603710PL**	\$1,435.00	60.00 x 37.38 x 10.88 [1524 x 949 x 276]	NP6036	NP6036G	NP6036PP	NP6036SS
SDN12603808PL**	\$1,480.00	60.00 x 37.38 x 8.88 [1524 x 949 x 226]	NP6036	NP6036G	NP6036PP	NP6036SS
SDN12603812PL**	\$1,572.00	60.00 x 37.38 x 12.88 [1524 x 949 x 327]	NP6036	NP6036G	NP6036PP	NP6036SS
SDN12603816PL**	Retired	60.00 x 37.38 x 16.88 [1524 x 949 x 429]	NP6036	NP6036G	NP6036PP	NP6036SS

Note: Subpanels must be ordered separately.

Dimensions in inches [millimeters].

**These enclosures have a closed-cell neoprene gasket, not poured-in-place.

Note: Enclosures 12 in [305 mm] and 16 in [152 mm] deep can be modified to accept I-T-E Siemens 800 amp and 1200 amp circuit breakers. (When using an I-T-E Siemens circuit breaker and an enclosure with an "H" dimension of 30", 36 in [914 mm] or 42 in [1067 mm], verify the amount of wire bend space required for both the line and load sides.)

NEMA 4, 12, and 13 Single-Door Wall-Mount Right-Flanged Disconnect



Construction

- 14-gauge steel bodies and doors
- Plasma welded seams
- Rolled lip around all sides of opening keeps out liquids and contaminants
- Stainless steel exterior hardware
- Stainless steel door clamps around three sides of doors for a watertight seal; no additional door hardware required
- Remove doors easily by pulling continuous hinge pin
- Polyurethane poured-in-place gasket
- External mounting feet
- Collar studs for mounting optional subpanel
- Grounding provisions provided
- Bracket welded to door for attaching disconnect interlock door catch
- Holes in body for mounting disconnect operating handle and operating mechanism. These enclosures are designed to operate properly without the use of door hardware



Listings

- UL 508 4, 12, and 13 [UL File E64791]
- NEMA/EEMAC 3, 4, 12, and 13



Notes: Disconnect switch or circuit breakers, operating handle, operating mechanism must be ordered separately.

Operator adapter plates are not required with this enclosure series.

Make sure the disconnect device you are using will fit the enclosure size you choose.

Finish

- ANSI 61 gray polyester powder inside and out over phosphatized surfaces
- Painted steel and perforated subpanels white polyester powder over phosphatized surfaces
- Galvanized and stainless steel subpanels are a conductive finish (unpainted)

Shipping Schedule

Same day 1 - 5 days 1 - 7 days 1 - 15 days 1 - 20 days

Color indicates shipping lead time in business days.

NEMA 4, 12, and 13 Single-Door Wall-Mount Right-Flanged Disconnect

Part Number	PriceCode	Enclosure Size HxWxD	Painted Steel Subpanel	Galvanized Subpanel	Perforated Subpanel	Stainless Steel Subpanel
SN4242108	Retired	24.00 x 21.38 x 8.97 [610 x 543 x 228]	NP2420	NP2420G	NP2420PP	NP2420SS
SN4242508	Retired	24.00 x 25.38 x 8.97 [610 x 645 x 228]	NP2420	NP2424G	NP2424PP	NP2424SS
SN4302508	Retired	30.00 x 25.38 x 8.97 [762 x 645 x 228]	NP3024	NP3024G	NP3024PP	NP3024SS
SN4363108	Retired	36.00 x 31.38 x 8.97 [914 x 797 x 228]	NP3630	NP3630G	NP3630PP	NP3630SS
SN4423112	Retired	42.00 x 31.38 x 12.97 [1067 x 797 x 329]	NP4230	NP4230G	NP4230PP	NP4230SS
SN4423712	Retired	42.00 x 37.37 x 12.97 [1067 x 949 x 329]	NP4236	NP4236G	NP4236PP	NP4236SS
SN4483712**	Retired	48.00 x 37.38 x 12.97 [1219 x 949 x 329]	NP4836	NP4836G	NP4836PP	NP4836SS
SN4603712**	Retired	60.00 x 37.38 x 12.97 [1524 x 949 x 329]	NP6036	NP6036G	NP6036PP	NP6036SS

Notes: Subpanels must be ordered separately.

Dimensions in inches [millimeters].


Letters in table correspond to letters on dimensional drawings.

**These enclosures have a closed-cell neoprene gasket, not poured-in-place.

NEMA 4, 12, and 13 Single-Door Wall-Mount Right-Flanged Disconnect



Dimensions



NOTES:

1. SUBPANELS ARE MADE FROM 12 GA. STEEL.
2. SUBPANELS HAVE FLANGES ALONG ALL SIDES WHEN EITHER DIMENSION EXCEEDS 17".

NEMA 12 and 13 Single-Door Wall-Mount Right-Flanged Disconnect for Allen-Bradley 1494D and 1494F



Applications

Designed to house Allen-Bradley 1494F flange-mounted disconnect switches and Bulletin 1494D flange-mounted operators for circuit breakers. Provides protection from dust, dirt, oil and water.

Door hardware (Bulletin 1494F-L1 for 2-point latching (enclosures under 40 in [1016 mm] high), or Bulletins 1494F-L2 and 1494F-L3 for 3-point latching (enclosures over 40 in [1016 mm] high).



Construction

- 14-gauge steel bodies and doors
- Rolled lip around all sides of opening keeps out liquids and contaminants
- Remove doors easily by pulling continuous hinge pin
- Polyurethane poured-in-place gasket
- External mounting feet
- Collar studs for mounting optional subpanel
- Grounding provisions provided
- Guide brackets and door catch welded to inside of door
- Locking bars for door hardware
- Spacers and screws to secure disconnect switch and fuse block adapter plate to panel
- Enclosures under 40 in [1016 mm] high require 2-point door hardware
- Enclosures 40 in [1016 mm] high and larger require 3-point door hardware
- Instructions to locate and install disconnect switches, circuit breakers, and operating mechanisms included

Finish

- ANSI 61 gray polyester powder inside and out over phosphatized surfaces
- Painted steel and perforated subpanels white polyester powder over phosphatized surfaces
- Galvanized and stainless steel subpanels are a conductive finish (unpainted)

Listings

- UL 508 12 and 13 [UL File E64791]
- NEMA/EEMAC 12 and 13



Notes: Disconnect switch or circuit breakers, operating handle, operating mechanism must be ordered separately.

Operator adapter plates are not required with this enclosure series.

Make sure the disconnect device you are using will fit the enclosure size you choose.

Shipping Schedule

Same day 1 - 5 days 1 - 7 days 1-10 days 1 - 15 days 1 - 20 days

Color indicates shipping lead time in business days.

NEMA 12 and 13 Single-Door Wall-Mount Right-Flanged Disconnect for Allen-Bradley 1494D and 1494F

Part Number	Price	Enclosure Size HxWxD	Painted Steel Subpanel	Galvanized Subpanel	Perforated Subpanel	Stainless Steel Subpanel
ABN12242108	Retired	24.00 x 21.38 x 8.85 [610 x 543 x 225]	NP2420	NP2420G	NP2420PP	NP2420SS
ABN12242508	Retired	24.00 x 25.38 x 8.85 [610 x 645 x 225]	NP2424	NP2424G	NP2424PP	NP2424SS
ABN12302108	Retired	30.00 x 21.38 x 8.85 [762 x 543 x 225]	NP3020	NP3020G	—	NP3020SS
ABN12302508	Retired	30.00 x 25.38 x 8.85 [762 x 645 x 225]	NP3024	NP3024G	NP3024PP	NP3024SS
ABN12362510	Retired	36.00 x 25.38 x 10.85 [914 x 645 x 276]	NP3624	NP3624G	NP3624PP	NP3624SS
ABN12363108	Retired	36.00 x 31.38 x 8.85 [914 x 797 x 225]	NP3630	NP3630G	NP3630PP	NP3630SS
ABN12363110	Retired	36.00 x 31.38 x 10.85 [914 x 797 x 276]	NP3630	NP3630G	NP3630PP	NP3630SS
ABN12423108	Retired	42.00 x 31.38 x 8.85 [1067 x 797 x 225]	NP4230	NP4230G	NP4230PP	NP4230SS
ABN12483710*	Retired	48.00 x 37.38 x 10.85 [1219 x 949 x 276]	NP4836	NP4836G	NP4836PP	NP4836SS
ABN12483812*	Retired	48.00 x 37.38 x 12.85 [1219 x 949 x 326]	NP4836	NP4836G	NP4836PP	NP4836SS
ABN12603710*	Retired	60.00 x 37.38 x 10.85 [1524 x 949 x 276]	NP6036	NP6036G	NP6036PP	NP6036SS

Notes: Subpanels must be ordered separately. Dimensions in inches [millimeters].


Letters in table correspond to letters on dimensional drawings.

*These enclosures have a closed-cell neoprene gasket, not poured-in-place.

NEMA 12 and 13 Single-Door Wall-Mount Right-Flanged Disconnect for Allen-Bradley 1494D and 1494F



Dimensions



NOTES:

1. SUBPANELS ARE MADE FROM 12 GA. STEEL.
2. SUBPANELS HAVE FLANGES ALONG ALL SIDES WHEN EITHER DIMENSION EXCEEDS 17".
3. ENCLOSURES UNDER 40.00" HIGH REQUIRE 2-POINT HARDWARE, ENCLOSURES 40.00" AND HIGHER REQUIRE 3-POINT DOOR HARDWARE.

NEMA 4, 4X, 12, and 13 Single-Door Wall-Mount Right-Flanged Disconnect



Construction

- 14-gauge 304 or 316L stainless steel bodies and doors
- Continuously-welded seams ground smooth
- Rolled lip around all sides of opening keeps out liquids and contaminants
- All stainless steel exterior hardware
- All stainless steel interior and exterior
- Stainless steel door clamps around three sides of doors for a watertight seal; additional door hardware is not required
- Doors removed by pulling stainless steel continuous hinge pin
- Polyurethane poured-in-place gasket
- External mounting feet
- Collar studs for mounting optional subpanel
- Grounding provisions provided
- Bracket welded to door for attaching disconnect interlock door catch
- Holes in body for mounting disconnect operating handle and operating mechanism. These enclosures are designed to operate properly without the use of door hardware

Finish

- Enclosures have a #3 intermediate polished finish on all external surfaces
- Painted steel and perforated subpanels white polyester powder over phosphatized surfaces
- Galvanized and stainless subpanels are a conductive finish (unpainted)

Listings

- UL 508 4, 4X, 12, and 13 [UL File E64791]
- NEMA/EEMAC 4, 4X, 12, and 13



Notes: Disconnect switch or circuit breakers, operating handle, operating mechanism must be ordered separately. Operator adapter plates are not required with this enclosure series. Make sure the disconnect device you are using will fit the enclosure size you choose.

Shipping Schedule

Same day 1 - 5 days 1 - 7 days 1-10 days 1 - 15 days 1 - 20 days

Color indicates shipping lead time in business days.

NEMA 4, 4X, 12, and 13 Single-Door Wall-Mount Right-Flanged Disconnect

304 Stainless Steel	Price	316L Stainless Steel	Price	Enclosure Size HxWxD	Painted Steel Subpanel	Galvanized Subpanel	Perforated Subpanel	Stainless Steel Subpanel
SSN4X242108	Retired	SSN4X242108A	Retired	24.00 x 21.38 x 8.97 [610 x 543 x 228]	NP2420	NP2420G	NP2420PP	NP2420SS
SSN4X242508	Retired	SSN4X242508A	Retired	24.00 x 25.38 x 8.97 [610 x 645 x 228]	NP2424	NP2424G	NP2424PP	NP2424SS
SSN4X302508	Retired	SSN4X302508A	Retired	30.00 x 25.37 x 9.18 [762 x 644 x 233]	NP3024	NP3024G	NP3024PP	NP3024SS
SSN4X362508	Retired	SSN4X362508A	Retired	36.00 x 25.37 x 9.18 [914 x 644 x 233]	NP3624	NP3624G	NP3624PP	NP3624SS
SSN4X363108	Retired	SSN4X363108A	Retired	36.00 x 31.37 x 9.18 [914 x 797 x 233]	NP3630	NP3630G	NP3630PP	NP3630SS
SSN4X423112	Retired	SSN4X423112A	Retired	42.00 x 31.37 x 13.18 [1067 x 797 x 335]	NP4230	NP4230G	NP4230PP	NP4230SS
SSN4X423712	Retired	SSN4X423712A	Retired	42.00 x 37.37 x 13.18 [1067 x 949 x 335]	NP4236	NP4236G	NP4236PP	NP4236SS
SSN4X483712	Retired	SSN4X483712A	Retired	48.00 x 37.38 x 13.18 [1219 x 949 x 335]	NP4836	NP4836G	NP4836PP	NP4836SS
SSN4X603712	Retired	SSN4X603712A	Retired	60.00 x 37.38 x 13.18 [1524 x 949 x 335]	NP6036	NP6036G	NP6036PP	NP6036SS

Notes: Subpanels must be ordered separately.


Dimensions in inches [millimeters].

Letters in table correspond to letters on dimensional drawings.

NEMA 4, 4X, 12, and 13 Single-Door Wall-Mount Right-Flanged Disconnect



Dimensions



NOTES:

1. SUBPANELS ARE MADE FROM 12 GA. STEEL.
2. SUBPANELS HAVE FLANGES ALONG ALL SIDES WHEN EITHER DIMENSION EXCEEDS 17".

KwikHinge™ Series NEMA 3R, 4, and 12 Freestanding Single- and Two-Door Disconnect



WRD72XM2718FS4

Applications

Designed to house and protect electrical and electronic controls, components and instruments in typical industrial environments. Enclosures protect equipment from dust, dirt, and water. These enclosures are used in machine tool applications for housing motor starters, drives, and contactors, PLCs, as well as a wide variety of other electrical and electronic equipment. The addition of 19 in [483 mm] rack-mounted accessories make these enclosures ideal for providing rugged protection for sensitive rack-mounted components in harsh industrial environments.

Finish

- ANSI 61 gray light-textured polyester powder coat, interior and exterior

Listings

- cULus File E64791
- IEC 60529, IP66
- UL 508A 3R, 4, and 12
- Meets NEMA/EEMAC 3R, 4, and 12 requirements




Note: For current listings, please see www.automationdirect.com

Construction

- Bodies and doors fabricated from carbon steel
- KwikHinge™ heavy-duty 316 stainless steel sliding hinge pins
- Continuous welded seams, ground smooth
- Removable heavy-duty lifting eyes for easy handling
- Door opens 170°
- Door sealed with Polyurethane poured-in-place gasket
- Subpanel included
- Uni-strut mounting channels welded horizontally to interior body sides to allow subpanels to be positioned in enclosure. Optional swing, half, full panels and rack angles can be mounted anywhere along the uni-strut channel
- 3-point keylocking/padlocking handle included
- Uses WAL4 series handles and WAEMK4A replacement key



WRD72XM5318FSD4



KwikHinge™ Series NEMA 3R, 4, and 12 Freestanding Single- and Two-Door Disconnect



Shipping Schedule

Same day 1 - 5 days 1 - 7 days 1 - 15 days 1 - 20 days


Color indicates shipping lead time in business days.

KwikHinge™ Series NEMA 3R, 4, and 12 Freestanding Single- and Two-Door Disconnect

Part Number	Price	Enclosure Size HxWxD	Number of Hinges per Door
Single-Door			
WRD72XM2718FS4	Retired	72.13 x 27.50 x 19.29 [1832 x 699 x 490]	4
WRD72XM3318FS4	Retired	72.13 x 33.50 x 19.29 [1832 x 851 x 490]	4
WRD72XM3918FS4	\$3,344.00	72.13 x 39.50 x 19.29 [1832 x 1003 x 490]	4
WRD84XM3918FS4	Retired	84.13 x 39.50 x 19.29 [2137 x 1003 x 490]	5
WRD90XM3920FS4	Retired	90.13 x 39.50 x 21.29 [2289 x 1003 x 541]	5
WRD90XM3924FS4	Retired	90.13 x 39.50 x 25.29 [2289 x 1003 x 642]	5
Two-Door			
WRD72XM5318FSD4	\$4,551.00	72.13 x 53.50 x 19.29 [1832 x 1359 x 490]	4
WRD72XM6518FSD4	Retired	72.13 x 66.50 x 19.29 [1832 x 1689 x 490]	4
WRD72XM7718FSD4	Retired	72.13 x 78.50 x 19.29 [1832 x 1994 x 490]	4
WRD72XM7724FSD4	\$6,127.00	72.13 x 78.50 x 25.29 [1832 x 1994 x 642]	4
WRD84XM7718FSD4	Retired	84.13 x 78.50 x 19.29 [2137 x 1994 x 490]	5
WRD90XM7720FSD4	Retired	90.13 x 78.50 x 21.29 [2289 x 1994 x 541]	5
WRD90XM7724FSD4	Retired	90.13 x 78.50 x 25.29 [2289 x 1994 x 642]	5

Note: Dimensions in inches [millimeters].


Dimensions



KwikHinge™ Series NEMA 3R, 4, and 12 Freestanding Single- and Two-Door Disconnect



Dimensions



Disconnect Handle Applications for Freestanding and Floor-Mount Painted Steel Disconnect Enclosures

Designed to house the following available at AutomationDirect.com

- AutomationDirect.com NEMA 1/12 Flexible shaft handle for Molded Case Circuit Breakers (MCCBs). Series F_SO_C flex handle mechanisms are available in four sizes to actuate all AutomationDirect MCCBs from 15 amps up to 600 amps. **F0S03C, F0S06C, F1S03C, F1S06C, F3S03C, F3S06C, F4S04C, and F4S06C**
- Socomec Disconnect switches with cable, flange-mounted cable operator and handles. Handles **37299002** and **37299003**, cable operator **37299903**, and cables **37299992** (3ft) or **37299993** (5ft)
- Fuji Electric NEMA 12 flexible shaft handle for Molded Case Circuit Breakers (MCCBs). Series BW9F flex handle mechanisms are available in four sizes to actuate all Fuji Electric MCCBs from 15 Amps to 800 Amps. **BW9F0CA-15A, BW9F0CA-20A, BW9F0GA-15A, BW9F0GA-20A, BW9F0HA-15A, BW9F0HA-20A, BW9F0JA-15A, and BW9F0JA-20A.**
- Gladiator Molded Case Circuit Breakers (MCCBs) flange mounted cable operator and handles. See Gladiator sections for handles and cable options. **GCBX1-FHC-N3R4-M, GCBX1-FHC-N4X-M, GCBX5-FHC-N3R4-M, and GCBX5-FHC-N4X-M**

Available at AutomationDirect.com				
Disconnect Enclosure Series	AutomationDirect F_SO_C Series	Socomec 37299002 and 37299003	Fuji BW9F Series	Gladiator GCBX
WAX_U Series	✓	✓	✓	✓
adapter plate required	WA21CHVA	WA21SDA	WA21FUFA	WA21SDA
WACPX_U Series	✓	✓	✓	✓
adapter plate required	WA21CHVA	WA21SDA	WA21FUFA	WA21SDA
WAXM_U Series	✓	✓	✓	✓
adapter plate required	WA21CHVA	WA21SDA	WA21FUFA	WA21SDA

Designed to house other brands

- Allen-Bradley** Bulletin 1494V and 140U disconnect switches with flange-mounted variable-depth operating mechanisms and Bulletin 1494V flange-mounted variable-depth operating mechanisms for circuit breakers. These enclosures will not accept Allen-Bradley Bulletin 1494F disconnect devices or Bulletin 1494D circuit breaker operators
- ABB Controls** flange-mounted variable-depth operating mechanisms for disconnect switches and circuit breakers
- Eaton / Cutler-Hammer** Type C361 flange-mounted variable depth
- Eaton / Cutler-Hammer** Type C361 flange-mounted variable-depth operating mechanisms with disconnect switches and Type C371 flange-mounted variable depth operating mechanisms for circuit breakers; also Flex Shaft™ handle mechanisms for circuit breakers
- General Electric** Type STDA flange handles and variable depth operating
- General Electric** Type STDA flange handles and variable depth operating mechanisms for disconnect switches and circuit breakers; also Spectra Flex™ cable operators for circuit breakers
- SIEMENS** I-T-E Max-Flex flange-mounted variable depth operating handle for disconnect switches and circuit breakers
- Square D** Class 9422 disconnect switches with flange-mounted variable depth operating mechanisms or cable Industry Standards mechanisms and Class 9422 flange-mounted variable depth operating mechanisms or cable mechanisms for circuit breakers. These enclosures will not accept Square D Class 9422 bracket-mounted disconnect devices, Class 9422TG1, or TG2 devices.

Other Brands							
Disconnect Enclosure Series	Square D9422 Series	Allen-Bradley 1494F and 1494D Series	Allen-Bradley 1494V, 1494C, 140U, 194RC Series	ABB Controls	Eaton/Cutler-Hammer C361 and C371 Series	General Electric STDA Series	Siemens I-T-E Max-Flex Series
WAX_U Series	✓	✓	✓	✓	✓	✓	✓
adapter plate required	WA21SDA	WA21ABA	WA21ABVA	WA21CHVA	WA21CHVA	WA21GETDA	WA21ITE
WACPX_U Series	✓	✓	✓	✓	✓	✓	✓
adapter plate required	WA21SDA	WA21ABA	WA21ABVA	WA21CHVA	WA21CHVA	WA21GETDA	WA21ITE
WAXM_U Series	✓	✓	✓	✓	✓	✓	✓
adapter plate required	WA21SDA	WA21ABA	WA21ABVA	WA21CHVA	WA21CHVA	WA21GETDA	WA21ITE

NEMA 12 Heavy-Duty Two-Door Right-Flange Floor-Mount Disconnect



Construction

- 10-gauge steel bodies and doors
- Continuous welded seams ground smooth
- Body stiffeners included for extra rigidity
- Heavy gauge continuous hinges to secure doors
- Heavy-duty 3-point padlocking handles on all doors
- 15 in [381 mm] floor stands welded to enclosure
- Poured in place polyurethane gasket
- Heavy-duty lifting eyes and provisions for fluorescent lighting
- Panel supports
- Collar studs for mounting optional subpanels
- Grounding provisions
- The right door is considered to be the "master" door on the "Right Flange" mount enclosures and the left door is the "master" door on the "Center Post" mount enclosures
- A mechanical interlock to prevent the slave door from opening before opening the master door
- Disconnects come with a universal cutout which provides mounting for most disconnects operators by using operator adapters
- Removable center post permits easy panel installation
- FTC rolled lip around all sides of opening keeps out liquids and contaminants

Finish

- ANSI 61 gray polyester powder inside and out over phosphatized surfaces
- Painted steel subpanels are white polyester powder over phosphatized surfaces
- Galvanized panels are a conductive finish (unpainted)

Listings

- UL 508 12 [UL File E64791]
- NEMA/EEMAC 12



Notes: Disconnect switch or circuit breakers, operating handle and operating mechanism must be ordered separately.

Operator adapter plates are required with this enclosure series and must be purchased separately. Select the proper operator adapter for the brand and type of disconnect being used. Make sure the disconnect device you are using will fit the enclosure size you choose.

Shipping Schedule

Same day 1 - 5 days 1 - 7 days 1 - 15 days 1 - 20 days

Color indicates shipping lead time in business days.

NEMA 12 Heavy-Duty Two-Door Right-Flange Floor-Mount Disconnect

Part Number	Price	Enclosure Size HxWxD	Painted Steel Subpanel	Galvanized Subpanel
WA60X4912U	Retired	60.13 x 49.75 x 13.36 [1527 x 1264 x 339]	NPDD6048	NPDD6048G
WA60X4918U	Retired	60.13 x 49.75 x 19.36 [1527 x 1264 x 492]	NPDD6048	NPDD6048G
WA60X4924U	\$4,001.00	60.13 x 49.75 x 25.36 [1527 x 1264 x 644]	NPDD6048	NPDD6048G
WA60X6112U	Retired	60.13 x 61.75 x 13.36 [1527 x 1568 x 339]	NPDD6060	NPDD6060G
WA60X6118U	Retired	60.13 x 61.75 x 19.36 [1527 x 1568 x 492]	NPDD6060	NPDD6060G
WA60X6124U	Retired	60.13 x 61.75 x 25.36 [1527 x 1568 x 644]	NPDD6060	NPDD6060G
WA72X6112U	Retired	72.13 x 61.75 x 13.36 [1832 x 1568 x 339]	NPDD7260	NPDD7260G
WA72X6118U	Retired	72.13 x 61.75 x 19.36 [1832 x 1568 x 492]	NPDD7260	NPDD7260G
WA72X7312U	\$4,827.00	72.13 x 73.75 x 13.36 [1832 x 1873 x 339]	NPDD7272	—
WA72X7318U	Retired	72.13 x 73.75 x 19.36 [1832 x 1873 x 492]	NPDD7272	—
WA72X7324U	Retired	72.13 x 73.75 x 25.36 [1832 x 1873 x 644]	NPDD7272	—

Notes: Subpanels must be ordered separately.

Dimensions in inches [millimeters].

Letters in table correspond to letters on dimensional drawings.

NEMA 12 Heavy-Duty Two-Door Center Post Floor-Mount Disconnect



Construction

- 10-gauge steel bodies and doors
- Continuous welded seams ground smooth
- Body stiffeners included for extra rigidity
- Heavy gauge continuous hinges to secure doors
- Heavy-duty 3-point padlocking handles on all doors
- 15 in [381 mm] floor stands welded to enclosure
- Poured in place polyurethane gasket
- Heavy-duty lifting eyes and provisions for fluorescent lighting
- Panel supports
- Collar studs for mounting optional subpanels
- Grounding provisions
- The right door is considered to be the "master" door on the "Right Flange" mount enclosures and the left door is the "master" door on the "Center Post" mount enclosures
- A mechanical interlock to prevent the slave door from opening before opening the master door
- Disconnects come with a universal cutout which provides mounting for most disconnects operators by using operator adapters
- Removable center post permits easy panel installation
- FTC rolled lip around all sides of opening keeps out liquids and contaminants

Finish

- ANSI 61 gray polyester powder inside and out over phosphatized surfaces
- Painted steel subpanels are white polyester powder over phosphatized surfaces
- Galvanized panels are a conductive finish (unpainted)

Listings

- UL 508 12 [UL File E64791]
- NEMA/EEMAC 12



Notes: Disconnect switch or circuit breakers, operating handle and operating mechanism must be ordered separately.

Operator adapter plates are required with this enclosure series and must be purchased separately. Select the proper operator adapter for the brand and type of disconnect being used. Make sure the disconnect device you are using will fit the enclosure size you choose.

Shipping Schedule

Same day 1 - 5 days 1 - 7 days 1 - 15 days 1 - 20 days

Color indicates shipping lead time in business days.

NEMA 12 Heavy-Duty Two-Door Center Post Floor-Mount Disconnect

Part Number	Price	Enclosure Size HxWxD	Painted Steel Subpanel	Galvanized Subpanel
WA60CPX4912U	\$3,657.00	60.13 x 49.75 x 13.36 [1527 x 1264 x 339]	NPDD6048	NPDD6048G
WA60CPX4924U	Retired	60.13 x 49.75 x 25.36 [1527 x 1264 x 644]	NPDD6048	NPDD6048G
WA60CPX6112U	\$4,069.00	60.13 x 61.75 x 13.36 [1527 x 1568 x 339]	NPDD6060	NPDD6060G
WA60CPX6124U	Retired	60.13 x 61.75 x 25.36 [1527 x 1568 x 644]	NPDD6060	NPDD6060G
WA72CPX7312U	Retired	72.13 x 73.75 x 13.36 [1832 x 1873 x 339]	NPDD7272	—
WA72CPX7318U	Retired	72.13 x 73.75 x 19.36 [1832 x 1873 x 492]	NPDD7272	—


Notes: Subpanels must be ordered separately.
Dimensions in inches [millimeters].
Letters in table correspond to letters on dimensional drawings.

NEMA 12 Heavy-Duty Two-Door Center Post Floor-Mount Disconnect




Dimensions


WAX-U



WACPX-U



Space Occupied by Disconnect



When ordering 24.13 (613mm) deep enclosures, long connecting rods must be ordered. Long connecting rods are available from disconnect manufacturers.

- ABB Controls flange-operated devices
- Cutler-Hammer C361 devices
- Cutler-Hammer C371 operating mechanisms C371E and C371F, order catalog number C371CS1 connecting rod. For C371G and C371K, order catalog number C371CS2 connecting rod.
- General Electric TDA devices, order catalog number TDSR extended length drive rod
- For Square D 9422 devices, order catalog number 9422-R2 extra long operating rod(s). Some devices require two rods.

Refer to National Electrical Code * 1996 article 430-10(b) for wiring space required for line side conductors to be connected to disconnect. Verify your application to determine if wiring space is adequate.

NEMA 12 Heavy-Duty Freestanding Disconnect



Construction

- 10-gauge steel bodies and doors
- Removable 10-gauge steel subpanels included and mounted on collar studs
- Smooth-ground continuous-welded seams
- Body stiffeners for extra rigidity
- Heavy-duty lifting eyes and provisions for fluorescent lighting
- Heavy gauge lift off hinges
- 3-point padlocking handles on all doors
- Panel supports
- Removable center posts allow easy panel installation
- Grounding provisions
- Doors have closed-cell neoprene gasket
- Unless specified, the far right door is considered to be the "Master" door. All other doors are considered slave doors
- The mechanical interlock is activated by the master door which prevents the slave doors from being opened first. Doors can be closed in any order
- Disconnects come with a universal cutout which provides mounting for most disconnect operators by using operator adapters
- FTC rolled lip around all sides of opening keeps out liquids and contaminants

Finish

- ANSI 61 gray polyester powder inside and out over phosphatized surfaces
- Included painted steel subpanels are white polyester powder over phosphatized surfaces

Listings

- UL 508 12 [UL File E64791]
- NEMA/EEMAC 12



Notes: Disconnect switch or circuit breakers, operating handle and operating mechanism must be ordered separately.

Operator adapter plates are required with this enclosure series and must be purchased separately. Select the proper operator adapter for the brand and type of disconnect being used. Make sure the disconnect device you are using will fit the enclosure size you choose.

NEMA 12 Heavy-Duty Freestanding Disconnect



Shipping Schedule

Same day 1 - 5 days 1 - 7 days 1 - 15 days 1 - 20 days


Color indicates shipping lead time in business days.

NEMA 12 Heavy-Duty Freestanding Disconnect				
Part Number	Price	Enclosure Size HxWxD	Number of Subpanels	Subpanel Size AxB
Single-Door				
WA72XM2718U	\$2,801.00	72.13 x 27.50 x 19.29 [1832 x 699 x 490]	1	60.00 x 21.00 [1524 x 552]
WA72XM3318U	Retired	72.13 x 33.50 x 19.29 [1832 x 851 x 490]	1	60.00 x 27.00 [1524 x 705]
WA72XM3918U	\$3,408.00	72.13 x 39.50 x 19.29 [1832 x 1003 x 490]	1	60.00 x 33.00 [1524 x 857]
WA84XM3918U	\$3,790.00	84.13 x 39.50 x 19.29 [2137 x 1003 x 490]	1	72.00 x 33.00 [1829 x 857]
WA90XM3920U	\$4,249.00	90.13 x 39.50 x 21.29 [2289 x 1003 x 541]	1	78.00 x 33.00 [1981 x 857]
WA90XM3924U	\$4,457.00	90.13 x 39.50 x 25.29 [2289 x 1003 x 642]	1	78.00 x 33.00 [1981 x 857]
Two-Door				
WA72XM5318U	Retired	72.13 x 43.50 x 19.29 [1832 x 1384 x 490]	1	60.00 x 48.00 [1524 x 1219]
WA72XM6518U	Retired	72.13 x 66.50 x 19.29 [1832 x 1689 x 490]	1	60.00 x 60.00 [1524 x 1524]
WA72XM7718U	Retired	72.13 x 78.50 x 19.29 [1832 x 1994 x 490]	1	60.00 x 72.00 [1524 x 1829]
WA72XM7724U	Retired	72.13 x 78.50 x 25.29 [1832 x 1994 x 642]	1	60.00 x 72.00 [1524 x 1829]
WA84XM7718U	\$6,263.00	84.13 x 78.50 x 19.29 [2137 x 1994 x 490]	1	72.00 x 72.00 [1829 x 1829]
WA90XM7720U	\$6,991.00	90.13 x 78.50 x 21.29 [2289 x 1994 x 541]	1	78.00 x 72.00 [1981 x 1829]
WA90XM7724U	Retired	90.13 x 78.50 x 25.29 [2289 x 194 x 642]	1	78.00 x 72.00 [1981 x 1829]
Three-Door				
WA72XM3EQ18U	Retired	72.13 x 99.50 x 19.29 [1832 x 2527 x 490]	1	60.00 x 60.00 [1524 x 1524]
			1	60.00 x 27.00 [1524 x 705]
WA72XM3EW18U	Retired	72.13 x 117.05 x 19.29 [1832 x 2985 x 490]	1	60.00 x 72.00 [1524 x 1829]
			1	60.00 x 33.00 [1524 x 857]
WA84XM3EW18U	Retired	84.13 x 117.50 x 19.29 [2137 x 2985 x 490]	1	72.00 x 72.00 [1829 x 1829]
			1	72.00 x 33.00 [1829 x 857]
WA90XM3EW24U	Retired	90.13 x 117.50 x 25.29 [2289 x 2985 x 642]	1	78.00 x 72.00 [1981 x 1829]
			1	78.00 x 33.00 [1981 x 857]
Four-Door				
WA84XM4EW18U	Retired	84.13 x 157.50 x 19.29 [2137 x 4001 x 490]	2	72.00 x 72.00 [1829 x 1829]
Five-Door				
WA84XM5EW18U	Retired	84.13 x 196.75 x 19.29 [2137 x 4997 x 490]	2	72.00 x 72.00 [1829 x 1829]
			1	72.00 x 33.00 [1829 x 857]
Notes: Subpanels are included. Dimensions in inches [millimeters]. Letters in table correspond to letters on dimensional drawings.				

NEMA 12 Heavy-Duty Freestanding Disconnect




Dimensions



NEMA 12 Heavy-Duty Two-Door Freestanding Disconnect




Dimensions



NEMA 12 Heavy-Duty Three-Door Freestanding Disconnect




Dimensions



NEMA 12 Heavy-Duty Four-Door Freestanding Disconnect





Dimensions



NEMA 12 Heavy-Duty Five-Door Freestanding Disconnect



Dimensions



Wiring Space "WB" is available when disconnect is installed in the enclosure.

When ordering 24.13 (613mm) deep enclosures, long connecting rods must be ordered. Long connecting rods are available from disconnect manufacturers.

- ABB Controls flange-operated devices
- Cutter-Hammer C361 devices
- Cutler-Hammer C371 operating mechanisms C371E and C371F, order C371CS1 connecting rod. For C371G and C371K, order catalog number C371CS2 connecting rod.
- General Electric TDA devices, order catalog number TDSR extended length drive rod
- For Square D 9422 devices, order catalog number 9422-R2 extra long operating rod(s). Some devices require two rods.

Refer to National Electrical Code 1996 article 430-10(b) for wiring space required for line side conductors to be connected to disconnect. Verify your application to determine if wiring space is adequate.

Disconnect Handle Applications for Freestanding and Floor-Mount Stainless Steel Disconnect Enclosures



Designed to house the following available at AutomationDirect.com

- AutomationDirect.com NEMA 1/12 Flexible shaft handle for Molded Case Circuit Breakers (MCCBs). Series F_S0_C flex handle mechanisms are available in four sizes to actuate all AutomationDirect MCCBs from 15 amps up to 600 amps. **F0S03C, F0S06C, F1S03C, F1S06C, F3S03C, F3S06C, F4S04C, and F4S06C**
- Socomec Disconnect switches with cable, flange-mounted cable operator and handles. Handles **37299002** and **37299003**, cable operator **37299903**, and cables **37299992** (3ft) or **37299993** (5ft)
- Fuji Electric NEMA 12 flexible shaft handle for Molded Case Circuit Breakers (MCCBs). Series BW9F flex handle mechanisms are available in four sizes to actuate all Fuji Electric MCCBs from 15 Amps to 800 Amps. **BW9F0CA-15A, BW9F0CA-20A, BW9F0GA-15A, BW9F0GA-20A, BW9F0HA-15A, BW9F0HA-20A, BW9F0JA-15A, and BW9F0JA-20A.**
- Gladiator Molded Case Circuit Breakers (MCCBs) flange mounted cable operator and handles. See Gladiator sections for handles and cable options. **GCBX1-FHC-N3R4-M, GCBX1-FHC-N4X-M, GCBX5-FHC-N3R4-M, and GCBX5-FHC-N4X-M**

Available at AutomationDirect.com				
Disconnect Enclosure Series	AutomationDirect F_S0_C Series	Socomec 37299002 and 37299003	Fuji BW9F Series	Gladiator GCBX
WAX-SSN4 Series	✓	✓	✓	✓
WACPX-SSN4 Series	✓	✓	✓	✓
WAXM-SSN4 Series	✓	✓	✓	✓

Designed to house other brands

- Allen-Bradley** Bulletin 1494V and 140U disconnect switches with flange-mounted variable-depth operating mechanisms and Bulletin 1494V flange-mounted variable-depth operating mechanisms for circuit breakers. These enclosures will not accept Allen-Bradley Bulletin 1494F disconnect devices or Bulletin 1494D circuit breaker operators
- ABB Controls** flange-mounted variable-depth operating mechanisms for disconnect switches and circuit breakers
- Eaton / Cutler-Hammer** Type C361 flange-mounted variable depth
- Eaton / Cutler-Hammer** Type C361 flange-mounted variable-depth operating mechanisms with disconnect switches and Type C371 flange-mounted variable depth operating mechanisms for circuit breakers; also Flex Shaft™ handle mechanisms for circuit breakers
- General Electric** Type STDA flange handles and variable depth operating
- General Electric** Type STDA flange handles and variable depth operating mechanisms for disconnect switches and circuit breakers; also Spectra Flex™ cable operators for circuit breakers
- SIEMENS** I-T-E Max-Flex flange-mounted variable depth operating handle for disconnect switches and circuit breakers
- Square D** Class 9422 disconnect switches with flange-mounted variable depth operating mechanisms or cable Industry Standards mechanisms and Class 9422 flange-mounted variable depth operating mechanisms or cable mechanisms for circuit breakers. These enclosures will not accept Square D Class 9422 bracket-mounted disconnect devices, Class 9422TG1, or TG2 devices.

Other Brands							
Disconnect Enclosure Series	Square D9422 Series	Allen-Bradley 1494F and 1494D Series	Allen-Bradley 1494V, 1494C, 140U, 194RC Series	ABB Controls	Eaton/Cutler-Hammer C361 and C371 Series	General Electric STDA Series	Siemens I-T-E Max-Flex Series
WAX-SSN4 Series	✓	✗	✓	✓	✓	✓	✓
WACPX-SSN4 Series	✓	✗	✓	✓	✓	✓	✓
WAXM-SSN4 Series	✓	✗	✓	✓	✓	✓	✓

NEMA 4, 4X, and 12 Two-Door Floor-Mount Right-Flange Disconnect



Construction

- 14-gauge 304 stainless steel bodies and doors
- Continuously-welded seams ground smooth
- Rolled lip around all sides of opening keeps out liquids and contaminants
- All stainless steel exterior hardware
- All stainless steel interior and exterior
- 3-point 316L stainless steel padlocking handles on all doors
- Doors removed by pulling stainless steel continuous hinge pin
- Polyurethane poured-in-place gasket
- External mounting feet
- Collar studs for mounting optional subpanel
- Grounding provisions provided
- Bracket welded to door for attaching disconnect interlock door catch
- Holes in body for mounting disconnect operating handle and operating mechanism. These enclosures are designed to operate properly without the use of door hardware

Finish

- Enclosures have a #3 intermediate polished finish on all external surfaces
- Painted steel and perforated subpanels white polyester powder over phosphatized surfaces
- Galvanized are a conductive finish (unpainted)

Listings

- UL 508 4, 4X, and 12 [UL File E64791]
- NEMA/EEMAC 4, 4X, and 12



Notes: Disconnect switch or circuit breakers, operating handle, and operating mechanism must be ordered separately.

Operator adapter plates are not required with this enclosure series.

Make sure the disconnect device you are using will fit the enclosure size you choose.

Shipping Schedule

Same day 1 - 5 days 1 - 7 days 1 - 15 days 1 - 20 days

Color indicates shipping lead time in business days.

NEMA 4, 4X, and 12 Two-Door Floor-Mount Right-Flange Disconnect

Part Number	Price	Enclosure Size HxWxD	Painted Steel Subpanel	Galvanized Subpanel
WA60X4912SSN4	Retired	60.13 x 49.75 x 13.35 [1527 x 1264 x 339]	NPDD6048	NPDD6048G
WA60X4918SSN4	Retired	60.13 x 49.75 x 19.35 [1527 x 1264 x 491]	NPDD6048	NPDD6048G
WA60X6112SSN4	Retired	60.13 x 61.75 x 13.35 [1527 x 1568 x 339]	NPDD6060	NPDD6060G
WA60X6118SSN4	Retired	60.13 x 61.75 x 19.35 [1527 x 1568 x 491]	NPDD6060	NPDD6060G
WA72X6112SSN4	Retired	72.13 x 61.75 x 13.35 [1832 x 1568 x 339]	NPDD7260	NPDD7260G
WA72X6118SSN4	Retired	72.13 x 61.75 x 19.35 [1832 x 1568 x 491]	NPDD7260	NPDD7260G
WA72X7312SSN4	Retired	72.13 x 73.75 x 13.35 [1832 x 1873 x 339]	NPDD7272	—
WA72X7318SSN4	Retired	72.13 x 73.75 x 19.35 [1832 x 1873 x 491]	NPDD7272	—
WA72X7324SSN4	Retired	72.13 x 73.75 x 25.35 [1832 x 1873 x 644]	NPDD7272	—

Notes: Subpanels must be ordered separately.


Dimensions in inches [millimeters].

Letters in table correspond to letters on dimensional drawings.

NEMA 4, 4X, and 12 Two-Door Floor-Mount Right-Flange Disconnect



Dimensions



NEMA 4, 4X, and 12 Two-Door Floor-Mount Center Post Disconnect



Construction

- 14-gauge 304 stainless steel bodies and doors
- Continuously-welded seams ground smooth
- Rolled lip around all sides of opening keeps out liquids and contaminants
- All stainless steel exterior hardware
- All stainless steel interior and exterior
- 3-point 316L stainless steel padlocking handles on all doors
- Doors removed by pulling stainless steel continuous hinge pin
- Polyurethane poured-in-place gasket
- External mounting feet
- Collar studs for mounting optional subpanel
- Grounding provisions provided
- Bracket welded to door for attaching disconnect interlock door catch
- Holes in body for mounting disconnect operating handle and operating mechanism. These enclosures are designed to operate properly without the use of door hardware

Finish

- Enclosures have a #3 intermediate polished finish on all external surfaces
- Painted steel and perforated subpanels white polyester powder over phosphatized surfaces
- Galvanized and stainless subpanels are a conductive finish (unpainted)

Listings

- UL 508 4, 4X, and 12 [UL File E64791]
- NEMA/EEMAC 4, 4X, and 12



Notes: Disconnect switch or circuit breakers, operating handle, and operating mechanism must be ordered separately.

Operator adapter plates are not required with this enclosure series.

Make sure the disconnect device you are using will fit the enclosure size you choose.

Shipping Schedule

Same day 1 - 5 days 1 - 7 days 1 - 15 days 1 - 20 days

Color indicates shipping lead time in business days.

NEMA 4, 4X, and 12 Two-Door Floor-Mount Center Post Disconnect


Part Number	Price	Enclosure Size HxWxD	Painted Steel Subpanel	Galvanized Subpanel
<u>WA60CPX4812SSN4</u>	Retired	60.13 x 49.75 x 13.35 [1527 x 1264 x 339]	<u>NPDD6048</u>	<u>NPDD6048G</u>
<u>WA60CPX6012SSN4</u>	Retired	60.13 x 61.75 x 13.35 [1527 x 1568 x 339]	<u>NPDD6060</u>	<u>NPDD6060G</u>
<u>WA72CPX7212SSN4</u>	Retired	72.13 x 73.75 x 13.35 [1832 x 1873 x 339]	<u>NPDD7272</u>	—
<u>WA72CPX7218SSN4</u>	Retired	72.13 x 73.75 x 19.35 [1832 x 1873 x 491]	<u>NPDD7272</u>	—

Notes: Subpanels must be ordered separately.
Dimensions in inches [millimeters].

NEMA 4, 4X, and 12 Two-Door Floor-Mount Center Post Disconnect



Dimensions



NEMA 3R, 4, 4X, and 12 Single-Door Freestanding Right-Flange Disconnect



Construction

- 14-gauge 304 stainless steel bodies and doors
- Continuously-welded seams ground smooth
- Rolled lip around all sides of opening keeps out liquids and contaminants
- All stainless steel exterior hardware
- All stainless steel interior and exterior
- 3-point 316L stainless steel padlocking handles on all doors
- Doors removed by pulling stainless steel continuous hinge pin
- Polyurethane poured-in-place gasket
- External mounting feet
- Collar studs for mounting optional subpanel
- Grounding provisions provided
- Bracket welded to door for attaching disconnect interlock door catch
- Holes in body for mounting disconnect operating handle and operating mechanism. These enclosures are designed to operate properly without the use of door hardware
- Removable 10-gauge steel back panels are included and mounted on collar studs

Finish

- Except for the back, exterior has a #3 intermediate polished Finish
- Included painted steel subpanels are white polyester powder over phosphatized surfaces

Listings

- UL 508 3R, 4, 4X, and 12 [UL File E64791]
- NEMA/EEMAC 3R, 4, 4X, and 12



Notes: Disconnect switch or circuit breakers, operating handle, and operating mechanism must be ordered separately.

Operator adapter plates are not required with this enclosure series.

Make sure the disconnect device you are using will fit the enclosure size you choose.

Shipping Schedule

Same day 1 - 5 days 1 - 7 days 1 - 15 days 1 - 20 days

Color indicates shipping lead time in business days.

NEMA 3R, 4, 4X, and 12 Single-Door Freestanding Right Flange Disconnect

Part Number	Price	Enclosure Size HxWxD	Subpanel Size
WA72XM2718SSN4	Retired	72.12 x 27.50 x 19.35 [1832 x 699 x 491]	60.00 x 21.75 (1524 x 552)
WA72XM3318SSN4	Retired	72.12 x 33.50 x 19.35 [1832 x 851 x 491]	60.00 x 27.75 (1524 x 705)
WA72XM3918SSN4	Retired	72.12 x 39.50 x 19.35 [1832 x 1003 x 491]	60.00 x 33.75 (1524 x 857)
WA84XM3918SSN4	Retired	84.12 x 39.50 x 19.35 [2137 x 1003 x 491]	72.00 x 33.75 (1829 x 857)
WA84XM3924SSN4	Retired	84.12 x 39.50 x 25.35 [2137 x 1003 x 644]	78.00 x 33.75 (1981 x 857)
WA90XM3918SSN4	Retired	90.12 x 39.50 x 19.35 [2289 x 1003 x 491]	79.00 x 33.75 (2007 x 857)
WA90XM3920SSN4	Retired	90.12 x 39.50 x 21.35 [2289 x 1003 x 542]	80.00 x 33.75 (2032 x 857)
WA90XM3924SSN4	Retired	90.12 x 39.50 x 25.35 [2289 x 1003 x 644]	81.00 x 33.75 (2057 x 857)


Notes: Dimensions in inches [millimeters].

Letters in table correspond to letters on dimensional drawings.

NEMA 3R, 4, 4X, and 12 Single-Door Freestanding Right-Flange Disconnect



Dimensions



NEMA 3R, 4, 4X, and 12 Two-Door Freestanding Right-Flange Disconnect



Construction

- Bodies and doors fabricated from 12- and 10-gauge 304 stainless steel
- Removable 10-gauge steel back panels are included and mounted on collar studs
- Continuously-welded seams ground smooth
- Body stiffeners provided for extra rigidity
- Heavy gauge continuous hinges to support each door
- Heavy-duty lifting eyes and Provisions for fluorescent lighting provided
- 3-PT 316L stainless steel padlocking handles on all doors
- Panel supports
- Center posts are removable to permit easy panel installation
- Grounding provisions provided
- Doors are sealed with polyurethane poured-in-place gasket
- Unless specified, the far right door is considered to be the "master" door. All other doors are considered slave doors
- The mechanical interlock is activated by the master door which prevents the slave doors from being opened first
- Doors can be closed in any order
- Disconnects come with a universal cutout which provides mounting for most disconnect operators by using operator adapters

Finish

- Except for back, exterior has a #3 intermediate polished Finish
- Included subpanels are white polyester powder over phosphatized surfaces

Listings

- UL 508 3R, 4, 4X, and 12 [UL File E64791]
- NEMA/EEMAC 3R, 4, 4X, and 12



Notes: Disconnect switch or circuit breakers, operating handle, and operating mechanism must be ordered separately.

Operator adapter plates are not required with this enclosure series.

Make sure the disconnect device you are using will fit the enclosure size you choose.

Shipping Schedule

Same day 1 - 5 days 1 - 7 days 1 - 15 days 1 - 20 days

Color indicates shipping lead time in business days.

NEMA 3R, 4, 4X, and 12 Two-Door Freestanding Right Flange Disconnect

Part Number	Price	Enclosure Size HxWxD	Subpanel Size AandB
WA72XM5318SSN4	Retired	72.13 x 43.50 x 19.29 [1832 x 1384 x 490]	60.00 x 48.00 [1524 x 1219]
WA72XM6518SSN4	Retired	72.13 x 66.50 x 19.35 [1832 x 1689 x 491]	60.00 x 60.00 [1524 x 1524]
WA72XM7718SSN4	Retired	72.13 x 78.50 x 19.35 [1832 x 1994 x 491]	60.00 x 72.00 [1524 x 1829]
WA72XM7724SSN4	Retired	72.13 x 78.50 x 25.35 [1832 x 1994 x 644]	60.00 x 72.00 [1524 x 1829]
WA84XM7718SSN4	Retired	84.13 x 78.50 x 19.35 [2137 x 1994 x 491]	72.00 x 72.00 [1829 x 1829]
WA84XM7724SSN4	Retired	84.13 x 78.50 x 25.35 [2137 x 1994 x 644]	72.00 x 72.00 [1829 x 1829]
WA90XM7718SSN4	Retired	90.13 x 78.50 x 19.35 [2289 x 1994 x 491]	78.00 x 72.00 [1981 x 1829]
WA90XM7720SSN4	Retired	90.13 x 78.50 x 21.35 [2289 x 1994 x 542]	78.00 x 72.00 [1981 x 1829]
WA90XM7724SSN4	Retired	90.13 x 78.50 x 25.35 [2289 x 1994 x 644]	78.00 x 72.00 [1981 x 1829]

Notes: Dimensions in inches [millimeters].

Letters in table correspond to letters on dimensional drawings.

NEMA 3R, 4, 4X, and 12 Two-Door Freestanding Right-Flange Disconnect



Dimensions

