



# TABLE OF CONTENTS

---

## Chapter 1: Getting Started

<b>Introduction</b> .....	<b>1-2</b>
The Purpose of this Manual.....	1-2
About Getting Started.....	1-2
Supplemental Manuals and Other Help.....	1-2
Technical Support.....	1-2
<b>Conventions Used</b> .....	<b>1-3</b>
Key Topics for Each Chapter.....	1-3
Before you begin.....	1-4
Step 1: Install Programming Software.....	1-5
Step 2: Launch Programming Software.....	1-6
Step 3: Create a Project.....	1-8
Step 4: Compile and Save Project.....	1-14
Step 5: Apply Power.....	1-15
Step 6: Establish PC to PLC Communications.....	1-16
Step 7: Write Project into PLC.....	1-24
Step 8: Place PLC in RUN Mode.....	1-25
Step 9: Test Project using Data View Monitor.....	1-26
Step 10: Y001 Output On?.....	1-27
Additional Training Resources.....	1-28

## Chapter 2: Specifications

<b>Overview</b> .....	<b>2-2</b>
PLC Units.....	2-3
Basic PLC Units.....	2-3
Standard PLC Units.....	2-4
Analog PLC Units.....	2-5
Ethernet Basic PLC Units.....	2-6

## Table of Contents

---

Ethernet Standard PLC Units .....	2-7
Ethernet Analog PLC Units .....	2-8
Communication Ports.....	2-9
I/O Modules.....	2-10
Power Supply .....	2-13
Programming Software .....	2-14
PC Requirements.....	2-14
<b>PLC Numbering System.....</b>	<b>2-15</b>
Data Types .....	2-15
Memory Types .....	2-16
I/O Numbering System .....	2-18
<b>PLC Operation .....</b>	<b>2-19</b>
Introduction .....	2-19
PLC Operating System .....	2-19
PLC Operating Modes.....	2-20
Stop Mode.....	2-20
Run Mode .....	2-20
Read Inputs.....	2-21
Service Peripherals and Force I/O .....	2-21
Update Special Control (SC) Relays and Special Data (SD) Registers.....	2-22
Solve Application Program .....	2-22
Write Outputs .....	2-22
Diagnostics. ....	2-22
<b>Power Budgeting.....</b>	<b>2-23</b>
What is Power Budgeting? .....	2-23
Power Budget Calculation .....	2-24
Power Budget Example .....	2-25
Power Budgeting using the CLICK Programming Software.....	2-25
<b>General Specifications .....</b>	<b>2-26</b>
General Specifications (all CLICK PLC products) .....	2-26
<b>PLC Unit Specifications.....</b>	<b>2-27</b>
Common Specifications.....	2-27
PLC LED Status Indicators.....	2-29
Memory Map .....	2-32
<b>Basic PLC Unit Specifications .....</b>	<b>2-33</b>

C0-00DD1-D – 8 DC Input/6 Sinking DC Output Micro PLC .....	2–33
C0-00DD2-D – 8 DC Input/6 Sourcing DC Output Micro PLC .....	2–35
C0-00DR-D – 8 DC Input/6 Relay Output Micro PLC .....	2–37
C0-00AR-D – 8 AC Input/6 Relay Output Micro PLC .....	2–39
<b>Standard PLC Unit Specifications.....</b>	<b>2–41</b>
C0-01DD1-D – 8 DC Input/6 Sinking DC Output Micro PLC .....	2–41
C0-01DD2-D – 8 DC Input/6 Sourcing DC Output Micro PLC .....	2–43
C0-01DR-D – 8 DC Input/6 Relay Output Micro PLC .....	2–45
C0-01AR-D – 8 AC Input/6 Relay Output Micro PLC .....	2–47
<b>Analog PLC Unit Specifications .....</b>	<b>2–49</b>
C0-02DD1-D – 4 DC Input/4 Sinking DC Output; 2 Analog In/2 Analog Out .....	2–49
C0-02DD2-D – 4 DC Input/4 Sourcing DC Output; 2 Analog In/2 Analog Out.....	2–52
C0-02DR-D – 4 DC Input/4 Relay Output; 2 Analog In/2 Analog Out .....	2–55
<b>Ethernet Basic PLC Unit Specifications .....</b>	<b>2–58</b>
C0-10DD1E-D – 8 DC Input/6 Sinking DC Output Micro PLC.....	2–58
C0-10DD2E-D – 8 DC Input/6 Sourcing DC Output Micro PLC .....	2–60
C0-10DRE-D – 8 DC Input/6 Relay Output Micro PLC.....	2–62
C0-10ARE-D – 8 AC Input/6 Relay Output Micro PLC .....	2–64
<b>Ethernet Standard PLC Unit Specifications .....</b>	<b>2–66</b>
C0-11DD1E-D – 8 DC Input/6 Sinking DC Output Micro PLC.....	2–66
C0-11DD2E-D – 8 DC Input/6 Sourcing DC Output Micro PLC .....	2–68
C0-11DRE-D – 8 DC Input/6 Relay Output Micro PLC.....	2–70
C0-11ARE-D – 8 AC Input/6 Relay Output Micro PLC .....	2–72
<b>Ethernet Analog PLC Unit Specifications.....</b>	<b>2–74</b>
C0-12DD1E-D – 4 DC Input (Sink/Source)/4 Sinking DC Output, 2 Analog Voltage/ Current Input, 2 Analog Voltage/Current Output Micro PLC.....	2–74
C0-12DD2E-D – 4 DC Input (Sink/Source)/4 Sourcing DC Output, 2 Analog Voltage/ Current Input, 2 Analog Voltage/Current Output Micro PLC.....	2–77
C0-12DRE-D – 4 DC Input (Sink/Source)/4 Relay Output, 2 Analog Voltage/Current Input, 2 Analog Voltage/Current Output Micro PLC.....	2–80
C0-12ARE-D – 4 AC Input (Sink/Source)/4 Relay Output, 2 Analog Voltage/Current Input, 2 Analog Voltage/Current Output Micro PLC.....	2–83
C0-12DD1E-1-D – 4 DC Input (Sink/Source)/4 Sinking DC Output, 2 Analog Current Input, 2 Analog Current Output Micro PLC.....	2–86
C0-12DD2E-1-D – 4 DC Input (Sink/Source)/4 Sourcing DC Output, 2 Analog Current Input, 2 Analog Current Output Micro PLC.....	2–89

## Table of Contents

---

C0-12DRE-1-D – 4 DC Input (Sink/Source)/4 Relay Output, 4 Analog Current Input, 2 Analog Current Output Micro PLC .....	2-92
C0-12ARE-1-D – 4 AC Input/4 Relay Output, 4 Analog Current Input, 2 Analog Current Output Micro PLC.....	2-95
C0-12DD1E-2-D – 4 DC Input (Sink/Source)/4 Sinking DC Output, 4 Analog Voltage Input, 2 Analog Voltage Output Micro PLC.....	2-98
C0-12DD2E-2-D – 4 DC Input (Sink/Source)/4 Sourcing DC Output, 4 Analog Voltage Input, 2 Analog Voltage Output Micro PLC.....	2-101
C0-12DRE-2-D – 4 DC Input (Sink/Source)/4 Relay Output 4 Analog Voltage Input, 2 Analog Voltage Output Micro PLC.....	2-104
C0-12ARE-2-D – 4 AC Input/4 Relay Output, 4 Analog Voltage Input, 2 Analog Voltage Output Micro PLC .....	2-107
<b>I/O Module Specifications.....</b>	<b>2-110</b>
I/O Terminal Block Specifications for PLCs and I/O Modules .....	2-110
LED Indicators .....	2-110
C0-08ND3 – 8-Point Sink/Source DC Input Module.....	2-111
C0-08ND3-1 – 8-Point Sink/Source DC Input Module.....	2-112
C0-16ND3 – 16-Point Sink/Source DC Input Module.....	2-113
C0-08NE3 – 8-Point Sink/Source AC/DC Input Module.....	2-114
C0-16NE3 – 16-Point Sink/Source AC/DC Input Module.....	2-115
C0-08NA – 8-Point AC Input Module.....	2-116
C0-08TD1 – 8-Point Sinking DC Output Module .....	2-117
C0-08TD2 – 8-Point Sourcing DC Output Module .....	2-118
C0-16TD1 – 16-Point Sinking DC Output Module .....	2-119
C0-16TD2 – 16-Point Sourcing DC Output Module .....	2-120
C0-08TA – 8-Point AC Output Module.....	2-121
C0-04TRS – 4-Point Relay Output Module.....	2-122
C0-08TR – 8-Point Relay Output Module .....	2-123
C0-16CDD1 – 8-Point DC Input and 8-Point DC Sinking Output Module.....	2-124
C0-16CDD2 – 8-Point DC Input and 8-Point DC Sourcing Output Module.....	2-126
C0-08CDR – 4-Point DC Input and 4-Point Relay Output Module.....	2-128
C0-04AD-1 – 4-Channel Analog Current Input Module.....	2-130
C0-04AD-2 – 4-Channel Analog Voltage Input Module.....	2-131
C0-04RTD – 4-Channel RTD Input Module .....	2-132
C0-04THM – 4-Channel Thermocouple Input Module .....	2-134
C0-04DA-1 – 4-Channel Analog Current Output Module.....	2-136

C0-04DA-2 – 4-Channel Analog Voltage Output Module ..... 2-137  
 C0-4AD2DA-1 – 4-Ch. Analog Current In & 2-Ch. Analog Current Out Module .. 2-138  
 C0-4AD2DA-2 – 4-Ch. Analog Current In & 2-Ch. Analog Voltage Out Module .. 2-140  
**Power Supply Specifications** ..... 2-142  
     C0-00AC Power Supply ..... 2-142  
     C0-01AC Power Supply ..... 2-142  
**Accessories** ..... 2-143

## Chapter 3: Installation and Wiring

**Safety Guidelines** ..... 3-2  
     Plan for Safety ..... 3-2  
     Three Levels of Protection ..... 3-3  
     Orderly System Shutdown..... 3-3  
     System Power Disconnect ..... 3-3  
     Emergency Stop Circuits ..... 3-4  
**Introduction to the CLICK PLC Mechanical Design**..... 3-5  
     CLICK PLC Modules ..... 3-5  
     CLICK I/O Modules ..... 3-8  
     CLICK Power Supplies ..... 3-9  
     Battery Backup (Standard, Analog and Ethernet PLCs Only)..... 3-10  
**Mounting Guidelines**..... 3-11  
     Environmental Specifications ..... 3-11  
     Agency Approvals..... 3-11  
     CLICK Unit Dimensions ..... 3-11  
     Enclosures ..... 3-14  
     Panel Layout and Clearances ..... 3-14  
**Installing the CLICK PLC**..... 3-16  
     Connecting the Modules Together..... 3-16  
     Mounting the CLICK PLC on a DIN Rail..... 3-17  
     Optional Mounting Method ..... 3-17  
**Wiring Guidelines** ..... 3-18  
     Power Input Wiring to CLICK Power Supply ..... 3-18  
     Power Input Wiring to CLICK PLC ..... 3-18  
     Fuse Protection..... 3-19

## Table of Contents

---

Planning the I/O Wiring Routes .....	3-20
Wiring I/O Modules.....	3-21
ZIPLink Wiring System Compatibility Matrix for CLICK PLCs .....	3-22
<b>I/O Wiring Checklist .....</b>	<b>3-25</b>
<b>System Wiring Strategies .....</b>	<b>3-26</b>
PLC Isolation Boundaries .....	3-26
Powering I/O Circuits .....	3-27
Sinking/Sourcing Concepts .....	3-28
I/O “Common Terminal” Concepts.....	3-29
DC Input Wiring Methods.....	3-30
DC Output Wiring Methods.....	3-30
Relay Outputs - Wiring Methods .....	3-32
Relay Outputs - Transient Suppression for Inductive Loads in a Control System .....	3-33
<b>Analog I/O Configuration .....</b>	<b>3-36</b>
Terminal Block Wiring - Analog PLC Units .....	3-36
Terminal Block Wiring - Analog I/O Modules.....	3-39
Configuration in the CLICK Programming Software .....	3-40
Analog I/O Monitoring.....	3-43
 <b>Chapter 4: PLC Communication</b>	
<b>Introduction.....</b>	<b>4-2</b>
<b>PLC Communication Ports Specifications .....</b>	<b>4-3</b>
<b>LED Status Indicators.....</b>	<b>4-5</b>
LED Status Indicators.....	4-5
DirectLogic Devices That Do Not Work With CLICK PLCs.....	4-5
<b>3 Steps to Using the CLICK Communications .....</b>	<b>4-7</b>
<b>Typical Communications Applications .....</b>	<b>4-8</b>
Port 1 (RS-232) - Modbus RTU Slave Mode Only .....	4-8
Port 1 (Ethernet) - Modbus TCP .....	4-9
Port 2 (RS-232) - Modbus RTU or ASCII .....	4-10
Port 3 (RS-485 - Modbus RTU or ASCII.....	4-11
<b>W-1: Com Port 1 &amp; 2 (RS-232) Wiring.....</b>	<b>4-12</b>
<b>W-2: Com Port 1 (Ethernet) Wiring.....</b>	<b>4-17</b>

W-3: Com Port 3 Wiring .....	4-19
C-1: Com Port 1 (RS-232) Setup .....	4-20
C-2: Com Port 1 (Ethernet) Setup .....	4-21
C-3: Com Port 2 Setup (Modbus RTU) .....	4-22
C-4: Com Port 2 Setup (ASCII).....	4-23
C-5: Com Port 3 Setup (Modbus RTU) .....	4-24
C-6: Com Port 3 Setup (ASCII).....	4-25
P-1: Modbus Slave (Server) Programming .....	4-26
P-2: Modbus Master Programming (Modbus RTU) .....	4-29
P-3: Modbus Client (Modbus TCP) Programming .....	4-34
P-4: ASCII Receive Programming .....	4-40
P-5: ASCII Send Programming .....	4-43

## Chapter 5: Maintenance

PLC Maintenance.....	5-2
Check LED Indicators.....	5-2
Project Backup .....	5-2
Check Operating Environment .....	5-2
Check Operating Voltage .....	5-2
Check Physical Condition .....	5-3
Check Project Functionality .....	5-3
Check the PLC Program from CLICK PLC Programming Software .....	5-3

## Chapter 6: Troubleshooting

Troubleshooting Direction .....	6-2
PLC Unit Troubleshooting .....	6-3
Toggle Switch .....	6-3
LED Indicators .....	6-4
Power Supply Troubleshooting.....	6-5
The input voltage measures less than 20V DC.....	6-5
The input voltage measures greater than 28V DC .....	6-5
How to check the power budget.....	6-5

## Table of Contents

---

<b>I/O Module Troubleshooting .....</b>	<b>6-6</b>
Input Module Troubleshooting.....	6-6
Output Module Troubleshooting.....	6-7
How to Check the I/O Configuration .....	6-7
How to Check the I/O Status.....	6-8
Replacement of I/O Modules.....	6-9
<b>Troubleshooting Electrical Noise Problems .....</b>	<b>6-10</b>
Electrical Noise Problems.....	6-10
Reducing Electrical Noise.....	6-10
<b>Error Codes .....</b>	<b>6-11</b>