



The Spartan Scientific Series 3580 is an engineered composite 2-Way, 2-Position solenoid/air operated valve designed for the control of liquid media and inert gas. The valve exhibits a large 1/2" orifice and three port sizes standard, 1/4", 3/8" and 1/2" NPT. The Normally Open version of the 3580 has a unique operator that allows for function without the use of a bypass tube as with the 3510 and has a push non-locking and a turn-lock manual override. The valve's compact design utilizes the latest in material sciences with the use of composite materials in the valve body. The solenoid pilot is power saving low wattage, made of stainless steel working components and is miniaturized to fit in tight places. Standard elastomers available are FKM, NBR, and EPDM. The fully encapsulated coils are available in all standard voltages and with spaded, flying leads or with a connector attached. Typical applications are for installations where there is a need to control inert fluids and gases, condensate drainage, hot water plumbing and sprinkler systems.


Dimensional Data


ALL DIMENSIONS ARE IN INCHES UNLESS OTHERWISE NOTED
















Technical Data

Function: 2-Way, 2-Position; Inlet Pilot Diaphragm;

Solenoid Operated; Normally Closed, or Normally Open

Port Size / 1/4" NPT / 1.55 Cv Flow Factor: 3/8" NPT / 1.95 Cv

1/2" NPT / 2.45 Cv

Orifice Sizes: 12.5mm / 2.45Cv

Pressure Range: 7 to 150 psi (depending on orifice size and function)

Temp. Range: Fluid Max.: +60°C

Dry Range: Ambient +10° to +50°C

Response Time: 20 to 80ms Complete Cycle

Media: Air, water

Environment IP65 (IEC 144), NEMA 4

Protection: Dust-tight and water resistant (with electrical connector)

Wetted Materials: Elastomers: EPDM, FKM, NBR

Operator: 300 and 400 Series Stainless Steel, or Brass

Orifice Basket: Acetal POM Shading Ring: Copper (AC Only) Springs: 300 Series Stainless Steel

Valve Body: Glass-filled Nylon (NSF Approved)

Mounting: Use #8 x 0.50" long self-tapping screws (2)

(not provided)

Coil Data: Duty Cycle: Continuous (within specifications)

Encapsulation: Glass-Filled Nylon

Insulation: Class F

Power Rating: 6.5 Watt VDC, 8.5 VA VAC

(others available on request) Voltage: 6, 12, 24 VDC 24, 120, 220, 240 VAC 50/60 Hz Voltage Tolerance: +/- 10% Nominal


Winding: Class H

Connections: Spades: Terminals AMP 6.3x0.8 width 11mm


Flying Lead: PVC 22 AWG, Multi-Strand Copper Wire,

300V, 12" minimum length

Packaged Weight: 0.48 lbs.



How To Order



Specify Part Number

FKM 3580-01-0001 NBR 3580-B1-0001 EPDM 3580-E1-0001

Order Example: 3580-010-8211A

2-Way, N.C., FKM, No Override, 1/4" NPT, 6 VDC, DIN Spade

