


The Spartan Scientific Series 3827 is a composite body solenoid valve offered in both 2-Way & 3-Way, 2-Position Normally Closed or Normally Open functions and eight orifice sizes. Component features include the proven Series 3800 solenoid operator available in brass/ stainless steel or all stainless steel pilot design, optional seal materials and nylon encapsulated coil. The "basket" orifice design feature allows the possibility of changing the orifice diameter to meet flow requirements within a matter of seconds. The composite material is media compatible, eliminating the need for stocking multiple body materials.


Dimensional Data

ALL DIMENSIONS ARE IN INCHES UNLESS OTHERWISE NOTED


NOTE: SHOWN WITHOUT MANUAL OVERRIDE OPTION











ORIFICE SIZE / VOLTAGE

F	0.6		mm	0.81	0.8mm		1.0mm		1.2mm		1.5mm		2.0mm		2.4mm		*3.0mm	
UNCT-OX		AC	DC	AC	DC	AC	DC	AC	DC	AC	DC	AC	DC	AC	DC	AC	DC	
	2/2 NC	200	200	200	200	200	200	200	200	200	200	200	200	200	200	75	60	
	2/2 NO	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	150	150	N/A	N/A	N/A	N/A	N/A	N/A	
	3/2 NC	200	200	200	200	200	200	180	180	150	150	90	75	60	60	25	25	
	3/2 NO	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	150	150	N/A	N/A	N/A	N/A	N/A	N/A	
	3/2 MIX	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	100	90	N/A	N/A	N/A	N/A	N/A	N/A	
	3/2 DIV	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	120	110	N/A	N/A	N/A	N/A	N/A	N/A	

MAX. PRESSURE RANGE (psi)





Technical Data

Function: 2-Way, 2-Position; Direct Acting;

> Normally Closed or Normally Open 3-Way, 2-Position; Direct Acting; Normally Closed or Normally Open

Series 3827

Diverting or Mixing

Port Size: 1/8" NPT

Orifice Sizes / 0.6mm / 0.02 Cv Flow Factor: 0.8mm / 0.03 Cv

> 1.0mm / 0.05 Cv 1.2mm / 0.06 Cv 1.5mm / 0.08 Cv 2.0mm / 0.17 Cv 2.4mm / 0.24 Cv 3.0mm / 0.31 Cv

Pressure Range: Vacuum to 200 psi (depending on orifice size and function)

Temp. Range: Fluid Max.: +60°C

Dry Range: Ambient +10° to +50°C

Response Time: 12 to 14ms Complete Cycle Media: Air, caustics, light oils, water (contact factory for compatibilities)

Environment IP65 (IEC 144), NEMA 4

Protection: Dust-tight and water resistant (with electrical connector)

Mounting: #8 x 0.150" self-tapping screw (2) not provided

Wetted Materials: Elastomers: EPDM, FKM, NBR

(others available on request)

Operator: 400 Series Stainless Steel and Brass

(others available on request) Shading Ring: Copper (AC Only) Springs: 300 Series Stainless Steel

Valve Body: Glass-Filled Nylon (FDA Approved)

Coil Data: Duty Cycle: Continuous (within specifications)

Encapsulation: Glass-Filled Nylon

Insulation: Class F Power Rating: 6.5 Watt, 8.5VA (others available on request) Voltage: 6, 12, 24 VDC 24, 120, 220, 240 VAC 50/60 Hz

Voltage Tolerance: +/- 10% Nominal

Winding: Class H

Spades: Terminals AMP 6.3x0.8 width 11mm Connections:

(Ávailable in DIN Style "A" EN175301-803


for 3.0mm orifice or larger)

Flying Lead: PVC 22 AWG, Multi-Strand Copper Wire,

300V, 12" minimum length

Packaged Weight: 22mm Coil: 0.22 lbs.

30mm Coil: 0.31 lbs.



2-Way N.C., 6 VDC, DIN Spade.

