



M.G.M. ELECTRIC MOTORS BAX SERIES IE3 PREMIUM EFFICIENCY AC INDUCTION MOTOR, GENERAL PURPOSE, INVERTER RATED AND BRAKE, 15HP, 3-PHASE, 230/460 VAC, 1800RPM, TEFC, IEC 160 FRAME, CAST IRON, D-FLANGE/REMOVABLE RIGID BASE (B35) MOUNT. INTEGRATED BRAKE ASSEMBLY INCLUDED

1B34

AutomationDirect.com
1-800-633-0405

	3rd	NOT TO	PART DIMENSIONS MAY DIFFER SLIGHTLY	METRIC UNITS USED	UNLESS OTHERWISE	inch	MODEL	LATEST VERSION	SHEET 1 OF 1
	ANGLE					SCALE			