



M.G.M. ELECTRIC MOTORS BAX SERIES IE3 PREMIUM EFFICIENCY AC INDUCTION MOTOR, GENERAL PURPOSE, INVERTER RATED AND BRAKE, 20HP, 3-PHASE, 230/460 VAC, 1800RPM, TEFC, IEC 160 FRAME, CAST IRON, D-FLANGE/REMOVABLE RIGID BASE (B35) MOUNT. INTEGRATED BRAKE ASSEMBLY INCLUDED

1B36

AutomationDirect.com  
1-800-633-0405



3rd  
ANGLE

NOT TO  
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY  
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED  
FOR PART DESIGN

UNLESS OTHERWISE  
SPECIFIED UNITS ARE:

inch  
[mm]

MODEL  
REV.

LATEST VERSION  
5/14/2026

SHEET 1 OF 1