



FINGER-SAFE, 310A, 1-POLE, LINE SIDE: 1 OPENING ACCEPTS 350 KCMIL TO 3/0 AWG, LOAD SIDE: 2 OPENINGS ACCEPT 2 AWG TO 14 AWG & 5 OPENINGS ACCEPT 6 AWG TO 14 AWG & 4 OPENINGS ACCEPT 8 AWG TO 14 AWG, PANEL OR 35MM DIN RAIL MOUNT.

FTG ENCLOSED TERMINAL BLOCK

38019AL

AutomationDirect.com
1-800-633-0405

	3rd ANGLE	NOT TO SCALE	PART DIMENSIONS MAY DIFFER SLIGHTLY DUE TO MANUFACTURER'S VARIANCES	METRIC UNITS USED FOR PART DESIGN	UNLESS OTHERWISE SPECIFIED UNITS ARE:	mm [inch]	LATEST VERSION 7/23/2024	SHEET 1 OF 1
--	-----------	--------------	---------------------------------------------------------------------	-----------------------------------	---------------------------------------	---------------------	-----------------------------	--------------