

Table of Contents

Chapter 1: Getting Started

Introduction	1-2
The Purpose of this Manual	1-2
Who Should Read this Manual	1-2
Where to Begin	1-2
Supplemental Manuals	1-2
How this Manual is Organized	1-3
Technical Assistance	1-3
What is Remote I/O?	1-4
When Do You Need Remote I/O?	1-4
Number of Masters and Slaves Allowed	1-5
How Does the DL405 Support Remote I/O?	1-5
Distance Between Slaves and Master, Baud Rates	1-6
Remote Master (D4-RM) Features	1-7
Specifications	1-7
Remote Slave (D4-RS or D4-RSDC) Features	1-8
Specifications	1-8
Assigning the Remote Input and Output Addresses	1-9
You Assign the Addresses	1-9
Remote I/O Data Types	1-9
Specify Addresses with Setup Logic	1-9
How the CPU Updates Remote I/O Points	1-10
3 Easy Steps for Setting Up Remote I/O	1-11
Step One: Design the System	1-11
Step Two: Install the Components	1-11
Step Three: Write the Setup Program	1-11
Example Setup Diagram	1-12

Chapter 2: Designing a Remote I/O System

Designing Your System	2-2
Determine I/O Needed and How Many Masters & Slaves	2-2
Define Your Idea By Using Worksheets	2-2
Filling Out the Remote Slave Worksheet for Slave #1	2-3
Filling Out the Remote Slave Worksheet for Slave #2	2-4
Filling Out the Remote Slave Worksheet for Slave #3	2-5
Calculating the Power Budget	2-6
Managing your Power Resource	2-6
CPU Power Specifications	2-6
Module Power Requirements	2-6
Power Budget Calculation Example	2-8
Which Modules Can Go In the Remote Bases	2-9

Chapter 3: Installation & Field Wiring Guidelines

Introduction	3-2
4 Easy Steps:	3-2
Step One: Setting the Front Rotary Switch	3-3
Step Two: Setting the Rear DIP Switches	3-4
Step Three: Inserting the Module in the Base	3-6
Step Four: Connecting the Wiring	3-7
General Wiring Guidelines	3-7
Power Connections for the D4-RS or D4-RSDC	3-7
Cabling Between the Master and Slaves	3-8
Termination Resistors	3-8
Connecting the Run Output Circuit	3-9

Chapter 4: Writing the Setup Program

Getting Started with Your Programming	4-2
Writing Your Remote I/O Setup	4-3
Step 1: Decide How You Are Going to Call Your Program	4-3
Step 2: Write the Setup Logic For Each Remote Base	4-4
Tell the CPU That You Are Finished With the Setup	4-5
A Completed Example	4-6
Special Relays Used for Remote I/O	4-8
How to Use the Special Relays	4-9
C670/C674: Setup Complete (Mandatory)	4-9
C700 to C707 and C720 to C727: Locate Communications Error (Optional)	4-9
C671/C675: I/O Status On Error (Optional)	4-9
C673/C677: Error/Restart But Ignore Problem Area (Optional)	4-10
C710 to C717 and C730 to C737: Communications OK Status (Optional)	4-10
Example of RLL Using All the Special Relays	4-11

Appendix A : Remote I/O Worksheet

Appendix B: Reserved Memory Tables

Remote Input/Output (GX) Addresses	B-2
Standard Input (X) Addresses	B-3
Standard Output (Y) Addresses	B-4
Control Relay (C) Addresses	B-5

Appendix C: Determining I/O Update Time

Overview	C-2
Remote I/O Update Table	C-3
Calculating Total Delay for the System	C-4
Total Delay Time Formulas	C-5
Delay Time Example	C-6