



FINGER-SAFE, 840A, 1-POLE, LINE SIDE: 2 OPENINGS ACCEPT 600 KCMIL TO 4 AWG, LOAD SIDE: 2 OPENINGS ACCEPT 600 KCMIL TO 4 AWG, PANEL OR 35MM DIN RAIL MOUNT, UL 1059 RECOGNIZED.

## FTG ENCLOSED TERMINAL BLOCK

38059

AutomationDirect.com  
1-800-633-0405



3rd  
ANGLE

NOT TO  
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY  
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED  
FOR PART DESIGN

UNLESS OTHERWISE  
SPECIFIED UNITS ARE:

**mm**  
[inch]

LATEST VERSION  
7/23/2024

SHEET 1 OF 1