



FINGER-SAFE, 175A, 1-POLE, LINE SIDE: 1 OPENINGS ACCEPT 2/0 AWG TO 14 AWG CU/AL, LOAD SIDE: 1 OPENINGS ACCEPT 2/0 AWG TO 14 AWG CU/AL, DIN RAIL OR PANEL MOUNT, UL 1953 LISTED.

## PENN UNION OPEN SPLICER/REDUCER BLOCK

ASRB-11-2\_0-1

AutomationDirect.com  
1-800-633-0405



3rd  
ANGLE

NOT TO  
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY  
DUE TO MANUFACTURER'S VARIANCES

INCH UNITS USED FOR  
PART DESIGN

UNLESS OTHERWISE  
SPECIFIED UNITS ARE:

**inch**  
[mm]

LATEST VERSION  
6/25/2024

SHEET 1 OF 1