



Instruktion-Instruction-Instruktionen SC1 D. XX15A

Montering - Mounting - Montage




80 mm min.




DK: Hvis enheden er monteret vandret, skal driftsstrømmen reduceres med 50%

UK: If the unit is mounted horizontally the current must be derated by 50%

DE: Falls Einheit horizontal montiert wird, muss der Strom um 50% reduziert werden




30 mm min.



30 mm min.

Dimensioner - Dimensions - Dimensionen



DK: Køleplade skal holdes ren. Luftstrømmen må ikke blokeres

UK: Keep heatsink clean. Airflow must not be blocked

DE: Kühlflächen freihalten. Luftstrom muss ungehindert fließen


Forbindelse - Wiring - Verdrahtung

75°C Cu Wire/Kabel	mm ²	mm ²
*	1 x 0.75 - 4	1 x 0.5 - 1.5
	2 x 1.0	2 x 0.5 - 0.75
*	1 x 0.75 - 6	1 x 0.5 - 1.5
	2 x 0.75 - 4.5	2 x 0.5 - 1.5
*	1 x 0.75 - 6	1 x 0.5 - 1.5
	2 x 0.75 - 1.5	2 x 0.5 - 1.5
Pozidrive 1 0.5 Nm max.		
4 mm 0.5 Nm max.		3 mm 0.5 Nm max.

* UL Tested

- **Vigtigt** (Overhold max skrue drejningsmomenter)
- **Important:** (Observe the maximum screw torque limits)
- **Wichtig:** (Max. Drehmoment beachten)
Do not connect power factor correction capacitors to the output.

SC1 DX..15A



UL: Use thermal overload protection as required by the National Electric Code.

UL: When protected by a non-time delay K5 or H Class fuse, rated 266 % of motor FLA, this device is rated for use on a circuit capable of delivering not more than 5,000 rms. symmetrical amperes, 600 V maximum.
Maximum surrounding temperature 40°C.

DK: Se specifikationer i datablad

UK: See recommendation in datasheet

DE: Empfehlungen im Datenblatt beachten