



LAUMAS TENSION AND COMPRESSION LOAD CELL, 27550 LB/12500 KG, +/- 0.02% OF FULL SCALE ACCURACY, VOLTAGE SIGNAL RANGE(s) OF 2 MV/V, 3-15 VDC, STAINLESS STEEL, IP68, 32.8FT/10M INTEGRAL 6-WIRE SHIELDED CABLE

**CTL12500**

AutomationDirect.com  
1-800-633-0405



3rd  
ANGLE

NOT TO  
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY  
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED  
FOR PART DESIGN

UNLESS OTHERWISE  
SPECIFIED UNITS ARE:

**mm**  
[inch]

LATEST VERSION  
11/5/2024

SHEET 1 OF 1