


Instruktion-Instruction-Instruktionen-Instructions SC1 / SC 2

Montering - Mounting Montage - Montage




DK: Hvis enheden er monteret vandret, skal driftsstrømmen reduceres med 50%


UK: If the unit is mounted horizontally the current must be derated by 50%

DE: Falls Einheit horizontal montiert wird, muss der Strom um 50% reduziert werden

FR: En cas montage horizontal, réduire le courant de 50%



Dimensioner - Dimensions Dimensionen - Dimensions



DK: Køleplade skal holdes ren. Luftstrømmen må ikke blokeres

UK: Keep heatsink clean. Airflow must not be blocked

DE: Kühlflächen freihalten. Luftstrom muss ungehindert fließen

FR: Maintenir les plaques de refroidissement libres, l'air doit pouvoir circuler


Forbindelse - Wiring - Verdrahtung - Cablage

75°C Cu Wire/Kabel	mm ²	mm ²
	1 x 1.5 - 6	1 x 0.5 - 1.5
	2 x 1.5 - 6	2 x 0.5 - 0.75
	1 x 1.5 - 6	1 x 0.5 - 1.5
	2 x 1.5 - 6	2 x 0.5 - 1.5
	1 x 1 - 10	1 x 0.5 - 1.5
	2 x 1 - 6	2 x 0.5 - 1.5
	Pozidrive 2 1.2 Nm max.	
	6 mm 1.2 Nm max.	3 mm 0.5 Nm max.

* UL Tested

- Vigtigt (Overhold max skruedrejmingsmomenter)
 - Important: (Observe the maximum screw torque limits)
 - Wichtig: (Max. Drehmoment beachten)
- Do not connect power factor correction capacitors to the output.

SC 1 DX



Note


11&12 for UP 62 (termisk beskyttelse) eller andre tilslutninger. Ingen forbindelse til det øvrige kredsløb.

11&12 for UP 62 (thermal overload) or other wiring purposes. Have no internal connection.


11&12 für UP 62 (Thermischer Schutz) oder andere Anschluss Möglichkeiten. Keine interne Verbindung.

Control Voltage:
SC X DD = 5 - 24VDC
SC X DA = 24 - 230VAC/DC

SC 2 DX



SC 2 DX



UL: Use thermal overload protection as required by the National Electric Code.

UL: When protected by a non-time delay K5 or H Class fuse, rated 266 % of motor FLA, this device is rated for use on a circuit capable of delivering not more than 5,000 rms. symmetrical amperes, 600 V maximum. Maximum surrounding temperature 40°C.

DK: Se specifikationer i datablad

UK: See recommendation in datasheet

DE: Empfehlungen im Datenblatt beachten