



ENDRESS+HAUSER PICOMAG LIQUID FLOW METER, MAGNETIC-INDUCTIVE, 1/2IN FEMALE NPT, 0 TO 9.2 GPM, 14 TO 158 DEG F, +/- 3.436E10 LITERS, 20 TO 30,000 µS/cm, OUTPUT: SWITCH, PULSE, ANALOG, DISCRETE INPUT, IO-LINK, OUTPUT 2: SWITCH, ANALOG, DISCRETE INPUT, EPDM RUBBER SEAL(S)

**DMA15-AAADA1**

AutomationDirect.com  
1-800-633-0405



3rd  
ANGLE

NOT TO  
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY  
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED  
FOR PART DESIGN

UNLESS OTHERWISE SPECIFIED UNITS ARE:  
**mm** [inch]

MODEL  
REV.

DRAWING DATE  
12/8/2025

SHEET 1 OF 1