



ENDRESS+HAUSER PICOMAG LIQUID FLOW METER, MAGNETIC-INDUCTIVE, 3/4IN FEMALE NPT, 0 TO 19.8 GPM, 14 TO 158 DEG F, +/- 3.436E10 LITERS, 20 TO 30,000 µS/cm, OUTPUT: SWITCH, PULSE, ANALOG, DISCRETE INPUT, IO-LINK, OUTPUT 2: SWITCH, ANALOG, DISCRETE INPUT, EPDM RUBBER SEAL(S)

DMA20-AAADA1

AutomationDirect.com
 1-800-633-0405

3rd ANGLE	NOT TO SCALE	PART DIMENSIONS MAY DIFFER SLIGHTLY DUE TO MANUFACTURER'S VARIANCES	METRIC UNITS USED FOR PART DESIGN	UNLESS OTHERWISE SPECIFIED UNITS ARE: mm [inch]	MODEL REV.	DRAWING DATE 12/8/2025	SHEET 1 OF 1
-----------	--------------	---------------------------------------------------------------------	-----------------------------------	--------------------------------------------------------	------------	------------------------	--------------