



FINGER-SAFE, 510A, 1-POLE, LINE SIDE: 2 OPENINGS ACCEPT 250 KCMIL TO 4 AWG, LOAD SIDE: 2 OPENINGS ACCEPT 250 KCMIL TO 4 AWG, DIN RAIL OR PANEL MOUNT, UL 1059 RECOGNIZED.

**GLADIATOR ENCLOSED TERMINAL BLOCK**

**GPB2-510P1-2L**

AutomationDirect.com  
1-800-633-0405

	3rd ANGLE	NOT TO SCALE	PART DIMENSIONS MAY DIFFER SLIGHTLY DUE TO MANUFACTURER'S VARIANCES	METRIC UNITS USED FOR PART DESIGN	UNLESS OTHERWISE SPECIFIED UNITS ARE:	<b>mm</b> [inch]	LATEST VERSION 8/5/2024	SHEET 1 OF 1
--	-----------	--------------	---	-----------------------------------	---------------------------------------	---------------------	----------------------------	--------------