



STANDARD DUPLEX  
GFCI RECEPTACLES  
(2X)

6.0  
[0.24]

ACCEPTS  
35MM DIN

ISOMETRIC VIEW

115.0  
[4.53]

32.3  
[1.27]

11.0  
[0.43]

#### GENERAL NOTES :

- 1.) TIGHTENING TORQUE: 4.5 LB-IN (0.51 N.m).
- 2.) WIRE SIZE: 14 - 12AWG (COPPER OR COPPER CLAD).
- 3.) MOUNTING: PANEL (128.0 X 63.5 HOLE DISTANCES); DIN RAIL (35MM WIDE).
- 4.) COMBINED CURRENT CAPACITY OF ALL FOUR OUTLETS.
- 5.) GFCI-PROTECTED (CONNECTED TO THE LOAD SIDE OF GFCI OUTLET).

GLADIATOR QUAD STRAIGHT BLADE RECEPTACLE, 15A, 125 VAC, 1-PHASE, 2-POLE, 3-WIRE, NEMA 5-15, GROUND-FAULT CIRCUIT INTERRUPTION PROTECTION, GLASS FIBER REINFORCED POLYAMIDE HOUSING, BLACK.

**GR-REC4-GFCI**

AutomationDirect.com  
1-800-633-0405



3rd  
ANGLE

NOT TO  
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY  
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED  
FOR PART DESIGN

UNLESS OTHERWISE  
SPECIFIED UNITS ARE:

**mm**  
[inch]

LATEST VERSION  
4/30/2024

SHEET 1 OF 1