



EVER MOTION SOLUTIONS AC OPEN/CLOSED LOOP MICROSTEPPING STEPPER DRIVE, 8A PER PHASE, 2-PHASE OUTPUT, 85-120 VAC (24 VDC PROCESSOR), BIPOLAR, TORQUE, VELOCITY AND POSITION MODE, 200 TO 65536 STEPS PER REVOLUTION, (2) ETHERNET 100BASE-TX (RJ45) AND (1) RJ11 PORT(S)

**SW5A5080H221-30C0680**

AutomationDirect.com  
1-800-633-0405



3rd  
ANGLE

NOT TO  
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY  
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED  
FOR PART DESIGN

UNLESS OTHERWISE  
SPECIFIED UNITS ARE:

mm  
[inch]

LATEST VERSION  
2/4/2025

SHEET 1 OF 1