



SECTION A-A



$\phi 25.00^{+0.009}_{-0.004}$   
 $[0.984^{+0.0004}_{-0.0002}]$

M10-1.5  
 $\nabla 16.0[0.629]$   
 THREAD  
 (BOTH ENDS)

HARDWARE INCLUDED	
TYPE	QTY
SPACER: 34.0 OD X 25.7 ID X 3.75T	2
ROUNDED KEY: 8.0W X 7.0 T X 25.0 LONG	2
ROUNDED KEY: 8.0W X 7.0 T X 40.0 LONG	2
RETAINING RING: FREE $\phi 23.1$ X 1.1 THICK	2

# IRONHORSE GEARBOX BOUBLE OUTPUT SHAFT

WGA-63M-D-IEC

AutomationDirect.com  
 1-800-633-0405



3rd  
ANGLE

NOT TO  
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY  
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED  
FOR PART DESIGN

UNLESS OTHERWISE  
SPECIFIED UNITS ARE:

**mm**  
[inch]

LATEST VERSION  
1/2/2025

SHEET 1 OF 1