

# Index

---

## Numbers

10BaseFL, 2–17  
10BaseT, 2–17  
62.5/125 MMF, 2–17

## A

ACT LED, 4–4  
Advanced Settings, 2–11  
Aliases, 3–6

## B

Bulletin Board Service, 1–3

## C

Cables, 2–17  
    10BaseFL, 2–18  
    10BaseT, 2–17  
    crossover, 2–17  
    distance limitations, 2–18  
    fiber optic, 2–18  
    length, 2–19  
    patch, 2–17  
    recommended 10BaseT, 2–18  
    straight-through, 2–17  
Communication status bits  
    busy, 3–11  
    error, 3–11  
Configuration box, 2–11

## Connectors

10BaseFL, 2–17  
10BaseT, 2–17  
RJ45, 2–17  
ST bayonet, 2–17

CPU, use with ECOM, 2–11, 2–13, 2–14, 2–20

## D

Data types, 3–7  
DSDData Server, 1–6  
DIP switch  
    H2-ECOM (-F), 2–5, 2–17  
    H4-ECOM (-F), 2–6

## *Direct*SOFT32

for setting Network Identifiers, 2–12  
programming software, 1–4

## E

ECOM Module, inserting in PLC base, 2–13  
ECOM Modules, maximum number, 2–20  
ERROR LED, 4–4  
Ethernet, 1–6  
    address, 2–2, 2–9, 2–10, 2–11  
    standards, A–3  
    stats box, 2–10  
Expansion bases, 2–14

## F

Fiber Optic, cables, 2–18  
Flash memory, 2–11

---

## H

Hubs, 2–16

## I

Interlocks, for RX/WX instructions, 3–17

IP Address, 2–2, 2–10, 2–11

## L

LEDs, for troubleshooting, 4–2

Link, 2–2

LINKGD, 4–4

Load Address instruction, 3–3

Load instruction, 3–3

Local expansion bases, 2–14

## M

Memory Types, 3–6

Module ID, 2–2, 2–10, 2–11

Module Information Box, 2–10

Multimode Fiber Optic, 2–17, 2–18

Multiple Read and Write Instructions, 3–17

## N

Name identifier, 2–2, 2–10

NetEdit

features, 2–8

running, 2–7

setting Network Identifiers, 2–10

troubleshooting, 4–5

Network, 2–2, 2–15

cabling, 2–17

identifiers, 2–2

layouts, 2–11, 2–15

table of identifiers, 2–11

## O

Octal numbering system, 3–6

## P

Patch cable, 2–17

PLC-to-PLC Communications, 2–10, 3–2

Power budget, 2–13

Programming Examples

multiple Read/Write instructions, 3–17

one Read instruction, 3–13

one Write instruction, 3–15

Protocols, 1–6

adding in your PC, 2–9

IPX, 2–8

UDP/IP, 2–8

## Q

Query Network, 2–9

## R

Read/Write instructions, 3–2, 3–3

References, 1–2

Repeaters, 2–16

RJ45, 2–17

RLL, 3–2

## S

Sequencing

RX/WX instructions, 3–17

using control relays, 3–17

using shift register, 3–17, 3–20

Slot 0, 2–13

Slot table

H2-ECOM, 2–13

H4-ECOM, 2–14

Special Relays, 3–10

Specifications, A–2

ST, connectors, 2–17

---

## **T**

### Tables

- data types, 3–7
- network identifiers, 2–11
- special relays, 3–10
- usable slots, 2–13, 2–14

Technical support, 1–2

Topology, 2–15

- star, 2–15

### Troubleshooting

- chart, 4–2
- using diagnostic LEDs, 4–2, 4–4

Truth table, 3–17

## **U**

Update Module, 2–10

## **W**

Web site, 1–2

---