


- C) CONNECT THE 1485V1 KIT TO ENCLOSURE USING 1/4 20 SCREWS AND NUTS (PARTS 5 & 1) THROUGH CLAMP (PART 4), ADAPTER PLATE (PART 2), GASKET (PART 3), AND ENCLOSURE. DO NOT TIGHTEN COMPLETELY UNTIL STEP D IS COMPLETE. IF 1485V2 IS USED SEE STEP D.
- D) CONNECT THE BODY (PART 7) TO THE FLANGE ON THE MATING WIREWAY USING 1/4 - 20 X .75 HEX HD. SCREWS AND 1/4 - 20 KEP NUTS (PARTS 5 & 1) PROVIDED. IF 1485V2 IS USED IGNORE STEP C AND ASSEMBLE USING 1/4 - 20 HARDWARE THROUGH CLAMP (PART 4), ADAPTER PLATE (PART 2), GASKET (PART 3) AND MATING WIREWAY.
- E) ONCE THE SWIVEL BODY AND ADAPTER PLATES ARE ALIGNED TO MATING COMPONENTS. TIGHTEN THE CLAMPS DOWN TO FIX THE POSITION OF THE SQIVEL ASEMBLY.



5 OR 8 1/4 - 20 KEP NUT 1 2 CONNECTOR PLATE (1485V1) 1 3 3 SOLID FLANGE GASKET 4 4 CLAMPS 5 4 OR 7 1/4 - 20 X 3/4 HEX CAP SCREW ADAPTER PLATE 6 1 7 1485 V SWIVEL NIPPLE BODY 1

PAGE 1 OF 1