



# TABLE OF CONTENTS

---

## Chapter 1 - Introduction

<b>Introduction</b> .....	1-2
The Purpose of this Manual.....	1-2
Other Reference Materials .....	1-2
Who Should Read this Manual .....	1-2
Quality Technical Support.....	1-3
<b>Conventions Used</b> .....	1-3
Key Topics for Each Chapter.....	1-3
ECOM Module Introduction.....	1-4
ECOM Communication Possibilities.....	1-4
Your Network PC .....	1-5
<b>Frequently Asked Questions</b> .....	1-6

## Chapter 2 - Setup and Installation

<b>ECOM Network Identifiers</b> .....	2-2
Module ID.....	2-3
Name.....	2-3
Example: .....	2-4
Ethernet (MAC) Address.....	2-4
Using Multiple Network Identifies .....	2-4
<b>Setting the Module ID with the DIP Switch</b> .....	2-5
H0 / H2 Series ECOM DIP Switch.....	2-6
H4 Series ECOM DIP Switch.....	2-7
<b>Inserting the ECOM Module in the PLC Base</b> .....	2-8
H0 Series ECOM Module Installation .....	2-8
DL205 Slot Choices .....	2-8
H2 Series ECOM Module.....	2-9
DL405 Slot Choices.....	2-10
H4 Series ECOM.....	2-11

<b>ECOM Network Layouts .....</b>	<b>2-11</b>
<b>Network Cabling.....</b>	<b>2-13</b>
ECOM Supports Two Standards .....	2-13
10/100BaseT Networks .....	2-13
10/100BaseT Connections.....	2-14
UTP Cable .. .....	2-14
10BaseFL Connections.....	2-14
Fiber Optic Cable .....	2-14
Fiber Optic Module ST Connector.....	2-14
<b>Maximum Cable Length.....</b>	<b>2-15</b>
10/100BaseT Distance Limitations.....	2-15
10BaseFL Distance Limitations.....	2-15
<b>Maximum Number of ECOM Modules on the Network .....</b>	<b>2-16</b>

## Chapter 3 - Configuring ECOMs Using NetEdit3

<b>NetEdit3 Software .....</b>	<b>3-2</b>
Installing NetEdit3.....	3-2
Launching NetEdit3.....	3-3
The NetEdit3 Screen.....	3-3
Adding Network Protocol Support to the NetEdit3 PC.....	3-4
Using NetEdit3 .....	3-5
Ethernet Communication Protocol .....	3-5
Ethernet Address .....	3-6
Module Type, IP Address and ID .....	3-6
Module Info> General Information .....	3-7
Module Info> Ethernet Stats.....	3-7
ECOM Settings.....	3-7
ECOM Settings> Configuration> General .....	3-8
ECOM Settings> Configuration> Advanced .....	3-9
ECOM Settings> Configuration> Peer to Peer.....	3-10
ECOM Settings> Utils>Test CPU Access.....	3-12
ECOM Settings> Firmware .....	3-12
FileMenu> Live Update.....	3-13
F / B / C Columns .....	3-13

## Chapter 4 - RLL Programming for Communications

PLC-to-PLC Communications.....	4-2
How RLL is Used for Communications.....	4-2
<b>Network Instructions</b> .....	<b>4-3</b>
Read (RX) and Write (WX) Instructions.....	4-3
Building the Read (RX) and Write (WX) Routine.....	4-3
The First LD Instruction.....	4-3
The Second LD Instruction.....	4-4
The LDA Instruction.....	4-4
Read (WX) Instruction.....	4-5
Write (WX) Instruction.....	4-5
<b>Addressing the Different Memory</b> .....	<b>4-6</b>
Bit Memory.....	4-6
Word Memory and Aliases.....	4-6
<b>DirectSOFT</b> is Flexible.....	4-7
DL05 CPU.....	4-7
DL06 CPU.....	4-7
D2-240 CPU.....	4-8
D2-250-1 CPU.....	4-8
D2-260/D2-262 CPU.....	4-9
D4-430 CPU.....	4-9
D4-440 CPU.....	4-10
D4-450/D4-454 CPU.....	4-10
<b>Special Relays for Communications</b> .....	<b>4-11</b>
<b>Program with One Read Instruction</b> .....	<b>4-13</b>
Program for the Initiating PLC.....	4-13
Program for the Responding PLC.....	4-13
<b>Example Program with One Write Instruction</b> .....	<b>4-15</b>
Program for the Initiating PLC.....	4-15
Program for the Responding PLC.....	4-15
<b>Integrating Multiple Read and Write Instructions</b> .....	<b>4-17</b>
Interlocking Relays.....	4-17
First RX/WX Instruction.....	4-18

Second RX/WX Instruction .....	4-19
Third RX/WX Instruction .....	4-19
Shift Register .....	4-20
Store If Equal.....	4-20
First RX/WX Instruction .....	4-21
Second RX/WX Instruction .....	4-21
Third RX/WX Instruction .....	4-21

## Chapter 5 - Modbus TCP for H0/H2/H4-ECOM100

<b>Modbus TCP</b> .....	<b>5-2</b>
Client / Server Model .....	5-2
Protocol Description.....	5-2
<b>Supported Modbu Function Codes</b> .....	<b>5-4</b>
<b>Network Server (Slave) Operation</b> .....	<b>5-5</b>
Modbus Function Codes Supported .....	5-5
Determining the Modbus Address.....	5-5
If Your Host Software or Client Requires the Data Type and Address.....	5-6
Example 1: V2100.....	5-11
Example 2: Y20 .....	5-11
Example 3: T10 Current Value.....	5-11
Example 4: C54.....	5-12
If the Host Software or Client Requires an Address ONLY .....	5-12
Example 1: V2100.....	5-14
Example 2: Y20 .....	5-14
Example 3: C54.....	5-14
<b>Network Client (Master) Operation</b> .....	<b>5-15</b>
PLC Memory Supported for Client Operation.....	5-17
Example 1: Calculating Word PLC Address .....	5-18
Example 2: Calculating Discrete Input PLC Address.....	5-18
Building the Read (RX) or Write (WX) Routine.....	5-19
Step 1: Identify ECOM Slot Location and Server Node #.....	5-19
Step 2: Load Number of Bytes to Transfer.....	5-20
Step 3: Specify Master Memory Area.....	5-20
Step 4: Specify Slave Memory Area .....	5-20
Communications from a Ladder Program.....	5-21

Multiple Read and Write Interlocks..... 5-21  
 ECOM100 IBOX ..... 5-22  
 Modbus TCP Setup ..... 5-24  
 Example Modbus TCP Program..... 5-26  
 Troubleshooting:..... 5-26  
**H0/H2/H4 -ECOM100 System Memory ..... 5-30**

## Chapter 6 - H0/H2/H4-ECOM100 DHCP & HTML Configuration

**H0/H2/H4 -ECOM100 DHCP ..... 6-2**  
 DHCP Issues ..... 6-2  
 Disabling DHCP and Assigning a Static IP Address ..... 6-2  
**Using HTML Configuration ..... 6-3**  
 Connecting to the H0/H2/H4 -ECOM100 ..... 6-3  
 H0/H2/H4-ECOM100 Client Peer to Peer Configuration..... 6-5

## Chapter 7 - Maintenance and Troubleshooting

**Isolating a Communication Problem ..... 7-2**  
 Diagnostic Tools and Techniques ..... 7-2  
**Troubleshooting Chart ..... 7-2**  
**ECOM Module Diagnostic LEDs ..... 7-4**  
 H0 Series Indicators..... 7-4  
 OK Indicator..... 7-4  
 LINK Indicator ..... 7-4  
 ACT Indicator ..... 7-4  
 ERR Indicator ..... 7-4  
 100MBIT Indicator ..... 7-4  
**Network Server (Slave) Operation..... 7-5**  
 H24-ECOM-(F) Indicators ..... 7-5  
 LINKGD Indicator ..... 7-5  
 ACT Indicator ..... 7-5  
 ERROR Indicator ..... 7-5  
 H2/H4-ECOM100 Indicators..... 7-6  
 STATUS ..... 7-6  
 LINKGD Indicator ..... 7-6

## Table of Contents

---

ACTIVE Indicator .....	7-6
ERROR Indicator .....	7-6
100MBIT Indicator .....	7-6
<b>Using NetEdit3 for Troubleshooting.....</b>	<b>7-7</b>
Select a Module .....	7-7
Module Information .....	7-7
Change Protocol .....	7-8
Ethernet Stats.....	7-8
RX/WX Settings.....	7-9
Record the Module Settings.....	7-9
<b>Replacing the ECOM Module.....</b>	<b>7-10</b>
<b>Diagnosing Network Cable Problems.....</b>	<b>7-11</b>

## Appendix A - General Specifications

General Specifications .....	A-2
ECOM Specifications .....	A-2
Ethernet Standards.....	A-4

## Appendix B - Peerlink Specifications

Peerlink Function for ECOM100 .....	B-2
Peerlink Data-Sharing Network .....	B-3
Configuration .....	B-4
Parameters: .....	B-5
DL05 .....	B-6
DL06 .....	B-7
DL205 .....	B-8
DL405 .....	B-9
Do-more .....	B-10
Block Summary .....	B-11