

1) Sensing surface, 2) Housing, 3) Cover, 4) Potentiometer, 5) LED function indicator



### Basic features

Approval/Conformity	CE cULus WEEE
Basic standard	IEC 60947-5-2
Scope of delivery	Nut (2x)
Sensitivity	Switching distance adjustable
Series	M18

### Electrical connection

Connection	M12x1-Male, 4-pin, A-coded
Polarity reversal protected	yes
Protection against device mix-ups	yes
Short-circuit protection	yes

### Electrical data

Operating voltage $U_b$	10...35 VDC
Rated insulation voltage $U_i$	75 V DC
Rated operating current $I_e$	300 mA
Ripple max. (% of $U_e$ )	10 %
Switching frequency	100 Hz
Utilization category	DC -13
Voltage drop static max.	1.5 V

### Environmental conditions

Ambient temperature	-30...70 °C
IP rating	IP67

### Functional safety

MTTF (40 °C)	300 a
--------------	-------

### Interface

Switching output	PNP normally open (NO)
------------------	------------------------

### Material

Cover material	PA
Housing material	1.4301 stainless steel
Material sensing surface	PTFE

### Mechanical data

Dimension	Ø 18 x 75 mm
Installation	non-flush
Size	M18x1
Thread (A)	M18x1
Tightening torque	60 Nm

### Range/Distance

Hysteresis H max. (% of $S_r$ )	15.0 %
Measuring range	2...15 mm
Rated operating distance $S_n$	15 mm
Repeat accuracy max. (% of $S_r$ )	2.0 %
Temperature drift max. (% of $S_r$ )	15 %

Capacitive Sensors  
**BCS M18T4G2-PSC15G-S04G**  
Order Code: BCS006A



Remarks


The potentiometer does not have a fixed stop, but can be turned endlessly without destroying anything.  
If no change in the switching signal is detected, the potentiometer should be turned forwards or backwards until a signal change occurs at the output.  
For more information about MTTF and B10d see MTTF / B10d Certificate

Indication of the MTTF- / B10d value does not represent a binding composition and/or life expectancy assurance; these are simply experiential values with no warranty implications. These declared values also do not extend the expiration period for defect claims or affect it in any way.


Connector Drawings



Wiring Diagrams



Installation remarks



1) Machine GND