

# DATA SHEET

Premium Efficiency Motor: **MTSP-002-3BD18R**

**60 Hz**

Document Generated: 22-Sep-2021

Document ID:

Customer:

## MOTOR INFORMATION

HP	2
RPM	1800
Phase	3
Frequency	60
Voltage	230/460
Frame Size	56C
Enclosure	TEFC
Degree of Protection	IP69K
Service Factor	1.15
Poles	4
Full Load Speed	1750
Insulation Class	F
Temp Rise	80°C
NEMA Code Letter	L
Duty Cycle	S1
Slip	2.78%
NEMA Design	B
Moment of Inertia	0.184 lb.ft.^2
Locked Rotor Time (Hot)	12 seconds
Sound Pressure Level	61 dB(A)
Number of Starts	12
Max Ambient Temperature	40° C
Max Elevation	1000 m.a.s.l (3300 f.a.s.l)
Mounting	F1
Rotation	Bidirectional
Area of Classification	Div.2 Class I, Gr. A,B,C&D T2B
Inverter Rating	10:1 CT/20:1 VT
Standard	NEMA MG1, UL1004
Approvals	CSA,UL,CE

## EFFICIENCY/POWER FACTOR

LOAD	EFF	P. F.
100%	86.5 %	0.78
75%	83.0 %	0.66
50%	80.0 %	0.52

## TORQUE

FULL LOAD	LRT	BDT
5.9 lb.ft.	285 %	300 %

## AMPERAGE INFORMATION


	230V	460V
Full Load Amps	6	3
Locked Rotor Amps	50	25
No Load Current	3.5	1.75
Usable at 208V	6	

## BEARING INFORMATION

DE Bearing	6205 2RS
ODE Bearing	6205 2RS
Grease Type	Mobil Polyrex EM
DE Regreasing Interval	-- Hours
ODE Regreasing Interval	-- Hours
Grease Quantity	--

## ADDITIONAL DATA

F2 Suitable	No
Shaft Material	304 Stainless Steel
Connection Diagram	9 Lead 2Y/Y
Approximate Weight	50 lbs.



**DIMENSIONS - INCHES**

C	T	P	BC	AB	FLANGE				
					AK	BD	AJ	BF	BB
13.75	--	6.95	-0.19	5.95	4.5	6.45	5.875	(4)3/8-16	0.16

SHAFT & KEY					
S	ES	R	N-W	U	AH
0.188	1.41	0.517	1.88	0.625	2.06

TERMINAL BOX				
AA	AB	AC	RD	BV
1/2	5.95	4.5	3.45	6.95

# PERFORMANCE CURVES


Premium Efficiency Motor: **MTSP-002-3BD18R**

Document Generated: 22-Sep-2021  
 Document ID:

Customer:

Motor Type	MTS		FL Speed	1750	
Output Rating (HP)	2		LRT (%FLT)	285	460 volt FLA 3
Full Load Torque	5.9	lb.ft	BDT (%FLT)	300	230 volt FLA 6
Rotor Wk <sup>2</sup>	0.184	lb-ft <sup>2</sup>			

SPEED VS TORQUE & CURRENT CURVE



OUTPUT VS EFF., P.F. & CURRENT CURVE

