
General Specifications			
Operating Temperature		0° to 60° C (32° to 140° F)	
Storage Temperature		-20° to 85° C (-4° to 185° F)	
Humidity		5 to 95% (non-condensing)	
Environmental Air		No corrosive gases permitted	
Vibration		IEC60068-2-6 (Test Fc)	
Shock		IEC60068-2-27 (Test Ea)	
Enclosure Type		Open Equipment	
Agency Approvals		UL61010-2 - UL File # E185989 Canada and USA	
		CE Compliant EN61131-2*	
Noise Immunity		NEMA ICS3-304	
EU Directive		See the "EU Directive" topic in the Help File	
Weight	BX-12CD3D1	93g (3.3 oz)	
	BX-16CD3D1	94g (3.3 oz)	
Software Version		Do-more! Designer 2.0 or later	


*Meets EMC and Safety requirements. See the D.O.C. for details.

I/O Wiring

Sinking Input



Sourcing Input




Discrete Input Specifications			
Input Type		Sink/Source	
Inputs per Module		8	
Commons	BX-12CD3D1	2 (4 points/common) Isolated	
	BX-16CD3D1	2 (4 points/common) Isolated	
Nominal Voltage Range		12–24 VDC	
Input Voltage Range		9–30 VDC	
Maximum Voltage		30VDC	
Input Impedance		3kΩ @ 24VDC	
Input Current (typical)		8mA @ 24VDC	
Maximum Input Current		12mA @ 30VDC	
ON Voltage Level		> 9.0 VDC	
OFF Voltage Level		< 2.0 VDC	
Status Indicators		Logic Side, Green	

Discrete Output Specifications			
Outputs Type		Sinking	
	BX-12CD3D1	4	
Outputs per Module	BX-16CD3D1	8	
	BX-12CD3D1	1 (4 points/common)	
Commons	BX-16CD3D1	2 (4 points/common) Isolated	
Maximum Current per Common		2A	
Nominal Voltage Range		12–24 VDC	
Operating Voltage Range		5–36 VDC	
Maximum Voltage		36VDC	
Minimum Output Current		0.1 mA @ 24VDC	
Maximum Output Current		0.5 A per output, no derating over temperature range	
Maximum Leakage Current		10µA	
Status Indicators		Logic Side, Green	

AUTOMATION DIRECT BRX Expansion Module





BX-12CD3D1 Combination Discrete Module

In - 8-pt, 12-24 VDC, Sink/Source, Out - 4-pt, 12-24 VDC, Sinking **BX-16CD3D1** Combination Discrete Module In – 8-pt, 12–24 VDC, Sink/Source, Out – 8-pt, 12–24 VDC, Sinking

I/O Terminal Blocks sold separately. (See Terminal Block Connection Options tables).

WARNING: To minimize the risk of potential safety problems, you should follow all applicable local and national codes that regulate the installation and operation of your equipment. These codes vary from area to area and it is your responsibility to determine which codes should be followed, and to verify that the equipment, installation, and operation are in compliance with the latest revision of these codes.

Equipment damage or serious injury to personnel can result from the failure to follow all applicable codes and standards. We do not guarantee the products described in this publication are suitable for your particular application, nor do we assume any responsibility for your product design, installation, or operation.

İf you have any questions concerning the installation or operation of this equipment, or if you need additional information, please call Technical Support at 770-844-4200.

This publication is based on information that was available at the time it was printed. At AutomationDirect.com[®] we constantly strive to improve our products and services, so we reserve the right to make changes to the products and/or publications at any time without notice and without any obligation. This publication may also discuss features that may not be available in certain revisions of the product.

Do-more BRX Manual available at http://www.automationdirect.com/pn/doc/manual/ BX-USER-M



IMPORTANT!

\wedge	
<u> </u>	Note

Hot-Swapping Information Note: This device cannot be Hot Swapped.

Document Name	Edition/Revision	Date
BX-xxCD3D1	1st Ed. RevE	11/3/2020


Copyright 2021, AutomationDirect.com Incorporated/All Rights Reserved Worldwide.

Your Automation Foundation!™


Connector	Options — 12 point
BX-RTB08	Terminal Block Kit, 90-degree screw type. For use with BRX 5-point, 8-point, and 12-point expansion modules. Kit includes (3) 5-pin 5mm plugs.
BX-RTB08-1	Terminal Block Kit, 180-degree spring clamp type. For use with BRX 5-point, 8-point, and 12-point expansion modules. Kit includes (3) 5-pin 5mm plugs.
BX-RTB08-2	Terminal Block Kit, 180-degree screw type. For use with BRX 5-point, 8-point, and 12-point expansion modules. Kit includes (3) 5-pin 5mm plugs.
ZL-BXEM-CBL15	ZIP Link PLC I/O cable, 15-position terminal block to 24-pin connector, 24AWG, cable length 0.5meter (1.6ft). For use with 5-point and 12-point BRX expansion modules.
ZL-BXEM-CBL15-1	ZIP Link PLC I/O cable, 15-position terminal block to 24-pin connector, 24AWG, cable length 1meter (3.3ft). For use with 5-point and 12-point BRX expansion modules.
ZL-BXEM-CBL15-2	ZIP Link PLC I/O cable, 15-position terminal block to 24-pin connector, 24AWG, cable length 2meter (6.6ft). For use with 5-point and 12-point BRX expansion modules.
ZL-BXEM-CBL15-1P	ZIP Link PLC I/O cable, 15-position terminal block to pigtail connection, 24AWG, cable length 1meter (3.3ft). For use with 5-point and 12-point BRX expansion modules.
ZL-BXEM-CBL15-2P	ZIP Link PLC I/O cable, 15-position terminal block to pigtail connection, 24AWG, cable length 2meter (6.6ft). For use with 5-point and 12-point BRX expansion modules.
ZL-RTB20	ZIPLink Two Level Feedthrough Module, 20-pole, 35mm, DIN mount.
ZL-RTB20-1	ZIPLink Three Level Feedthrough Module, 20-pole, 35mm, DIN mount.


I/O Wiring





Connector	Options – 16 point
BX-RTB10	Terminal Block Kit, 90-degree screw type. For use with BRX 10-point PLCs and BRX 16-point expansion modules.Kit includes (2) 10-pin 3.8mm plugs.
BX-RTB10-1	Terminal Block Kit, 180-degree spring clamp type. For use with BRX 10-point PLCs and BRX 16-point expansion modules.Kit includes (2) 10-pin 3.8mm plugs.
BX-RTB10-2	Terminal Block Kit, 180-degree screw type. For use with BRX 10-point PLCs and BRX 16-point expansion modules.Kit includes (2) 10-pin 3.8mm plugs.
ZL-BXEM-CBL20	ZIP Link PLC I/O cable, 20-position terminal block to 24-pin connector, 24AWG, cable length 0.5meter (1.6ft). For use with 16-point BRX expansion modules.
ZL-BXEM-CBL20-1	ZIP Link PLC I/O cable, 20-position terminal block to 24-pin connector, 24AWG, cable length 1meter (3.3ft). For use with 16-point BRX expansion modules.
ZL-BXEM-CBL20-2	ZIP Link PLC I/O cable, 20-position terminal block to 24-pin connector, 24AWG, cable length 2meter (6.6ft). For use with 16-point BRX expansion modules.
ZL-BXEM-CBL20-1P	ZIP Link PLC I/O cable, 20-position terminal block to pigtail connection, 24AWG, cable length 1meter (3.3ft). For use with 16-point BRX expansion modules.
ZL-BXEM-CBL20-2P	ZIP Link PLC I/O cable, 20-position terminal block to pigtail connection, 24AWG, cable length 2meter (6.6ft). For use with 16-point BRX expansion modules.
ZL-RTB20	ZIPLink Two Level Feedthrough Module, 20-pole, 35mm, DIN mount.
ZL-RTB20-1	ZIPLink Three Level Feedthrough Module, 20-pole, 35mm, DIN mount.





12 point Term			
Part Number	BX-RTB08	BX-RTB08-1	BX-RTB08-2
Connector Type	Screw Type-90°	Spring Clamp Type-180°	Screw Type-180°
Wire Exit	180°	180°	180°
Pitch	5.0mm	5.0mm	5.0mm
Screw Size	M2.5	N/A	M2.5
Recommended Screw torque	< 3.98 lb∙in (0.45 N∙m)	N/A	< 3.98 lb∙in (0.45 N⋅m)
Screwdriver Blade Width	3.5mm	3.5mm	3.5mm
Wire Gauge (Single Wire)	28-12 AWG	28-14 AWG	28-12 AWG
Wire Gauge (Two Wires)	28-16 AWG	28-16 AWG (Dual Wire Ferrule Required)	28-16 AWG
Wire Strip Length	0.3in (7.5mm)	0.37in (9.5mm)	0.3in (7.5mm)
Equiv. Dinkle part #	5ESDV-05P-BK	5ESDSR-05P-BK	5ESDF-05P-BK
16 point Term	inal Block C	onnector Specific	ations
Part Number	BX-RTB10	BX-RTB10-1	BX-RTB10-2
Connector Type	Screw Type-90°	Spring Clamp Type-180°	Screw Type-180°
Wire Exit	180°	180°	180°
Pitch	3.81mm	3.81mm	3.81mm
Screw Size	M2	N/A	M2
Recommended Screw torque	<1.77 lb·in (0.2 N·m)	N/A	<1.77 lb∙in (0.2 N⋅m)
Screwdriver Blade Width	2.5mm	2.5mm	2.5mm
Wire Gauge (Single Wire)	28-16 AWG	28-18 AWG	30-16 AWG
Wire Gauge (Two Wires)	28-18 AWG	30-20 AWG (Dual Wire Ferrule Required)	30-18 AWG

www.do-moreplcs.com

0.35in (9mm)

ESC381V-10-BK

0.26in (6.5mm)

EC381F-10P-BK

0.24in (6mm)

EC381V-10P-BK

Wire Strip Length

Equiv. Dinkle part #