

General Specifications Operating Temperature 0° to 60° C (32° to 140° F) -20° to 85° C (-4° to 185° F) Storage Temperature Humidity 5 to 95% (non-condensing) Environmental Air No corrosive gases permitted Vibration IEC60068-2-6 (Test Fc) Shock IEC60068-2-27 (Test Ea) **Enclosure Type** Open Equipment UL61010-2 - UL File # E185989 Canada and USA Agency Approvals CE Compliant EN61131-2* Noise Immunity NEMA ICS3-304 **EU** Directive See the "EU Directive" topic in the Help File BX-12CD3D2 93g (3.3 oz) Weight BX-16CD3D2 94g (3.3 oz) Software Version Do-more! Designer 2.0 or later

I/O Wiring

Sinking Input



Sourcing Input




Discrete Input Specifications		
Input Type		Sink/Source
Inputs per Module		8
Commons	BX-12CD3D2	2 (4 points/common) Isolated
	BX-16CD3D2	2 (4 points/common) Isolated
Nominal Voltage Range		12–24 VDC
Input Voltage Range		9–30 VDC
Maximum Voltage		30VDC
Input Impedance		3kΩ @ 24VDC
Input Current (typical)		8mA @ 24VDC
Maximum Input Current		12mA @ 30VDC
ON Voltage Level		> 9.0 VDC
OFF Voltage Level		< 2.0 VDC
Status Indicators		Logic Side, Green

Discrete Output Specifications			
Outputs Type		Sourcing	
	BX-12CD3D2	4	
Outputs per Module	BX-16CD3D2	8	
	BX-12CD3D2	1 (4 points/common)	
Commons	BX-16CD3D2	2 (4 points/common) Isolated	
Maximum Current per Common		2A	
Nominal Voltage Range		12–24 VDC	
Operating Voltage Range		5–36 VDC	
Maximum Voltage		36VDC	
Minimum Output Current		0.1 mA @ 24VDC	
Maximum Output Current		0.5 A per output, no derating over temperature range	
Maximum Leakage Current		10μΑ	
Status Indicators		Logic Side, Green	

VAUTOMATION DIRECT

BRX

Expansion Module



BX-12CD3D2

Combination Discrete Module In – 8-pt, 12–24 VDC, Sink/Source, Out – 4-pt, 12–24 VDC, Sourcing



BX-16CD3D2

Combination Discrete Module In – 8-pt, 12–24 VDC, Sink/Source, Out – 8-pt, 12–24 VDC, Sourcing

I/O Terminal Blocks sold separately.

(See Terminal Block Connection Options tables).

WARNING: To minimize the risk of potential safety problems, you should follow all applicable local and national codes that regulate the installation and operation of your equipment. These codes vary from area to area and it is your responsibility to determine which codes should be followed, and to verify that the equipment, installation, and operation are in compliance with the latest revision of these codes.

Equipment damage or serious injury to personnel can result from the failure to follow all applicable codes and standards. We do not guarantee the products described in this publication are suitable for your particular application, nor do we assume any responsibility for your product design, installation, or operation.

If you have any questions concerning the installation or operation of this equipment, or if you need additional information, please call Technical Support at 770-844-4200.

This publication is based on information that was available at the time it was printed. At AutomationDirect.com® we constantly strive to improve our products and services, so we reserve the right to make changes to the products and/or publications at any time without notice and without any obligation. This publication may also discuss features that may not be available in certain revisions of the product.

Do-more BRX Manual available at http://www.automationdirect.com/pn/doc/manual/ BX-USER-M



IMPORTANT!



Hot-Swapping Information

Note: This device cannot be Hot Swapped.

Document Name	Edition/Revision	Date
BX-xxCD3D2	1st Ed. RevF	11/3/2020


Copyright 2021, AutomationDirect.com Incorporated/All Rights Reserved Worldwide.

^{*}Meets EMC and Safety requirements. See the D.O.C. for details


Connector	Options — 12 point		
BX-RTB08	Terminal Block Kit, 90-degree screw type. For use with BRX 5-point, 8-point, and 12-point expansion modules. Kit includes (3) 5-pin 5mm plugs.		
BX-RTB08-1	Terminal Block Kit, 180-degree spring clamp type. For use with BRX 5-point, 8-point, and 12-point expansion modules. Kit includes (3) 5-pin 5mm plugs.		
BX-RTB08-2	Terminal Block Kit, 180-degree screw type. For use with BRX 5-point, 8-point, and 12-point expansion modules. Kit includes (3) 5-pin 5mm plugs.		
ZL-BXEM-CBL15	ZIPL ink PLC I/O cable, 15-position terminal block to 24-pin connector, 24AWG, cable length 0.5meter (1.6ft). For use with 5-point and 12-point BRX expansion modules.		
ZL-BXEM-CBL15-1	ZIPL ink PLC I/O cable, 15-position terminal block to 24-pin connector, 24AWG, cable length 1meter (3.3ft). For use with 5-point and 12-point BRX expansion modules.		
ZL-BXEM-CBL15-2	ZIPLink PLC I/O cable, 15-position terminal block to 24-pin connector, 24AWG, cable length 2meter (6.6ft). For use with 5-point and 12-point BRX expansion modules.		
ZL-BXEM-CBL15-1P	ZIPLink PLC I/O cable, 15-position terminal block to pigtail connection, 24AWG, cable length 1meter (3.3ft). For use with 5-point and 12-point BRX expansion modules.		
ZL-BXEM-CBL15-2P	ZIPLink PLC I/O cable, 15-position terminal block to pigtail connection, 24AWG, cable length 2meter (6.6ft). For use with 5-point and 12-point BRX expansion modules.		
ZL-RTB20	ZIPLink Two Level Feedthrough Module, 20-pole, 35mm, DIN mount.		
ZL-RTB20-1	ZIPLink Three Level Feedthrough Module, 20-pole, 35mm, DIN mount.		

I/O Wiring

Sourcing Output




Connector Options — 16 point		
BX-RTB10	Terminal Block Kit, 90-degree screw type. For use with BRX 10-point PLCs and BRX 16-point expansion modules.Kit includes (2) 10-pin 3.8mm plugs.	
BX-RTB10-1	Terminal Block Kit, 180-degree spring clamp type. For use with BRX 10-point PLCs and BRX 16-point expansion modules.Kit includes (2) 10-pin 3.8mm plugs.	
BX-RTB10-2	Terminal Block Kit, 180-degree screw type. For use with BRX 10-point PLCs and BRX 16-point expansion modules.Kit includes (2) 10-pin 3.8mm plugs.	
ZL-BXEM-CBL20	ZIP Link PLC I/O cable, 20-position terminal block to 24-pin connector, 24AWG, cable length 0.5meter (1.6ft). For use with 16-point BRX expansion modules.	
ZL-BXEM-CBL20-1	ZIP Link PLC I/O cable, 20-position terminal block to 24-pin connector, 24AWG, cable length 1meter (3.3ft). For use with 16-point BRX expansion modules.	
ZL-BXEM-CBL20-2	ZIP Link PLC I/O cable, 20-position terminal block to 24-pin connector, 24AWG, cable length 2meter (6.6ft). For use with 16-point BRX expansion modules.	
ZL-BXEM-CBL20-1P	ZIP Link PLC I/O cable, 20-position terminal block to pigtail connection, 24AWG, cable length 1meter (3.3ft). For use with 16-point BRX expansion modules.	
ZL-BXEM-CBL20-2P	ZIP Link PLC I/O cable, 20-position terminal block to pigtail connection, 24AWG, cable length 2meter (6.6ft). For use with 16-point BRX expansion modules.	
ZL-RTB20	ZIPLink Two Level Feedthrough Module, 20-pole, 35mm, DIN mount.	
ZL-RTB20-1	ZIPLink Three Level Feedthrough Module, 20-pole, 35mm, DIN mount.	



Dimensional Information

Note: Drawings are for reference only. Shown without terminal blocks.



12 point Terminal Block Connector Specifications			
Part Number	BX-RTB08	BX-RTB08-1	BX-RTB08-2
Connector Type	Screw Type-90°	Spring Clamp Type-180°	Screw Type-180°
Wire Exit	180°	180°	180°
Pitch	5.0mm	5.0mm	5.0mm
Screw Size	M2.5	N/A	M2.5
Recommended Screw torque	< 3.98 lb·in (0.45 N·m)	N/A	< 3.98 lb·in (0.45 N·m)
Screwdriver Blade Width	3.5mm	3.5mm	3.5mm
Wire Gauge (Single Wire)	28-12 AWG	28-14 AWG	28-12 AWG
Wire Gauge (Two Wires)	28-16 AWG	28-16 AWG (Dual Wire Ferrule Required)	28-16 AWG
Wire Strip Length	0.3in (7.5mm)	0.37in (9.5mm)	0.3in (7.5mm)
Equiv. Dinkle part #	5ESDV-05P-BK	5ESDSR-05P-BK	5ESDF-05P-BK

16 point Term	inal Block Co	onnector Specification	ations
Part Number	BX-RTB10	BX-RTB10-1	BX-RTB10-2
Connector Type	Screw Type-90°	Spring Clamp Type-180°	Screw Type-180°
Wire Exit	180°	180°	180°
Pitch	3.81mm	3.81mm	3.81mm
Screw Size	M2	N/A	M2
Recommended Screw torque	<1.77 lb·in (0.2 N·m)	N/A	<1.77 lb·in (0.2 N·m)
Screwdriver Blade Width	2.5mm	2.5mm	2.5mm
Wire Gauge (Single Wire)	28-16 AWG	28-18 AWG	30-16 AWG
Wire Gauge (Two Wires)	28-18 AWG	30-20 AWG (Dual Wire Ferrule Required)	30-18 AWG
Wire Strip Length	0.24in (6mm)	0.35in (9mm)	0.26in (6.5mm)
Equiv. Dinkle part #	EC381V-10P-BK	ESC381V-10-BK	EC381F-10P-BK