

REV. 8 12300 10/14/24
REV. 7 11575 5/29/15
REV. 9Y81-55083-02
REV. 8

REV. 8 12300 10/14/24
REV. 7 11575 5/29/15

COPPER CONNECTOR CATALOG NUMBER FOR TYPES: BLU, BCU, BBLU, BBCU, BBLZ, BCUR	VERSA-CRIMP® TOOLS WIRE RANGE AWG OR MCM STRANDED COPPER	PENN UNION COPPER CONNECTORS FOR USE WITH VERSA-CRIMP® INSTALLATION TOOLING. (NUMBER OF REQUIRED CRIMPS PER CONNECTION BY CONNECTOR & TOOL COMBINATIONS)														UL US BCUR PRODUCTS	
		VERSA-CRIMP® TOOLS / CONNECTOR TYPES / NUMBER OF CRIMPS															
		VC6-350		VC6-500-BP		VC6-3 ◇		VC6-FT		VC7 ◇		VC7-FT		VC8C			
		BLU BCU *BCUR	BBLU BBLZ BBCU	BLU BCU *BCUR	BBLU BBLZ BBCU	BLU BCU *BCUR	BBLU BBLZ BBCU	BLU BCU *BCUR	BBLU BBLZ BBCU	BLU BCU *BCUR	BBLU BBLZ BBCU	BLU BCU *BCUR	BBLU BBLZ BBCU	BLU BCU *BCUR	BBLU BBLZ BBCU		
-6	#6	1	2	1	2	-	-	-	-	-	-	-	-	-	-		
-4	#4	1	2	1	2	-	-	-	-	-	-	-	-	-	-		
-2	#6-#2	1	2	1	2	1	2 O'LAP	1	2 O'LAP	1	2	1	2	-	-		
-1	#6-#1	1	3	1	3	1	2	1	2	1	2	1	2	-	-		
-1/0	#6-1/0	1	3	1	3	1	2	1	2	1	2	1	2	-	-		
-2/0	#4-2/0	1	3	1	3	1	2	1	2	1	2	1	2	-	-		
-3/0	#2-3/0	2	3	2	3	2 O'LAP	2	2 O'LAP	2	2	2	2	2	-	-		
-4/0	#1-4/0	2	3	2	3	2 O'LAP	2	2 O'LAP	2	2	2	2	2	-	-		
-025	1/0-250	2	3	2	3	2 O'LAP	2	2 O'LAP	2	2	2	2	2	-	-		
-030	2/0-300	2	4	2	4	2 O'LAP	3	2 O'LAP	3	2	3	2	3	-	-		
-035	3/0-350	-	-	3 O'LAP	5	2 O'LAP	3	2 O'LAP	3	2	3	2	3	-	-		
-040	4/0-400	-	-	3 O'LAP	6	2 O'LAP	3	2 O'LAP	3	2	3	2	3	-	-		
-050	4/0-500	-	-	4 O'LAP	6	2	4 O'LAP	2	4 O'LAP	2	4	2	4	1 ◇	2 ◇		
-060	250-600	-	-	-	-	-	-	2	4	-	-	2	4	1 ◇	3 ◇		
-075	500-750	-	-	-	-	-	-	3 O'LAP	4 O'LAP	-	-	3	4	2 O'LAP	3		
-080	500-800	-	-	-	-	-	-	-	-	-	-	-	-	2 O'LAP	3		
-100	750-1000	-	-	-	-	-	-	-	-	-	-	-	-	2	4 O'LAP		
-150	1000-1500	-	-	-	-	-	-	-	-	-	-	-	-	2	4 O'LAP		
* NOTE* BCUR REDUCING SPLICES REQUIRE DIFFERENT CRIMP TOOLING AND DIES ON EACH END DUE TO REDUCING CAPABILITY.		"A" VC6-350 RELATED TOOLS:		"A" VC6-3 ◇ RELATED TOOLS:				"A" VC6-FT RELATED TOOLS:				"A" VC7 ◇ RELATED TOOLS:		"A" VC8C RELATED TOOLS:			
		"A" VC6-350R		"P" TPU-6				"P" TPU-6FT				"A" VC7R		NONE			
		"A" VC6-350-SN		"H" EP-630A				"P" TPU-6FTH				"A" VC7-FT RELATED TOOLS:					
		"A" VC6-350R-SN		"P" TPU-6H				"A" VC6-FTR									
		"A" VC6-500-BP RELATED TOOLS:		"A" VC6-3				"P" TPU-6FTB				"A" VC7-FTR					
		NONE		"A" VC6-3-BP				"A" VC6-FT-BP									
								"H" REC-750									
TOOL SUMMARY: REPRESENTATIVE TOOL AND RELATED TOOLS - "P" = PENN-UNION, "A" = ANDERSON, "H" = HUSKIE																	
REDRAWN BY: RDB 2/23/17																	
◇ USERS OF ANDERSON VC6-3 AND VC7 AND RELATED TOOLS MUST STRIP OFF AN EXTRA 1/8" OF INSULATION FROM ONE END OF CABLE TO PERMIT REMOVAL OF TOOL OVER CONDUCTOR SIZES 250 MCM AND LARGER ON "BCU", "BBCU" & "BCUR" SPLICING SLEEVES.																	
◇ VC6C TOOL CRIMPS 500 MCM ONLY.																	
◇ VC6C TOOL CRIMPS 500-600 MCM ONLY.																	
VERSA-CRIMP® IS A REGISTERED TRADE-MARK OF HUBBELL INCORPORATED.																	
9Y81-55956-01																	
REV.																	

COPPER CONNECTOR CATALOG NUMBER FOR TYPES: BLU, BCU, BBLU, BBCU, BBLZ, BCUR	VERSA-CRIMP® TOOLS WIRE RANGE AWG OR MCM STRANDED COPPER	PENN UNION COPPER CONNECTORS FOR USE WITH VERSA-CRIMP® INSTALLATION TOOLING. (NUMBER OF REQUIRED CRIMPS PER CONNECTION BY CONNECTOR & TOOL COMBINATIONS) VERSA-CRIMP® TOOLS / CONNECTOR TYPES / NUMBER OF CRIMPS												UL US BCUR PRODUCTS					
		VC6-350		VC6-500-BP		VC6-3 ◇		VC6-FT		VC7 ◇		VC7-FT		VC8C					
		BLU BCU BBLZ *BCUR	BBLU BBLZ BBCU	BLU BCU BBLZ *BCUR	BBLU BBLZ BBCU	BLU BCU BBLZ *BCUR	BBLU BBLZ BBCU	BLU BCU BBLZ *BCUR	BBLU BBLZ BBCU	BLU BCU BBLZ *BCUR	BBLU BBLZ BBCU	BLU BCU BBLZ *BCUR	BBLU BBLZ BBCU	BLU BCU BBLZ *BCUR	BBLU BBLZ BBCU				
-6	#6	1	2	1	2	-	-	-	-	-	-	-	-	-	-				
-4	#4	1	2	1	2	-	-	-	-	-	-	-	-	-	-				
-2	#6-#2	1	2	1	2	1	2 O'LAP	1	2 O'LAP	1	2	1	2	-	-				
-1	#6-#1	1	3	1	3	1	2	1	2	1	2	1	2	-	-				
-1/0	#6-1/0	1	3	1	3	1	2	1	2	1	2	1	2	-	-				
-2/0	#4-2/0	1	3	1	3	1	2	1	2	1	2	1	2	-	-				
-3/0	#2-3/0	2	3	2	3	2 O'LAP	2	2 O'LAP	2	2	2	2	2	-	-				
-4/0	#1-4/0	2	3	2	3	2 O'LAP	2	2 O'LAP	2	2	2	2	2	-	-				
-025	1/0-250	2	3	2	3	2 O'LAP	2	2 O'LAP	2	2	2	2	2	-	-				
-030	2/0-300	2	4	2	4	2 O'LAP	3	2 O'LAP	3	2	3	2	3	-	-				
-035	3/0-350	-	-	3 O'LAP	5	2 O'LAP	3	2 O'LAP	3	2	3	2	3	-	-				
-040	4/0-400	-	-	3 O'LAP	6	2 O'LAP	3	2 O'LAP	3	2	3	2	3	-	-				
-050	4/0-500	-	-	4 O'LAP	6	2	4 O'LAP	2	4 O'LAP	2	4	2	4	1 ◇	2 ◇				
-060	250-600	-	-	-	-	-	-	2	4	-	-	2	4	1 ◇	3 ◇				
-075	500-750	-	-	-	-	-	-	3 O'LAP	4 O'LAP	-	-	3	4	2 O'LAP	3				
-080	500-800	-	-	-	-	-	-	-	-	-	-	-	-	2 O'LAP	3				
-100	750-1000	-	-	-	-	-	-	-	-	-	-	-	-	2	4 O'LAP				
-150	1000-1500	-	-	-	-	-	-	-	-	-	-	-	-	2	4 O'LAP				
* NOTE* BCUR REDUCING SPLICES REQUIRE DIFFERENT CRIMP TOOLING AND DIES ON EACH END DUE TO REDUCING CAPABILITY.		"A" VC6-350 RELATED TOOLS: "A" VC6-350R "A" VC6-350-SN "A" VC6-350R-SN		"A" VC6-3 ◇ RELATED TOOLS: "P" TPU-6 "H" EP-630A "P" TPU-6B "A" VC6-3 "A" VC6-3-BP		"H" REC-6630 "P" TPU-6H "A" VC6R "H" EP-630HA		"A" VC6-FT RELATED TOOLS: "P" TPU-6FT "H" EP-750A "P" TPU-6FTB "A" VC6-FT-BP "H" REC-750				"P" TPU-6FTH "A" VC6-FTR "H" EP-750HA		"A" VC7 ◇ RELATED TOOLS: "A" VC7R "A" VC7-FT RELATED TOOLS: "A" VC7-FTR		"A" VC8C RELATED TOOLS: NONE			
		TOOL SUMMARY: REPRESENTATIVE TOOL AND RELATED TOOLS - "P" = PENN-UNION, "A" = ANDERSON, "H" = HUSKIE														REDRAWN BY: RDB 2/23/17			
		◇ USERS OF ANDERSON VC6-3 AND VC7 AND RELATED TOOLS MUST STRIP OFF AN EXTRA 1/8" OF INSULATION FROM ONE END OF CABLE TO PERMIT REMOVAL OF TOOL OVER CONDUCTOR SIZES 250 MCM AND LARGER ON "BCU", "BBCU" & "BCUR" SPLICING SLEEVES.		◇ VC6C TOOL CRIMPS 500 MCM ONLY.		◇ VC6C TOOL CRIMPS 500-600 MCM ONLY.		VERSA-CRIMP® IS A REGISTERED TRADE- MARK OF HUBBELL INCORPORATED.										9Y81-55956-01	