



IO-Link Interface Description

InLine, -14.5 - 14.5 psi

General Data

Vendor ID	856 (0x0358)
Device ID	598296 (0x092118)
IO-Link Revision	V1.1
SIO mode	supported
Process data	16-bit pressure value, 2 switching points
Baudrate	COM2 (38.4 kBaud)
Minimum cycle time	5 ms

Process data input

RecordT (24Bit)

Pressure

IntegerT (16 Bit)

Current pressure

Value range [mbar] (-1000 to 1000)

Gradient (multiplier) to obtain pressure desired unit

psi

0.014504

The pressure is passed to the IO-link master in units of mbar. To obtain the pressure in the desired units, the PLC will need to multiply the value by the multiplier shown in the table above.

OUT 1

BooleanT (Bit offset 22, Bit length 1)

Current status of the digital signal [OUT 1]

Value range false (OFF)
true (On)



OUT 2

BooleanT (Bit offset 23, Bit length 1)

Current status of the digital signal [OUT 2]

Value range false (OFF)
true (On)

Pressure



Word 1





IO-Link Interface Description

InLine, -14.5 - 14.5 psi

IO-Link - specific device data

Index dec (hex)	Sub Index	Name	Length	Data type	Access	Default value	Value range
2 (0x02)	0	System command	8 Bit	UInt	wo		(130) Reset Factory Settings
12 (0x0C)	0	Device Access Locks	16 Bit	Boolean	rw	0	(false) Unlocked (true) Locked
	4	Local user interface	1 Bit				
16 (0x10)	0	Vendor Name	max 19 Byte	String	ro	MP-Sensor	
17 (0x11)	0	Vendor Text	max 11 Byte	String	ro	www.mp-sensor.de	
18 (0x12)	0	Product Name	max 6 Byte	String	ro	InLine	
19 (0x13)	0	Product ID	max 6 Byte	String	ro	[product number]	
20 (0x14)	0	Product Text	max 26 Byte	String	ro	Pressure Sensor InLine - 14.5... 14.5 psi	
21 (0x15)	0	Hardware Revision	max 2 Byte	String	ro		
22 (0x16)	0	Firmware Revision	max 5 Byte	String	ro		
23 (0x17)	0	Application Specific Tag	32 Byte	String	rw		
24 (0x18)	0	Device Status	8 Bit	UInt	ro		
32 (0x20)	0	Detailed Device Status	3 Byte	Array	ro		



IO-Link Interface Description

InLine, -14.5 - 14.5 psi

InLine – specific device data

<i>Index dec (hex)</i>	<i>Sub Index</i>	<i>Name</i>	<i>Length</i>	<i>Data type</i>	<i>Access</i>	<i>Default Value</i>	<i>Value range</i>	<i>Unit</i>
64 (0x40)	0	Switching threshold on, Hysteresis mode 1	16 Bit	Int	rw	-460	Lower Value = -1000 Upper Value = 1000	mbar
65 (0x41)	0	Switching threshold on, Hysteresis mode 2	16 Bit	Int	rw	790	Lower Value = -1000 Upper Value = 1000	mbar
66 (0x42)	0	Switching threshold off, Hysteresis mode 1	16 Bit	Int	rw	-390	Lower Value = -1000 Upper Value = 1000	mbar
67 (0x43)	0	Switching threshold off, Hysteresis mode 2	16 Bit	Int	rw	720	Lower Value = -1000 Upper Value = 1000	mbar
68 (0x44)	0	Upper switching threshold, Comparator mode	16 Bit	Int	rw	-460	Lower Value = -1000 Upper Value = 1000	mbar
69(0x45)	0	Upper switching threshold, Comparator mode	16 Bit	Int	rw	790	Lower Value = -1000 Upper Value = 1000	mbar
70 (0x46)	0	Lower switching threshold, Comparator mode 1	16 Bit	Int	rw	-390	Lower Value = -1000 Upper Value = 1000	mbar
71 (0x47)	0	Lower switching threshold, Comparator mode 2	16 Bit	Int	rw	720	Lower Value = -1000 Upper Value = 1000	mbar



IO-Link Interface Description

InLine, -14.5 - 14.5 psi

72 (0x48)	0	Switch-on delay, Channel 1	16 Bit	<i>UInt</i>	<i>rw</i>	0	Lower Value = 0 Upper Value = 999	100ms/step
73 (0x49)	0	Switch-on delay, Channel 2	16 Bit	<i>UInt</i>	<i>rw</i>	0	Lower Value = 0 Upper Value = 999	100ms/step
74 (0x4A)	0	Switch-off delay, Channel 1	16 Bit	<i>UInt</i>	<i>rw</i>	0	Lower Value = 0 Upper Value = 999	100ms/step
75 (0x4B)	0	Switch-off delay, Channel 2	16 Bit	<i>UInt</i>	<i>rw</i>	0	Lower Value = 0 Upper Value = 999	100ms/step
76 (0x4C)	0	Mode selection, Channel 1	8 Bit	<i>UInt</i>	<i>rw</i>	1	(0) Windows Mode (1) Hysteresis Mode	
77 (0x4D)	0	Mode selection, Channel 2 [Mode Ch2]	8 Bit	<i>UInt</i>	<i>rw</i>	0	(0) Windows Mode (1) Hysteresis Mode (2) Diagnosis Mode	
78 (0x4E)	0	Type of contact (normally open/normally closed), Channel 1	8 Bit	<i>UInt</i>	<i>rw</i>	1	(0) NC (1) NO	
79 (0x4F)	0	Type of contact (normally open/normally closed), Channel 2	8 Bit	<i>UInt</i>	<i>rw</i>	1	(0) NC (1) NO	
85 (0x55)	0	Clear commands	8 Bit	<i>UInt</i>	<i>wo</i>		(0) Clear min press (1) Clear max press	
88 (0x58)	0	Offset	16 Bit	<i>Int</i>	<i>ro</i>		Lower Value = -1000 Upper Value = 1000	mbar
89 (0x59)	0	Minimum pressure	16 Bit	<i>Int</i>	<i>ro</i>		Lower Value = -1000 Upper Value = 1000	mbar
90 (0x5A)	0	Maximum pressure	16 Bit	<i>Int</i>	<i>ro</i>		Lower Value = -1000 Upper Value = 1000	mbar

Irrtümer und Änderungen vorbehalten / Subject to change without notice