



TABLE OF CONTENTS

Chapter 1 - Getting Started

Introduction.....	1-2
Conventions Used.....	1-3
Before you begin... ..	1-4
Step 1: Install Programming Software.....	1-5
Step 2: Launch Programming Software.....	1-6
Step 3: Create a Project.....	1-8
Step 4: Compile and Save Project.....	1-14
Step 5: Apply Power	1-15
Step 6: Establish PC to PLC Communications.....	1-16
Step 7: Write Project into PLC	1-24
Step 8: Place PLC in RUN Mode.....	1-25
Step 9: Test Project using Data View Monitor	1-26
Step 10: Y001 Output On?	1-27
Additional Training Resources	1-28

Chapter 2 - Specifications

Overview of PLC System.....	2-2
PLC Units	2-3
Basic PLC Units	2-3
Built-in I/O (Basic PLC Units)	2-3
Standard PLC Units	2-4
Built-in I/O (Standard PLC Units)	2-4
Analog PLC Units	2-5
Built-in I/O (Analog PLC Units).....	2-5

Table of Contents

Ethernet Basic PLC Units.....	2-6
Built-in I/O (Ethernet Basic PLC Units)	2-6
Ethernet Standard PLC Units	2-7
Built-in I/O (Ethernet Standard PLC Units)	2-7
Ethernet Analog PLC Units	2-8
Built-in I/O (Ethernet Analog PLC units)	2-8
Communication Ports	2-9
Memory	2-9
I/O Modules	2-10
Power Supply	2-13
Programming Software	2-14
PC Requirements.....	2-14
PLC Numbering System	2-15
Data Types	2-15
Memory Types	2-16
I/O Numbering System	2-18
PLC Operation	2-19
Introduction	2-19
PLC Operating System	2-19
PLC Operating Modes	2-20
Stop Mode	2-20
Run Mode	2-20
Read Inputs	2-21
Service Peripherals and Force I/O	2-21
Update System Control (SC) Relays and System Data (SD) Registers	2-22
Solve Application Program	2-22
Write Outputs	2-22
Diagnostics	2-22
Power Budgeting.....	2-23
What is Power Budgeting?	2-23
Power Budget Calculation	2-24
Power Budget Example	2-25
Power Budgeting using the CLICK Programming Software.....	2-25

General Specifications	2-26
General Specifications (all CLICK PLC units)	2-26
PLC Unit Specifications.....	2-27
Common Specifications.....	2-27
PLC LED Status Indicators.....	2-29
Memory Map.....	2-32
Basic PLC Unit Specifications	2-34
C0-00DD1-D – 8 DC Input/6 Sinking DC Output Micro PLC	2-34
C0-00DD2-D – 8 DC Input/6 Sourcing DC Output Micro PLC	2-36
C0-00DR-D – 8 DC Input/6 Relay Output Micro PLC	2-38
C0-00AR-D – 8 AC Input/6 Relay Output Micro PLC	2-40
Standard PLC Unit Specifications.....	2-42
C0-01DD1-D – 8 DC Input/6 Sinking DC Output Micro PLC	2-42
C0-01DD1-D – 8 DC Input/6 Sinking DC Output Micro PLC (continued)	2-43
C0-01DD2-D – 8 DC Input/6 Sourcing DC Output Micro PLC	2-44
C0-01DR-D – 8 DC Input/6 Relay Output Micro PLC	2-46
C0-01AR-D – 8 AC Input/6 Relay Output Micro PLC	2-48
Analog PLC Unit Specifications	2-50
C0-02DD1-D – 4 DC Input/4 Sinking DC Output; 2 Analog In/2 Analog Out Micro PLC	2-50
C0-02DD2-D – 4 DC Input/4 Sourcing DC Output; 2 Analog In/2 Analog Out Micro PLC	2-53
C0-02DR-D – 4 DC Input/4 Relay Output; 2 Analog In/2 Analog Out Micro PLC ...	2-56
Ethernet Basic PLC Unit Specifications	2-59
C0-10DD1E-D – 8 DC Input/6 Sinking DC Output Micro PLC	2-59
C0-10DD2E-D – 8 DC Input/6 Sourcing DC Output Micro PLC	2-61
C0-10DRE-D – 8 DC Input/6 Relay Output Micro PLC.....	2-63
C0-10ARE-D – 8 AC Input/6 Relay Output Micro PLC	2-65
Ethernet Standard PLC Unit Specifications	2-67
C0-11DD1E-D – 8 DC Input/6 Sinking DC Output Micro PLC.....	2-67
C0-11DD2E-D – 8 DC Input/6 Sourcing DC Output Micro PLC	2-69
C0-11DRE-D – 8 DC Input/6 Relay Output Micro PLC.....	2-71
C0-11ARE-D – 8 AC Input/6 Relay Output Micro PLC	2-73

Ethernet Analog PLC Unit Specifications.....	2-75
C0-12DD1E-D – 4 DC Input (Sink/Source)/4 Sinking DC Output	2-75
2 Analog Voltage/Current Input	
2 Analog Voltage/Current Output Micro PLC	2-75
C0-12DD2E-D – 4 DC Input (Sink/Source)/4 Sourcing DC Output;.....	2-78
2 Analog Voltage/Current Input	
2 Analog Voltage/Current Output Micro PLC	2-78
C0-12DRE-D – 4 DC Input (Sink/Source)/4 Relay Output;	2-81
2 Analog Voltage/Current Input	
2 Analog Voltage/Current Output Micro PLC	2-81
C0-12ARE-D – 4 AC Input/4 Relay Output;	2-84
2 Analog Voltage/Current Input	
2 Analog Voltage/Current Output Micro PLC	2-84
C0-12DD1E-1-D – 4 DC Input (Sink/Source)/4 Sinking DC Output;	2-87
4 Analog Current Input	
2 Analog Current Output Micro PLC	2-87
C0-12DD2E-1-D – 4 DC Input (Sink/Source)/4 Sourcing DC Output;	2-90
4 Analog Current Input	
2 Analog Current Output Micro PLC	2-90
C0-12DRE-1-D – 4 DC Input (Sink/Source)/4 Relay Output;	2-93
4 Analog Current Input	
2 Analog Current Output Micro PLC	2-93
C0-12ARE-1-D – 4 AC Input/4 Relay Output;	2-96
4 Analog Current Input	
2 Analog Current Output Micro PLC	2-96
C0-12DD1E-2-D – 4 DC Input (Sink/Source)/4 Sinking DC Output;	2-99
4 Analog Voltage Input	
2 Analog Voltage Output Micro PLC	2-99
C0-12DD2E-2-D – 4 DC Input (Sink/Source)/4 Sourcing DC Output;	2-102
4 Analog Voltage Input	
2 Analog Voltage Output Micro PLC	2-102
C0-12DRE-2-D – 4 DC Input (Sink/Source)/4 Relay Output;	2-105
4 Analog Voltage Input	
2 Analog Voltage Output Micro PLC	2-105
C0-12ARE-2-D – 4 AC Input (Sink/Source) /4 Relay Output;	2-108
4 Analog Voltage Input	
2 Analog Voltage Output Micro PLC	2-108

I/O Module Specifications	2-111
I/O Terminal Block Specifications for CPUs and I/O Modules.....	2-111
LED Indicators.....	2-111
C0-08ND3 – 8-Point Sink/Source DC Input Module.....	2-112
C0-08ND3-1 – 8-Point Sink/Source DC Input Module.....	2-113
C0-16ND3 – 16-Point Sink/Source DC Input Module.....	2-114
C0-08NE3 – 8-Point Sink/Source AC/DC Input Module.....	2-115
C0-16NE3 – 16-Point Sink/Source AC/DC Input Module.....	2-116
C0-08NA – 8-Point AC Input Module.....	2-117
C0-08TD1 – 8-Point Sinking DC Output Module.....	2-118
C0-08TD2 – 8-Point Sourcing DC Output Module.....	2-119
C0-16TD1 – 16-Point Sinking DC Output Module.....	2-120
C0-16TD2 – 16-Point Sourcing Output Module.....	2-121
C0-08TA – 8-Point AC Output Module.....	2-122
C0-04TRS – 4-Point Relay Output Module.....	2-123
C0-08TR – 8-Point Relay Output Module.....	2-124
C0-16CDD1 – 8-Point DC Input and 8-Point DC Sinking Output Module.....	2-125
C0-16CDD2 – 8-Point DC Input and 8-Point DC Sourcing Output Module.....	2-127
C0-08CDR – 4-Point DC Input and 4-Point Relay Output Module.....	2-129
C0-04AD-1 – 4-Channel Analog Current Input Module.....	2-131
C0-04AD-2 – 4-Channel Analog Voltage Input Module.....	2-132
C0-04RTD – 4-Channel RTD Input Module.....	2-133
C0-04THM – 4-Channel Thermocouple Input Module.....	2-135
C0-04DA-1 – 4-Channel Analog Current Output Module.....	2-137
C0-04DA-2 – 4-Channel Analog Voltage Output Module.....	2-138
C0-4AD2DA-1 – 4-Channel Analog Current Input and 2-Channel Analog Current Output Module.....	2-139
C0-4AD2DA-2 – 4-Channel Analog Voltage Input and 2-Channel Analog Voltage Output Module.....	2-141
C0-4AD2DA-2 – 4-Channel Analog Voltage Input and 2-Channel Analog Voltage Output Module (continued).....	2-142
Power Supply Specifications	2-143
C0-00AC Power Supply.....	2-143
C0-01AC Power Supply.....	2-143
PSP24-DC12-1 DC-DC Converter.....	2-143
Accessories	2-144

Chapter 3 - Installation and Wiring

Safety Guidelines	3-2
Plan for Safety	3-2
Three Levels of Protection	3-3
Orderly System Shutdown.....	3-3
System Power Disconnect	3-3
Emergency Stop Circuits	3-4
Introduction to the CLICK PLC Mechanical Design	3-5
CLICK PLC Units	3-5
Component Locations on Basic and Standard PLC Units	3-5
Component Locations on Analog PLC Units	3-6
Component Locations on Ethernet PLC Units.....	3-7
CLICK I/O Modules	3-8
CLICK Power Supplies	3-9
Battery Backup (Standard, Analog and Ethernet PLC Units).....	3-10
Mounting Guidelines	3-11
Environmental Specifications	3-11
Agency Approvals.....	3-11
CLICK Unit Dimensions	3-11
Enclosures	3-14
Panel Layout and Clearances	3-14
Installing the CLICK PLC	3-16
Connecting the Modules Together.....	3-16
Mounting CLICK PLC System on DIN Rail	3-17
Optional Mounting Method.....	3-17
Wiring Guidelines	3-18
Power Input Wiring to Click Power Supply	3-18
Power Input Wiring to CLICK PLC	3-18
Fuse Protection.....	3-19
Planning the I/O Wiring Routes	3-20
Wiring I/O Modules.....	3-21
ZIPLink Wiring System Compatibility Matrix for CLICK PLCs	3-22
I/O Wiring Checklist	3-25

System Wiring Strategies 3–26

- PLC Isolation Boundaries 3–26
- Powering I/O Circuits 3–27
- Sinking/Sourcing Concepts 3–28
- I/O “Common Terminal” Concepts..... 3–29
- DC Input Wiring Methods..... 3–30
- DC Output Wiring Methods..... 3–30
- Relay Outputs - Wiring Methods 3–32
- Relay Outputs – Transient Suppression for Inductive Loads in a Control System..... 3–33

Analog I/O Configuration 3–37

- Terminal Block Wiring - Analog PLC Units 3–37
- Terminal Block Wiring - Expansion Analog I/O Modules..... 3–39
- Configuration in the CLICK Programming Software 3–40
- Analog PLC units..... 3–40
- Analog I/O Modules 3–41
- Analog I/O Monitoring..... 3–43

High-Speed Input Configuration 3–44

- Wiring Examples High Speed Inputs..... 3–46
- 3-Wire Sensors 3–46

Chapter 4 - PLC Communications

Introduction..... 4–2

PLC Communication Ports Specifications 4–3

LED Status Indicators..... 4–5

- LED Status Indicators..... 4–5
- DirectLogic Devices That Do Not Work With CLICK PLCs..... 4–5

3 Steps to Using the CLICK PLC Communications 4–7

Typical Communication Applications..... 4–8

- Port 1 (RS-232) – Modbus RTU Slave Mode Only 4–8
- Port 1 (Ethernet) – Modbus TCP 4–9
- Port 2 (RS-232) – Modbus RTU or ASCII..... 4–10
- Port 3 (RS-485 – Modbus RTU or ASCII)..... 4–11

W-1: Com Port 1 & 2 (RS-232) Wiring..... 4–12

W-2: Com Port 1 (Ethernet) Wiring..... 4–17

Table of Contents

W-3: Com Port 3 Wiring.....	4-19
C-1: Com Port 1 (RS-232) Setup	4-20
C-2: Com Port 1 (Ethernet) Setup	4-21
C-3: Com Port 2 Setup (Modbus RTU)	4-22
C-4: Com Port 2 Setup (ASCII).....	4-23
C-5: Com Port 3 Setup (Modbus RTU)	4-24
C-6: Com Port 3 Setup (ASCII).....	4-25
P-1: Modbus Slave (Server) Programming	4-26
P-2: Modbus Master Programming (Modbus RTU)	4-29
P-3: Modbus Client (Modbus TCP) Programming	4-34
P-4: ASCII Receive Programming	4-40
P-5: ASCII Send Programming	4-43

Chapter 5 - Maintenance

PLC Maintenance.....	5-2
Check LED Indicators.....	5-2
Project Backup	5-2
Check Operating Environment	5-2
Check Operating Voltage	5-2
Check Physical Condition	5-3
Check Project Functionality	5-3
Check the PLC Program from CLICK PLC Programming Software	5-3

Chapter 6 - Troubleshooting

Troubleshooting Direction	6-2
PLC Unit Troubleshooting.....	6-3
Toggle Switch	6-3
LED Indicators	6-4
Power Supply Troubleshooting.....	6-5
The input voltage measures less than 20VDC.....	6-5
The input voltage measures greater than 28VDC	6-5
How to check the power budget.....	6-5

I/O Module Troubleshooting	6-6
Input Module Troubleshooting.....	6-6
Output Module Troubleshooting.....	6-7
How to Check the I/O Configuration	6-7
How to Check the I/O Status.....	6-8
Replacement of I/O modules.....	6-9
Troubleshooting Electrical Noise Problems	6-10
Electrical Noise Problems.....	6-10
Reducing Electrical Noise.....	6-10
Error Codes	6-11