



TABLE OF CONTENTS

Chapter 1 - Getting Started

Introduction	1-2
Purpose of this Manual.....	1-2
About Getting Started	1-2
Online Help Files and Other Documentation	1-2
Technical Support	1-2
Conventions Used.....	1-3
Key Topics for Each Chapter.....	1-3
Before you begin... ..	1-4
Productivity Suite System Requirements	1-5
Step 1: Install Programming Software.....	1-6
Step 2: Launch Programming Software.....	1-10
Step 3: Install Hardware	1-12
Step 4: Apply Power to CPU	1-16
Step 5: Establish PC to CPU Communications.....	1-16
Step 6: Open/Read Hardware Configuration	1-17
Step 7: Create a Project.....	1-19
Step 8: Save Project.....	1-25
Step 9: Write Project to CPU.....	1-26
Step 10: Place CPU in RUN Mode	1-27
Step 11: Test the Project Using Monitor Mode	1-28

Chapter 2 - Specifications

Overview	2-4
P1000 Power Supplies	2-5
P1-01AC and P1-02AC Power Supplies.....	2-5
Power Connections	2-8
Grounding	2-8
P1-01DC Power Supply	2-9
Power Connections	2-10
Grounding	2-10
Productivity1000 Alternate Power Supply Connection.....	2-11
Productivity1000 P1-540 CPU Module	2-12
P1-540 CPU Specifications.....	2-12
P1-540 Module Faceplate Layout	2-13
P1-540 Battery	2-14
P1-540 Communication Ports	2-15
MicroUSB Programming Port	2-15
P1-540 Ethernet Port.....	2-16
microSD Slot	2-17
RS-232 Port.....	2-18
RS-485 Port.....	2-19
Productivity1000 P1-550 CPU Module	2-20
P1-550 CPU Specifications.....	2-20
P1-550 Module Faceplate Layout	2-21
P1-550 Battery	2-22
P1-550 Communication Ports	2-23
MicroUSB Programming Port	2-23
P1-550 Ethernet Port.....	2-24
microSD Slot	2-25
RS-232 Port.....	2-26
RS-485 Port.....	2-27
I/O Modules Overview	2-28
Discrete I/O Modules	2-29
Discrete Input Modules	2-29
Discrete Output Modules	2-29

Discrete Combo I/O Modules 2-30
 Discrete Combo Input/Output Modules 2-30

I/O Modules Installation..... 2-30

P1-08SIM Input Simulator Module 2-31

P1-08ND3 Sinking/Sourcing DC Input..... 2-32
 Wiring Diagrams 2-34

P1-16ND3 Sinking/Sourcing DC Input..... 2-35
 Wiring Diagrams 2-37

P1-08NE3 AC/DC Sinking/Sourcing Input 2-38
 Wiring Diagrams 2-40

P1-16NE3 AC/DC Sinking/Sourcing Input 2-41
 Wiring Diagrams 2-43

P1-08NA AC Input 2-44
 Wiring Diagrams 2-46

P1-08TD1 Sinking DC Output 2-47
 Wiring Diagrams 2-49

P1-08TD2 Sourcing DC Output 2-50
 Wiring Diagrams 2-52

P1-15TD1 Sinking DC Output 2-53
 Wiring Diagrams 2-55

P1-15TD2 Sourcing DC Output 2-56
 Wiring Diagrams 2-58

P1-08TA AC Output 2-59
 Wiring Diagrams 2-61

P1-08TRS Isolated Relay 2-62
 Wiring Diagrams 2-64

P1-16TR Relay Output 2-65
 Wiring Diagrams 2-67

P1-15CDD1 Input/Output 2-68
 Wiring Diagrams 2-70

P1-15CDD2 Input/Output 2-71
 Wiring Diagrams 2-73

P1-16CDR Discrete Input/ Relay Output.....	2-74
Wiring Diagrams	2-76

Chapter 3 - Analog I/O Specifications

Analog I/O Modules Overview.....	3-3
Analog I/O Modules	3-4
Analog Input Modules.....	3-4
Analog Output Modules.....	3-4
Analog Input/Output Modules	3-5
P1-04AD Analog Input.....	3-6
Wiring Diagrams	3-8
Module Configuration.....	3-9
P1-04ADL-1 Analog Input.....	3-10
Wiring Diagrams	3-12
Module Configuration.....	3-13
P1-04ADL-2 Analog Input.....	3-14
Wiring Diagrams	3-16
Module Configuration.....	3-17
P1-08ADL-1 Analog Input.....	3-18
Wiring Diagrams	3-20
Module Configuration.....	3-21
P1-08ADL-2 Analog Input.....	3-22
Wiring Diagrams	3-24
Module Configuration.....	3-25
P1-04RTD Analog Input.....	3-26
Wiring Diagrams	3-29
Module Configuration.....	3-30
P1-04THM Analog Input.....	3-31
Wiring Diagrams	3-33
Module Configuration.....	3-35
P1-04NTC Thermistor.....	3-36
Wiring Diagrams	3-38
Module Configuration.....	3-39

P1-04DAL-1 Analog Output..... 3-40
 Wiring Diagrams 3-42
 Module Configuration 3-43

P1-04DAL-2 Analog Output..... 3-44
 Wiring Diagrams 3-46
 Module Configuration 3-47

P1-08DAL-1 Analog Output..... 3-48
 Wiring Diagrams 3-50
 Module Configuration 3-51

P1-08DAL-2 Analog Output..... 3-52
 Wiring Diagrams 3-54
 Module Configuration 3-55

P1-4ADL2DAL-1 Current Analog Input/Output..... 3-56
 Wiring Diagrams 3-59
 Module Configuration 3-60

P1-4ADL2DAL-2 Voltage Analog Input/Output..... 3-61
 Wiring Diagrams 3-64
 Module Configuration 3-65

Chapter 4 - Specialty Modules Specifications

Specialty Modules Overview 4-2

P1-02HSC High-Speed Isolated Sinking/Sourcing Input..... 4-3
 Wiring Diagrams 4-5
 Wiring Example for Koyo Totem Pole Output Encoder 4-7
 Module Configuration 4-8

P1-04PWM Module..... 4-9
 Wiring Diagrams 4-11
 Module Configuration 4-12

Chapter 5 - Installation and Wiring

Safety Guidelines 5-3
 Plan for Safety 5-3
 Three Levels of Protection 5-4
 Orderly System Shutdown..... 5-4

Table of Contents

System Power Disconnect	5-4
Emergency Stop Circuits	5-5
Introduction to the Productivity1000 Mechanical Design	5-6
Typical Productivity1000 System	5-6
Dimensions and Installation	5-7
Basic Dimensions	5-9
Mounting Guidelines	5-11
Enclosures	5-11
Mounting Position	5-11
Using Mounting Rails	5-11
Mounting Clearances	5-12
Temperature Considerations	5-12
Power Considerations	5-12
Grounding	5-13
Agency Approvals	5-13
Installing the Power Supply	5-14
DIN Rail Mounting P1000 System	5-15
Surface Mounting P1000 System	5-15
Installing the I/O Modules	5-16
Wiring Guidelines	5-17
Power Supply Wiring	5-17
Grounding	5-17
Fuse Protection	5-18
I/O Module Wiring Options	5-19
Hand Wiring System	5-19
I/O Module Wiring Options	5-20
ZIPLink Wiring System	5-20
Terminal Block With Pigtail Cable	5-20
Input and Output Modules ZIPLink Selections	5-21
Analog Modules ZIPLink Selections	5-22
Removable Terminal Blocks (Optional)	5-23
P1-10RTB and P1-10RTB-1	5-23
P2-RTB and P2-RTB-1	5-23
Terminal Block Installation	5-24

Terminal Block Removal 5–25

Planning the I/O Wiring Routes..... 5–25

System Wiring Strategies 5–26

CPU Isolation Boundaries 5–26

Sinking/Sourcing Concepts 5–27

I/O “Common Terminal” Concepts..... 5–28

DC Input Wiring Methods..... 5–29

DC Output Wiring Methods..... 5–29

Relay Outputs - Wiring Methods 5–31

Relay Outputs – Transient Suppression for Inductive Loads in a Control System..... 5–32

Chapter 6 - Communications

Communications..... 6-1

Communication Ports..... 6-1

Communications: Connectivity 6-8

CPU Port Connections..... 6-8

ASCII and Custom Protocol Functionality 6-13

ASCII Instructions 6-13

Custom Protocol Instructions 6-14

Communications: Ethernet..... 6-16

TCP and UDP Port Numbers 6-16

IP Addressing and Subnetting 6-16

PC Setup 6-17

CPU Setup..... 6-18

TCP Connection Behavior with Modbus TCP and Network Instructions 6-19

Communications Modbus Functionality 6-20

Master/Client Function Code and Data Type Support 6-20

Slave/Server Function Code and Data Type Support 6-22

Assigning Modbus Addresses to Tags..... 6-23

Modbus Options 6-26

Modbus Instructions..... 6-29

Network Instructions 6-31

Automatic Poll versus Manual Polling and Interlocking..... 6-32

Message Queue..... 6-34

Table of Contents

EtherNet/IP for the Productivity Series	6-35
Terminology Definitions	6-35
Network Layer Chart	6-36
EtherNet/IP Data	6-36
Class 1 and Class 3 Connections	6-37
Setup Example 1: Productivity1000 as EtherNet/IP Adapter	6-37
Example 2: Productivity1000 as EtherNet/IP Scanner	6-40
Troubleshooting Tips:.....	6-43
EtherNet/IP I/O Message Troubleshooting:	6-45
EtherNet/IP Explicit Message Troubleshooting:.....	6-45
ProNET	6-46
Custom Protocol over Ethernet Functionality.....	6-47
Hardware Configuration	6-48
Custom Protocol Ethernet Instruction.....	6-49
Communications: GS-Drives	6-50
Things To Consider for the design of Remote I/O and GS-Drives	6-50
Things To Consider for the design of Remote I/O and GS4-Drives	6-51
Communications: Port Configuration	6-56
External Ethernet Port Settings	6-57
Local Ethernet Port Settings.....	6-58
Remote Access Configuration	6-58
Serial Configuration.....	6-59
RS-232 and RS-485 Port Settings.....	6-59
Communications: Error Codes	6-62
P1000 EtherNet/IP Error Codes	6-63

Chapter 7 - Maintenance and Troubleshooting

Hardware Maintenance	7-3
Standard Maintenance	7-3
Air Quality Maintenance.....	7-3
CPU Battery Replacement.....	7-3
Diagnostics	7-4
Diagnostics.	7-4
Critical Errors.....	7-4

Non-Critical Errors	7-4
Finding Diagnostic Information	7-4
Error Codes	7-4
CPU Functions Indicators	7-5
PWR Indicator	7-6
Faulty or Incorrect Power Supply.....	7-6
Faulty CPU	7-6
Device or Module Causes the Power Supply to Shutdown	7-7
Run Indicator	7-8
CPU Indicator.....	7-8
Communications Problems	7-8
I/O Module Troubleshooting	7-9
Things to Check.....	7-9
Error Codes	7-9
Some Quick Steps	7-9
Testing Output Points	7-10
Noise Troubleshooting	7-11
Electrical Noise Problems.....	7-11
Reducing Electrical Noise.....	7-11
Run Time vs. Stop Mode Transfer Instruction.....	7-12
Run Time Transfers.....	7-13
Stop Mode Transfers	7-13
Forcing I/O Points	7-15
Advantages of Forces.....	7-15
Enabling Forces	7-15
Forcing Tags in Your System	7-16
Identifying Forced Values	7-18
Force Value Timing Chart.....	7-19

Appendix A - European Union Directives (CE)

European Union (EU) Directives	A-2
Member Countries	A-2
Applicable Directives	A-2
Compliance	A-2
General Safety	A-4
Special Installation Manual	A-4
Basic EMC Installation Guidelines	A-5
Enclosures	A-5
Mains Filters	A-5
Suppression and Fusing	A-5
Internal Enclosure Grounding	A-5
Equipotential Grounding	A-5
Communications and Shielded Cables	A-6
Analog and RS232 Cables	A-7
Multidrop Cables	A-7
Shielded Cables Within Enclosures	A-7
Analog Modules and RF Interference	A-7
Network Isolation	A-8
Items Specific to the Productivity1000	A-9

Appendix B - Productivity1000 Error Codes

Communications Error Codes	B-2
Module Error Codes	B-3
CPU Error Codes	B-4
Project Error Codes	B-5
Project Error Messages	B-7