


TABLE OF CONTENTS



User Caution	i
Publication History.....	iv
Table of Contents.....	vi
Chapter 1 - Getting Started.....	1-1
Introduction	1-2
Purpose of this Manual.....	1-2
About Getting Started	1-2
Online Help Files and Other Documentation.....	1-2
Technical Support.....	1-2
Conventions Used.....	1-3
Key Topics for Each Chapter.....	1-3
Before you begin... ..	1-4
Productivity Suite System Requirements.....	1-5
Step 1: Install Programming Software	1-6
Step 2: Launch Programming Software	1-10
Online Help	1-11
Step 3: Install Hardware	1-12
Step 4: Apply Power to CPU	1-16
Step 5: Establish PC to CPU Communications.....	1-16
Step 6: Open/Read Hardware Configuration.....	1-17
Step 7: Create a Project.....	1-19

Table of Contents

Step 8: Save Project.....	1-24
Step 9: Write Project to CPU.....	1-25
Step 10: Place CPU in RUN Mode	1-26
Step 11: Test the Project Using Monitor Mode.....	1-27
 Chapter 2 - Specifications	2-1
Overview	2-4
Hardware.....	2-4
P1000 Power Supplies.....	2-5
P1-01AC and P1-02AC Power Supplies	2-5
P1-01AC Power Supply.....	2-6
P1-02AC Power Supply	2-7
Power Connections	2-8
Grounding	2-8
P1-01DC Power Supply	2-9
Power Connections	2-10
Grounding	2-10
Productivity® 1000 Alternate Power Supply Connection	2-11
Productivity® 1000 P1-540 CPU Module	2-12
P1-540 CPU Specifications.....	2-12
P1-540 CPU General Specifications.....	2-13
P1-540 Module Faceplate Layout	2-14
P1-540 Battery	2-15
P1-540 Communication Ports.....	2-16
MicroUSB Programming Port	2-16
P1-540 Ethernet Port.....	2-17
microSD Slot.....	2-18
RS-232 Port	2-19
P1-540 RS-485 Port.....	2-20
RS-485 Port	2-20
Productivity1000 P1-550 CPU Module.....	2-21
P1-550 CPU Specifications.....	2-21
Productivity1000 P1-550 CPU Module.....	2-22
P1-550 CPU Specifications.....	2-22
P1-550 Module Faceplate Layout	2-23

Table of Contents

P1-550 Battery	2-24
P1-550 Communication Ports.....	2-25
MicroUSB Programming Port	2-25
P1-550 Ethernet Port.....	2-26
microSD Slot.....	2-27
RS-232 Port	2-28
RS-485 Port	2-29
Remote Slave Module.....	2-30
P1-RX Remote Slave Module.....	2-30
Status Indicators.....	2-30
P1-RX Power Terminal	2-31
P1-RX Remote I/O Example	2-31
P1-RX Setting Remote Slave Address	2-32
P1-RX Remote I/O Port	2-33
I/O Modules Overview	2-34
Discrete I/O Modules.....	2-35
Discrete Input Modules.....	2-35
Discrete Output Modules.....	2-35
Discrete Combo I/O Modules.....	2-36
Discrete Combo Input/Output Modules.....	2-36
I/O Modules Installation	2-36
P1-08SIM Input Simulator Module.....	2-37
P1-08ND-TTL DC Input.....	2-38
Wiring Diagrams.....	2-40
P1-08ND3 Sinking/Sourcing DC Input	2-41
Wiring Diagrams	2-43
P1-16ND3 Sinking/Sourcing DC Input.....	2-44
Wiring Diagrams.....	2-46
P1-08NE3 AC/DC Sinking/Sourcing Input	2-47
Wiring Diagrams.....	2-49
P1-16NE3 AC/DC Sinking/Sourcing Input.....	2-50
Wiring Diagrams.....	2-52
P1-08NA AC Input.....	2-53
Wiring Diagrams.....	2-55

P1-08TD-TTL DC Output	2-56
Wiring Diagrams.....	2-58
P1-08TD1 Sinking DC Output.....	2-59
Wiring Diagrams.....	2-61
P1-08TD2 Sourcing DC Output.....	2-62
Wiring Diagrams.....	2-64
P1-15TD1 Sinking DC Output	2-65
Wiring Diagrams.....	2-67
P1-15TD2 Sourcing DC Output.....	2-68
Wiring Diagrams.....	2-70
P1-08TA AC Output	2-71
Wiring Diagrams.....	2-73
P1-04TRS Isolated Relay.....	2-74
Wiring Diagrams.....	2-76
P1-08TRS Isolated Relay.....	2-77
Wiring Diagrams.....	2-79
P1-16TR Relay Output	2-80
Wiring Diagrams.....	2-82
P1-15CDD1 Input/Output	2-83
Wiring Diagrams.....	2-85
P1-15CDD2 Input/Output.....	2-86
Wiring Diagrams.....	2-88
P1-16CDR Discrete Input/ Relay Output.....	2-89
Wiring Diagrams.....	2-91
 Chapter 3 - Analog I/O Specifications	 3-1
Analog I/O Modules Overview.....	3-3
Analog I/O Modules.....	3-4
Analog Input Modules.....	3-4
Analog Output Modules.....	3-4
Analog Input/Output Modules	3-5

Table of Contents

P1-04AD Analog Input	3-6
Wiring Diagrams.....	3-8
Module Configuration.....	3-9
P1-04AD-1 Analog Input	3-10
Wiring Diagrams.....	3-12
Module Configuration.....	3-13
P1-04AD-2 Analog Input	3-14
Wiring Diagrams.....	3-16
Module Configuration.....	3-17
P1-04ADL-1 Analog Input	3-18
Wiring Diagrams.....	3-20
Module Configuration.....	3-21
P1-04ADL-2 Analog Input	3-22
Wiring Diagrams.....	3-24
Module Configuration.....	3-25
P1-08ADL-1 Analog Input	3-26
Wiring Diagrams.....	3-28
Module Configuration.....	3-29
P1-08ADL-2 Analog Input	3-30
Wiring Diagrams.....	3-32
Module Configuration.....	3-33
P1-04RTD Analog Input	3-34
Wiring Diagrams.....	3-37
Module Configuration.....	3-38
P1-04THM Analog Input	3-39
Wiring Diagrams.....	3-41
Module Configuration.....	3-43
P1-04NTC Thermistor	3-44
Wiring Diagrams.....	3-46
Module Configuration.....	3-47
P1-04DAL-1 Analog Output	3-48
Wiring Diagrams.....	3-50
Module Configuration.....	3-51

P1-04DAL-2 Analog Output	3-52
Wiring Diagrams	3-54
Module Configuration	3-55
P1-08DAL-1 Analog Output	3-56
Wiring Diagrams	3-58
Module Configuration	3-59
P1-08DAL-2 Analog Output	3-60
Wiring Diagrams	3-62
Module Configuration	3-63
P1-4ADL2DAL-1 Current Analog Input/Output	3-64
Wiring Diagrams	3-67
Module Configuration	3-68
P1-4ADL2DAL-2 Voltage Analog Input/Output	3-69
Wiring Diagrams	3-72
Module Configuration	3-73
 Chapter 4 - Specialty Modules Specifications	 4-1
Specialty Modules Overview	4-2
P1-02HSC High-Speed Isolated Sinking/Sourcing Input	4-3
Wiring Diagrams	4-5
Wiring Example for Koyo Open Collector Output Encoder	4-6
Wiring Example for Koyo Totem Pole Output Encoder	4-7
Module Configuration	4-8
P1-04PWM Module	4-9
Wiring Diagrams	4-11
Module Configuration	4-12
High-Speed Module Tester Utility	4-13
 Chapter 5 - Installation and Wiring	 5-1
Safety Guidelines	5-3
Plan for Safety	5-3
Three Levels of Protection	5-4
Orderly System Shutdown	5-4
System Power Disconnect	5-4
Emergency Stop Circuits	5-5

Table of Contents

Productivity® 1000 Mechanical Design	5-6
Typical Productivity1000 System	5-6
Dimensions and Installation	5-7
Basic Dimensions	5-9
P1-01AC, P1-02AC and P1-01DC	5-9
P1-540/P1-550	5-9
P1-RX Module	5-10
I/O Modules	5-10
Mounting Guidelines	5-11
Enclosures	5-11
Mounting Position	5-11
Using Mounting Rails	5-11
Mounting Clearances	5-12
Temperature Considerations	5-12
Power Considerations	5-12
Grounding	5-13
Agency Approvals	5-13
Installing the Power Supply	5-14
DIN Rail Mounting P1000 System	5-15
Surface Mounting P1000 System	5-15
Installing the I/O Modules	5-16
Wiring Guidelines	5-17
Power Supply Wiring	5-17
Grounding	5-17
Fuse Protection	5-18
I/O Module Wiring Options	5-19
Hand Wiring System	5-19
ZIPLink Wiring System	5-20
Terminal Block With Pigtail Cable	5-20
Input and Output Modules ZIPLink Selections	5-21
Analog Modules ZIPLink Selections	5-22
Removable Terminal Blocks (Optional)	5-23
P1-10RTB and P1-10RTB-1	5-23
P2-RTB and P2-RTB-1	5-23
Terminal Block Installation	5-24

Terminal Block Removal	5-25
Planning the I/O Wiring Routes.....	5-25
System Wiring Strategies.....	5-26
CPU Isolation Boundaries.....	5-26
Sinking/Sourcing Concepts	5-27
I/O "Common Terminal" Concepts	5-28
DC Input Wiring Methods.....	5-29
DC Output Wiring Methods.....	5-29
Relay Outputs - Wiring Methods	5-31
Relay Outputs – Transient Suppression for Inductive Loads.....	5-32
CPU's Integrated Transient Suppressors	5-33
Types of Additional Transient Protection.....	5-34
Chapter 6 - Communications	6-1
Communications	6-1
Communication Ports	6-1
microSD Card:	6-2
MicroUSB:	6-2
RS-232:	6-2
Communications: Connectivity	6-8
CPU Port Connections	6-8
ASCII and Custom Protocol Functionality.....	6-13
ASCII Instructions	6-13
Custom Protocol Instructions	6-14
Communications: Ethernet	6-16
TCP and UDP Port Numbers	6-16
IP Addressing and Subnetting	6-16
PC Setup.....	6-17
CPU Setup	6-18
CPU Setup, continued.....	6-19
TCP Connection Behavior with Modbus TCP and Network Instructions.....	6-19
Communications Modbus Functionality.....	6-20
Master/Client Function Code and Data Type Support	6-20
Slave/Server Function Code and Data Type Support.....	6-22
Assigning Modbus Addresses to Tags	6-23

Table of Contents

Modbus Options.....	6-26
Modbus Instructions	6-29
Network Instructions.....	6-31
Automatic Poll versus Manual Polling and Interlocking	6-32
Message Queue	6-34
EtherNet/IP for the Productivity Series	6-35
Terminology Definitions.....	6-35
Network Layer Chart	6-36
EtherNet/IP Data.....	6-36
Class 1 and Class 3 Connections.....	6-37
Setup Example 1: Productivity® 1000 as EtherNet/IP Adapter	6-37
Example 2: Productivity® 1000 as EtherNet/IP Scanner.....	6-40
Troubleshooting Tips:	6-43
EtherNet/IP I/O Message Troubleshooting:.....	6-45
EtherNet/IP Explicit Message Troubleshooting:.....	6-45
ProNET	6-46
Custom Protocol over Ethernet Functionality.....	6-47
Hardware Configuration	6-48
Custom Protocol Ethernet Instruction.....	6-49
Communications: Remote I/O and GS-Drives	6-50
Design Considerations for Remote I/O and GS-Drives	6-50
Communications: Port Configuration.....	6-56
External Ethernet Port Settings	6-57
Local Ethernet Port Settings.....	6-58
Remote Access Configuration	6-58
Serial Configuration.....	6-59
RS-232 and RS-485 Port Settings	6-59
Communications: Error Codes.....	6-62
P1000 EtherNet/IP Error Codes	6-63
 Chapter 7 - Maintenance and Troubleshooting	 7-1
Hardware Maintenance	7-3
Standard Maintenance	7-3
Air Quality Maintenance	7-3
CPU Battery Replacement	7-3

Diagnostics	7-4
Diagnostics.	7-4
Critical Errors	7-4
Non-Critical Errors.....	7-4
Finding Diagnostic Information	7-4
Error Codes	7-4
CPU Functions Indicators	7-5
PWR Indicator	7-6
Faulty or Incorrect Power Supply	7-6
Faulty CPU	7-6
Device or Module Causes the Power Supply to Shutdown.....	7-7
Run Indicator	7-8
CPU Indicator	7-8
Communications Problems	7-8
I/O Module Troubleshooting	7-9
Things to Check	7-9
Error Codes	7-9
Some Quick Steps	7-9
Testing Output Points	7-10
Noise Troubleshooting	7-11
Electrical Noise Problems.....	7-11
Reducing Electrical Noise.....	7-11
Run Time vs. Stop Mode Transfer Instruction.....	7-12
Run Time Transfers.....	7-13
Stop Mode Transfers	7-13
Forcing I/O Points.....	7-15
Advantages of Forces	7-15
Enabling Forces	7-15
Forcing Tags in Your System	7-16
Identifying Forced Values.....	7-18
Force Value Timing Chart.....	7-19

Table of Contents

Appendix A - European Union Directives (CE).....	A-1
European Union (EU) Directives.....	A-2
Member Countries	A-2
Applicable Directives.....	A-2
Compliance	A-2
General Safety.....	A-4
Special Installation Manual.....	A-4
Other Sources of Information	A-4
Basic EMC Installation Guidelines	A-5
Enclosures.....	A-5
Mains Filters.....	A-5
Suppression and Fusing.....	A-5
Internal Enclosure Grounding.....	A-5
Equipotential Grounding	A-5
Communications and Shielded Cables	A-6
Analog and RS232 Cables.....	A-7
Multidrop Cables	A-7
Shielded Cables Within Enclosures	A-7
Analog Modules and RF Interference.....	A-7
Network Isolation	A-8
Items Specific to the Productivity® 1000	A-9
 Appendix B - Productivity®1000 Error Codes.....	B-1
Communications Error Codes.....	B-2
Module Error Codes	B-3
CPU Error Codes.....	B-4
Project Error Codes	B-5
Project Error Messages.....	B-7
 Appendix C - Security Considerations for Control Systems Networks.....	C-1
Security Considerations for Control Systems Networks.....	C-2