




P1-M401-15DD2


The P1-M401-15DD2 is a P1000 CPU with 8 integrated sinking/sourcing inputs and 7 sourcing outputs. This PLC can be used as a stand-alone controller for small applications, or expanded with 2 additional P1000 I/O modules.

CPU Specifications	2
CPU Status Indicators	2
Input Specifications	3
Output Specifications	3
CPU Front Panel	3
Module Installation Procedure	4
Wiring Options	4
Schematic and Wiring Diagrams	5
RS-232 Specifications	6
USB-C Specifications	6
Removable Terminal Block Specifications	7
General Specifications	8
Warning	8

Terminal Block sold separately, (see wiring options on page 4).

CPU Specifications		
User Memory	32MB (Includes program, data and documentation)	
Memory Type	Flash and RAM	
Retentive Memory	27KB	
Scan Time	1.7 ms (1K Boolean, Max I/O)	
External Power Required	24VDC $\pm 2\%$ @ 6W plus 1.25 W per additional I/O module.	
Protection Circuit	Not built into module – Install protection element such as Edison S5061-R, Time Delay, 1A Fuse	
Communication; 2 Integrated Ports	USB IN: Programming, Monitoring, Debug, Firmware RS-232: (RJ-12 1200-115.2k baud) ASCII, Modbus	
Hardware Limits of System	Onboard I/O Points: 8 sink/source inputs and 7 sourcing outputs Expansion I/O Point Limit: 32 (2 modules with up to 16 points each)	
Instruction Types	Application Functions Array Functions Counters/Timers Communications Data Handling Drum Sequencers Math Functions	PID Program Control String Functions System Functions Contacts Coils
Real Time Clock	None	

CPU Status Indicators	
PWR	Green LED is illuminated when power is ON
RUN	Green LED is illuminated when CPU is in RUN mode
CPU	Red LED is illuminated during power ON reset, power down, or watch-dog time-out




CPU Run/Stop Switch Specifications	
RUN position	Executes user program, run-time edits possible
STOP position	Does not execute user program, normal program load position

Input Specifications	
Inputs per Module	8 (sink/source)
Rated Voltage	12–24 VDC
Operating Voltage Range	10.2–26.4 VDC, Max 30VDC
Input Current	8.4 mA @ 24VDC
Maximum Input Current	10mA @ 26.4 VDC
Input Impedance	3kΩ
Minimum ON Current	1.4 mA
Maximum OFF Current	1mA
ON Voltage Level	> 9VDC
OFF Voltage Level	< 4.5 VDC
OFF to ON, ON to OFF Response	2ms Maximum, 1ms Typical
Status Indicators	Logic Side (8 points)
Commons	1 (8 points/common)

Output Specifications	
Outputs per Module	7 (sourcing)
Rated Voltage	12–24 VDC
Operating Voltage Range	10.2–28.8 VDC
Maximum Output Current	1A per point
Minimum Load Current	1mA
Maximum Leakage Current	0.3 mA @ 28.8 VDC
On Voltage Drop	0.2 VDC @ 1A
Maximum Inrush Current	4A for 50ms, 6A for 10ms
OFF to ON, ON to OFF Response	0.5 ms
Status Indicators	Logic Side (7 points)
Commons	1 (7 points/common)
Protection Circuit	Not built into module – Install protection elements such as an external fuse.
External Power Supply Required	12–24 VDC (-15% / +20%) @ 22mA


CPU Front Panel




Module Installation

WARNING: Do not add or remove modules with field power applied.


Step One: With latch in "locked" position, align connectors on the side of each module and stack by pressing together. Click indicates lock is engaged.



Step Two: Attach field wiring using the removable terminal block or ZIPlink wiring system.




Step Three: To unstack modules, pull locking latch up into the unlocked position and then pull modules apart.



Wiring Options

1 ZIPlink Feed Through Modules and Cables¹




ZIPINK
AUTOMATIONDIRECT

ZL-RTB20
ZL-RTB20-1


ZL-P1-CBL18
ZL-P1-CBL18-1
ZL-P1-CBL18-2

2 Terminal Block with pigtail cable




ZL-P1-CBL18-1P
ZL-P1-CBL18-2P

3 Screw Terminal Block only



P2-RTB
(Quantity 1)

4 Spring Clamp Terminal Block only



P2-RTB-1
(Quantity 1)

5 Accessories²



ZL-RTB-COM




TW-SD-SL-1

TW-SD-MSL-1

1. Cable + ZIPlink Module = Complete System

2. ZL-RTB-COM provides a common connection point for power or ground in a small footprint.

Schematic and Wiring Diagram



Port Specifications

RS-232 Specifications

Port Name	RS-232
Description	Non-isolated RS-232 DTE port connects the CPU as a Modbus/ASCII master or slave to a peripheral device. Includes ESD and built-in surge protection
Data Rates	Selectable, 1200, 2400, 4800, 9600, 19200, 33600, 38400, 57600, and 115200
+5V Cable Power Source	210mA maximum at 5V, $\pm 5\%$. Reverse polarity and overload protected
TXD	RS-232 Transmit output
RXD	RS-232 Receive input
RTS	Handshaking output for modem control
GND	Logic ground
Maximum Output Load (TXD/RTS)	3k Ω , 1000 pF
Minimum Output Voltage Swing	± 5 V
Output Short Circuit Protection	± 15 mA
Port Status LED	Green LED is illuminated when active for TXD, RXD and RTS
Cable Options	EA-MG-PGM-CBL D2-DSCBL USB-RS232-1 with D2-DSCBL FA-CABKIT FA-ISOCON for converting RS-232 to isolated RS-485




6-pin RJ12 Female Modular Connector

Pin #	Signal	
6	GND	Logic Ground
5	RTS	RS-232 Output
4	TXD	RS-232 Output
3	RXD	RS-232 Input
2	+5V	210mA Maximum
1	GND	Logic Ground

USB-C Specifications

Port Name	USB-C
Description	Standard USB-C Slave input for programming and online monitoring and firmware update with built-in surge protection. Not compatible with older full speed USB devices.
Transfer Rate	480 Mbps
Port Status LED	Green LED is illuminated when LINK is established to programming software.
Cables	USB Type A to Micro USB Type C: 6ft cable part # USB-CBL-AC6

Power Removable Terminal Block Specifications	
Part Number	PCON-KIT
Number of Positions	3 Screw Terminals
Pitch	3.5 mm
Wire Range	28–16 AWG Solid Conductor 28–16 AWG Stranded Conductor
Screw Driver Width	1/8 in (3.175 mm) Maximum
Screw Size	M2
Screw Torque	1.7 lb-in (0.4 N-m)



Input/Output Removable Terminal Block Specifications		
Part Number	P2-RTB	P2-RTB-1
Positions	18 Screw Terminals	18 Spring Clamp Terminals
Wire Range	30–16 AWG (0.051–1.31 mm ²) Solid / Stranded Conductor 3/64 in (1.2 mm) Insulation Max. 1/4 in (6–7 mm) Strip Length	28–16 AWG (0.081–1.31 mm ²) Solid / Stranded Conductor 3/64 in (1.2 mm) Insulation Max. 19/64 in (7–8 mm) Strip Length
Conductors	"USE COPPER CONDUCTORS, 75°C" or equivalent.	
Screw Driver	0.1 in (2.5 mm) Maximum*	
Screw Size	M2	N/A
Screw Torque	2.5 lb-in (0.28 N-m)	N/A

*Recommended Screw Driver TW-SD-MSL-1

General Specifications	
Operating Temperature	0° to 60°C (32° to 140°F)
Storage Temperature	-20° to 70°C (-4° to 158°F)
Humidity	5 to 95% (non-condensing)
Altitude	2,000 meters max
Pollution Degree	2
Environmental Air	No corrosive gases permitted
Vibration	IEC60068-2-6 (Test Fc)
Shock	IEC60068-2-27 (Test Ea)
Overvoltage Category	II
Field to Logic Side Isolation	1800VAC applied for 1 second
Insulation Resistance	>10MΩ @ 500VDC
Heat Dissipation	5304mW
Enclosure Type	Open Equipment
Module Location	Controller in a Productivity1000 System.
Field Wiring	Use ZIP Link Wiring System or removable terminal block (Sold Separately). See "Wiring Options" on page 4.
Terminal Type (sold separately)	18-Position Removable Terminal Block
Weight	101g (3.57 oz)
Agency Approvals	UL 61010-1 and UL 61010-2-201 File E139594, Canada & USA CE (EN 61131-2 EMC, EN 61010-1 and EN 61010-2-201 Safety)*

*See CE Declaration of Conformance for details.

WARNING: To minimize the risk of potential safety problems, you should follow all applicable local and national codes that regulate the installation and operation of your equipment. These codes vary from area to area and it is your responsibility to determine which codes should be followed, and to verify that the equipment, installation, and operation are in compliance with the latest revision of these codes.

Equipment damage or serious injury to personnel can result from the failure to follow all applicable codes and standards. We do not guarantee the products described in this publication are suitable for your particular application, nor do we assume any responsibility for your product design, installation, or operation.

If you have any questions concerning the installation or operation of this equipment, or if you need additional information, please call Technical Support at 770-844-4200.

This publication is based on information that was available at the time it was printed. At AutomationDirect.com® we constantly strive to improve our products and services, so we reserve the right to make changes to the products and/or publications at any time without notice and without any obligation. This publication may also discuss features that may not be available in certain revisions of the product.

Document Name	Edition/Revision	Date
P1-M401-15DD2-DS	1st Edition	4/25/2025

Copyright 2025, AutomationDirect.com Incorporated/All Rights Reserved Worldwide