
VAUTOMATION DIRECTS Productivity 1000



P1-M622-4ADL2DAL-1

The P1-M622-4ADL2DAL-1 is a P1000 CPU with 4 integrated analog current inputs and 2 analog current outputs. This PLC can be used as a stand-alone controller for small applications, or expanded with 4 additional P1000 I/O modules.

CPU Specifications
CPU Status Indicators
CPU Stop/Run Switch Specifications
Input Specifications
Output Specifications
Module Installation Procedure
Wiring Options
Schematic and Wiring Diagrams
CPU Front Panel
Micro SD Specifications
Port Specifications
Removable Terminal Block Specifications
General Specifications
Warning 1

Terminal Block sold separately, (see wiring options on page 4).

CPU Specifications		
User Memory	50MB (Includes program, data and documentation)	
Memory Type	Flash and Battery Backed RA	AM
Retentive Memory	512KB	
Scan Time	1.9ms (1K Boolean, Max I/0	0)
External Power Required	24VDC ±2% @ 2.5W plus 1	1.25 W per additional I/O module
Protection Circuit	Not built into module – Inst S5601-R, Time Delay, 1A F	all protection element such as Edison use
Communications; 5 Integrated Ports	USB: Programming, Monitoring, Debug, Firmware ETHERNET: (10/100Mbps Ethernet) Programming, Monitoring, Debug, Firmware, Email SMTP Client, Modbus TCP Client (32 Servers) and Server (16 Clients), Ethernet IP Scanner (32 Adapters) and Adapter (4 scanners) with 8 connections per device. Custom Protocol over Ethernet, ProNet, MQTT/MQTTS. REMOTE I/0: 16 GS Drives*, 4 ProtosX TCP couplers, 4 P1-RX remote bases, 1 PS-AMC module RS-232: (RJ12, 1200-115.2k Baud) ASCII, Modbus RS-485: Removable Terminal Included, (1200-115.2k Baud) ASCII, Modbus RTU	
Data Logging	MicroSD card slot	
Hardware Limits of System	Onboard I/O Points: 4 0–20 mA inputs and 2 4–20 outputs Expansion I/O Point Limit: 64 (4 modules with up to 16 points each)	
Instruction Types	Application Functions Array Functions Counters/Timers Communications Data Handling Drum Sequencers Math Functions	PID Program Control String Functions System Functions Contacts Coils Motion Control
Real Time Clock Accuracy	±2s per day at typical 25°C ±10s per day maximum at 6	00°C

^{*}GS drive requires communication module/ card

	CPU Status Indicators
PWR	Green LED is illuminated when power is ON
RUN	Green LED is illuminated when CPU is in RUN mode
CPU	Red LED is illuminated during power ON reset, power down, or watch-dog time-out



CPL	J Run/Stop Switch Specifications
RUN position	Executes user program, run-time edits possible
STOP position	Does not execute user program, normal program load position

Input Specifications		
Inputs per Module	4	
Module Signal Input Range	0–20 mA	
Signal Resolution	13-bit	
Resolution Value of LSB (least significant bit)	0–20 mA = 2.44 μA per count (1LSB = 1 count)	
Data Range	0-8191 counts	
Input Type	Sinking, Single-ended (1 common)	
Maximum Continuous Overload	±31mA	
Input Impedance	243Ω, ±0.5%, 1/8W Current Input	
Filter Characteristics	Low Pass, -3dB @ 120Hz	
Sample Duration Time	4ms per channel (does not include ladder scan time)	
All Channel Update Rate	20ms	
Open Circuit Detection Time	Zero reading within 100ms	
Conversion Method	Successive approximation	
Accuracy vs. Temperature	±75PPM / °C maximum	
Maximum Inaccuracy	0.5% of range (including temperature drift)	
Linearity Error (end to end)	±0.037% of range Monotonic with no missing codes	
Input Stability and Repeatability	±0.024% of range (after 10 minute warm-up)	
Maximum Full Scale Calibration Error	±0.098% of range	
Offset Calibration Error	±0.098% of range	
Maximum Crosstalk at DC, 50Hz and 60Hz	±0.049% of range	
Protection Circuit	Edison S500-32-R, 0.032 A fuse	
External Power Supply Required	24VDC (-20% / + 25%), 140mA (Loop Power Included)	


Output Specifications		
Outputs per Module	2	
Output Range	4–20 mA	
Signal Resolution	12-bit	
Resolution Value of LSB (least significant bit)	4–20 mA = 3.9 μA / count 1 LSB = 1 count	
Data Range	0–4095 counts	
Output Type	Current sourcing at 20mA max	
Output Value in Fault Mode	Less than 4mA	
Load Impedance	0–570 Ω (19.2 VDC), 0–690 Ω (21.6 VDC), 0–810 Ω (24.0 VDC), 0–930 Ω (26.4 VDC), 0–1100 Ω (30.0 VDC) Minimum Load: 0 Ω @ 0–45 °C 125 Ω @ 45–60 °C ambient temperature	
Maximum Inductive Load	1mH	
Allowed Load Type	Grounded	
Maximum Inaccuracy	1% of range	
Full Scale Calibration Error	±0.2% of range minimum	
Offset Calibration Error	±0.2% of range maximum	
Accuracy vs. Temperature	±75 PPM / °C maximum full-scale calibration change (±0.005% of range / °C)	
Max Crosstalk at DC, 50Hz and 60Hz	-72dB, 1 LSB	
Linearity Error (End to End)	±4 counts max., (±0.1% of full scale)	
Output Stability and Repeatability	±2% counts after 10 min. warm up (typical)	
Output Ripple	±0.2% of full scale	
Output Settling Time	0.3 ms max., 5µs min. (full scale range)	
All Channel Update Rate	4ms (max)	
Maximum Continuous Overload	Outputs open circuit protected	
Type of Output Protection	Electronically current limited to 20mA or less	
Output Signal at Power Up and Power Down	4mA	

Module Installation

WARNING: Do not add or remove modules with


field power applied.

Step One: With latch in "locked" position, align connectors on the side of each module and stack pressing together. Click indicates lock is engaged.





Sten Two: Attach field wiring using the removable terminal block or **ZIP**Link wiring system.


Check all latches are secure after modules are connected



locking latch up into the unlocked position and then pull modules apart.










- 1. Cable + **ZIP**Link Module = Complete System
- 2. ZL-RTB-COM provides a common connection point for power or ground


Wiring Diagram






An Edison S500-32-R 0.032A fast-acting fuse is recommended for all 4-20 mA current loops.






Note: Do not connect both ends of shield.

Current Output Circuits



Note: Shield is connected to common at the source device.

CPU Front Panel




microSD Specifications				
Port Name	microSD	microSD		
Description	Standard microSD socket for data logging			
Maximum Card Capacity	32GB SDHC			
Transfer Data	Mbps	Minimum	Typical	Maximum
Transfer Rate	Read	14.3	14.4	14.6
(Class 4 memory card)*	Write	4.8	4.9	5.1
Port Status LED	Green LED is illuminated when card is inserted/detected			

^{*}Supported microSD MICSD-16G



NOTE: Card not included with unit.

Pin	SD
1	DAT2
2	CD/DAT3
3	CMD
4	VDD
5	CLK
6	VSS
7	DAT0
8	DAT1



Port Specifications

· · · · · · · · · · · · · · · · · · ·		
RS-232 Specifications		
Port Name	RS-232	
Description	Non-isolated RS-232 DTE port connects the CPU as a Modbus/ASCII master or slave to a peripheral device. Includes ESD and built-in surge protection	
Data Rates	Selectable,1200, 2400, 4800, 9600, 19200, 33600, 38400, 57600, and 115200	
+5V Cable Power Source	210mA maximum at 5V, ±5%. Reverse polarity and overload protected	
TXD	RS-232 Transmit output	
RXD	RS-232 Receive input	
RTS	Handshaking output for modem control	
GND	Logic ground	
Maximum Output Load (TXD/RTS)	3kΩ, 1000 pf	
Minimum Output Voltage Swing	±5 V	
Output Short Circuit Protection	±15 mA	
Port Status LED	Green LED is illuminated when active for TXD, RXD and RTS	
Cable Options	EA-MG-PGM-CBL D2-DSCBL USB-RS232-1 with D2-DSCBL FA-CABKIT FA-ISOCON for converting RS-232 to isolated RS-485	



6-pin RJ12 Female Modular Connector

Pin #		Signal
6	GND	Logic Ground
5	RTS	RS-232 Output
4	TXD	RS-232 Output
3	RXD	RS-232 Input
2	+5V	210mA Maximum
1	GND	Logic Ground

RS-485 Port Specifications	
Port Name	RS-485
Description	Non-isolated RS-485 port connects the CPU as a Modbus/ASCII master or slave to a peripheral device. Includes ESD/EFT protection and automatic echo cancellation when transmitter is active
Data Rates	Selectable, 1200, 2400, 4800, 9600, 19200, 33600, 38400, 57600, and 115200
TXD+/RXD+	RS-485 transceiver high
TXD-/RXD-	RS-485 transceiver low
GND	Logic ground
Input Impedance	19kΩ
Termination Resistance (TB Jumper Wire "T" to "+")	120Ω. To use, add a jumper between "T" and "+". Resistor is internally connected between "T" and "-'.
Maximum Load	50 transceivers, 19kΩ each, 60Ω termination
Output Short Circuit Protection	± 250mA, thermal shut-down protection
Electrostatic Discharge Protection	Contact ± 4KV, Air ± 8KV per IEC1000-4-2 Cable is installed for testing
Electrical Fast Transient Protection	± 1KV per IEC1000-4-4
Minimum Differential Output Voltage	1.5 V with 60Ω load
Fail Safe Inputs	Logic high input state if inputs are unconnected
Maximum Common Mode Voltage	-7.5 V to 12.5 V
Port Status LED	Green LED illuminated when active for TXD and RXD
Cable Options	Go to AutomationDirect.com for RS-232 and RS-485 cables






Pin #	Signal
G	GND
-	TXD-/RXD-
+	TXD+/RXD+
T	TERMINATION


Port Specifications

Ethernet Specifications					
Port Name	ETHERNET	REMOTE I/O			
Description	Standard transformer isolated Ethernet port with built-in surge protection for programming, online monitoring and ethernet communication protocols. See table on page 2 for supported devices and protocols.	Standard transformer isolated Ethernet port with built-in surge protection for connection to supported remote I/O devices. See table on page 2 for supported remote I/O devices.			
Transfer Rate	10 Mbps and 100 Mbps (auto-crossover)				
Port Status LED	LINK (Amber LED) is solid when network LINK is established. ACT (Green LED) flashes when port is active.				



USB-C Specifications			
Port Name	USB-C		
Description	Standard USB-C Slave input for programming and online monitoring and firmware update with built-in surge protection. Not compatible with older full speed USB devices.		
Transfer Rate	480 Mbps		
Port Status LED	Green LED is illuminated when LINK is established to programming software.		
Cables	USB Type A to Micro USB Type C: 6ft cable part # USB-CBL-AC6		

Power Removable Terminal Block Specifications		
Part Number	PCON-KIT	
Number of Positions	3 Screw Terminals	
Pitch	3.5 mm	
Wire Range	28–16 AWG Solid Conductor 28–16 AWG Stranded Conductor	
Screw Driver Width	1/8 in (3.175 mm) Maximum	
Screw Size	M2	
Screw Torque	1.7 lb-in (0.4 N·m)	



Input/Output Removable Terminal Block Specifications					
Part Number	P1-10RTB	P1-10RTB-1			
Positions	10 Screw Terminals	10 Spring Clamp Terminals			
Wire Range	30–16 AWG (0.051–1.31 mm²) Solid / Stranded Conductor 3/64 in (1.2 mm) Insulation Max. 1/4 in (6–7 mm) Strip Length	28–16 AWG (0.081–1.31 mm²) Solid / Stranded Conductor 3/64 in (1.2 mm) Insulation Max. 19/64 in (7–8 mm) Strip Length			
Conductors	"USE COPPER CONDUCTORS, 75°C" or equivalent.				
Screw Driver	0.1 in (2.5 mm) Maximum*				
Screw Size	M2	N/A			
Screw Torque	2.5 lb·in (0.28 N·m) N/A				

^{*}Recommended Screw Driver TW-SD-MSL-1

General Specifications			
Operating Temperature	0° to 60°C (32° to 140°F)		
Storage Temperature	-20° to 70°C (-4° to 158°F)		
Humidity	5 to 95% (non-condensing)		
Altitude	2,000 meters max		
Pollution Degree	2		
Environmental Air	No corrosive gases permitted		
Vibration	IEC60068-2-6 (Test Fc)		
Shock	IEC60068-2-27 (Test Ea)		
Field to Logic Side Isolation	1800VAC applied for 1 second		
Insulation Resistance	> 10MΩ @ 500VDC		
Heat Dissipation	4.75 W		
Overvoltage Category			
Enclosure Type	Open Equipment		
Module Location	Controller in a Productivity1000 System.		
Field Wiring	Removable terminal block (sold separately). Use ZIP Link Wiring System optional See "Wiring Options" on page 4.		
Terminal Type (sold separately)	10-position Removable Terminal Block		
Weight	168g (5.93 oz)		
Agency Approvals	UL 61010-1 and UL 61010-2-201 File E139594, Canada and USA CE (EN 61131-2 EMC, EN 61010-1 and EN 61010-2-201 Safety)*		

^{*}See CE Declaration of Conformance for details.

WARNING: To minimize the risk of potential safety problems, you should follow all applicable local and national codes that regulate the installation and operation of your equipment. These codes vary from area to area and it is your responsibility to determine which codes should be followed, and to verify that the equipment, installation, and operation are in compliance with the latest revision of these codes.

Equipment damage or serious injury to personnel can result from the failure to follow all applicable codes and standards. We do not guarantee the products described in this publication are suitable for your particular application, nor do we assume any responsibility for your product design, installation, or operation.

If you have any questions concerning the installation or operation of this equipment, or if you need additional information, please call Technical Support at 770-844-4200.

This publication is based on information that was available at the time it was printed. At AutomationDirect.com® we constantly strive to improve our products and services, so we reserve the right to make changes to the products and/or publications at any time without notice and without any obligation. This publication may also discuss features that may not be available in certain revisions of the product.

Document Name	Edition/Revision	Date
P1-M622-4ADL2DAL-1-DS	1st Edition	5/14/2025

Copyright 2025, AutomationDirect.com Incorporated/All Rights Reserved Worldwide