



TABLE OF CONTENTS

Chapter 1 - Getting Started

Before you begin.....	1-2
Productivity Suite System Requirements	1-3
Step 1: Install Programming Software.....	1-4
Step 2: Launch Programming Software.....	1-9
Online Help.....	1-10
Step 3: Install Hardware	1-11
Step 4: Apply Power to CPU	1-14
Step 5: Establish PC to CPU Communications.....	1-15
Step 6: Open/Read Hardware Configuration	1-16
Step 7: Create a Project.....	1-18
Step 8: Save Project.....	1-24
Step 9: Write Project to CPU.....	1-25
Step 10: Place CPU in RUN Mode	1-26
Step 11: Test the Project Using Monitor Mode	1-27

Chapter 2 - Specifications

Overview	2-3
Base Hardware	2-3
Base Configuration.....	2-4
P2-01AC and P2-01DCAC Power Supply.....	2-6
P2-01AC Power Supply	2-7
P2-01DCAC Power Supply	2-8
Power Connections	2-9
P2-550 Specifications	2-11

Table of Contents

OLED Message Display	2-13
Front Panel OLED Monitoring and Configuration	2-14
Battery (Optional)	2-15
Port Specifications	2-16
MICRO USB Programming Port	2-16
Ethernet Port (On bottom of CPU)	2-17
Remote I/O Port (On bottom of CPU)	2-17
MICRO SD SLOT	2-18
RS-232 Port	2-19
RS-485 Port	2-20
Remote Slave Module	2-21
P2-RS Remote Slave Module Example	2-22
P2-RS Remote Slave Module Specifications	2-23
P2-RS Remote Slave Module Front Panel	2-24
Status Indicators	2-24
OLED Message Display	2-25
Setting Remote Slave Address	2-26
Setting the Remote Slave Address (continued)	2-27
I/O Modules Overview	2-28
Discrete I/O Modules	2-29
Discrete Input Modules	2-29
Discrete Output Modules	2-29
P2-08SIM Input Simulator Module	2-30
Input Specifications	2-30
P2-08ND3-1 Sinking/Sourcing DC Input	2-31
Wiring Diagrams	2-33
P2-16ND3-1 Sinking/Sourcing DC Input	2-34
Wiring Diagrams	2-36
P2-32ND3-1 24VDC Sinking/Sourcing Input	2-37
Wiring Diagrams	2-39
P2-08NE3 AC/DC Sinking/Sourcing Input	2-40
Wiring Diagrams	2-42
P2-16NE3 AC/DC Sinking/Sourcing Input	2-43
Wiring Diagrams	2-45

P2-32NE3 AC/DC Sinking/Sourcing Input	2-46
Wiring Diagrams	2-48
P2-08NAS Isolated AC Input	2-49
Wiring Diagrams	2-51
P2-16NA AC Input	2-52
Wiring Diagrams	2-54
P2-08TD1S Isolated Sinking DC Output	2-55
Wiring Diagrams	2-57
P2-08TD2S Isolated Sourcing DC Output	2-58
Wiring Diagrams	2-60
P2-15TD1 Sinking DC Output	2-61
Wiring Diagrams	2-63
P2-15TD2 Sourcing DC Output	2-64
Wiring Diagrams	2-66
P2-08TD1P Sinking Protected DC Output	2-67
Wiring Diagrams	2-69
P2-08TD2P Sourcing Protected DC Output	2-70
Wiring Diagrams	2-72
P2-16TD1P Sinking Protected DC Output	2-73
Wiring Diagrams	2-75
P2-16TD2P Sourcing Protected DC Output	2-76
Wiring Diagrams	2-78
P2-32TD1P Sinking Protected DC Output	2-79
Wiring Diagrams	2-81
P2-32TD2P Sourcing Protected DC Output	2-82
Wiring Diagrams	2-84
P2-08TAS Isolated AC Output	2-85
Wiring Diagrams	2-87
P2-16TA AC Output	2-88
Wiring Diagrams	2-90

P2-08TRS Isolated Relay Output	2-91
Wiring Diagrams	2-93
P2-16TR Relay Output	2-94
Wiring Diagrams	2-96

Chapter 3 - Analog I/O Specifications

Analog I/O Modules Overview.....	3-3
Analog I/O Modules	3-4
Analog Input Modules.....	3-4
Analog Output Modules.....	3-4
Analog Input/Output Modules	3-5
P2-04AD Analog Input.....	3-6
Wiring Diagrams	3-8
Module Configuration.....	3-10
OLED Panel Display	3-11
P2-08AD-1 Analog Input	3-12
Wiring Diagrams	3-14
Module Configuration.....	3-15
OLED Panel Display	3-16
P2-08AD-2 Voltage Analog Input.....	3-17
Wiring Diagrams	3-19
Module Configuration.....	3-20
OLED Panel Display	3-21
P2-08ADL-1 Current Analog Input.....	3-22
Wiring Diagrams	3-24
Module Configuration.....	3-25
P2-08ADL-2 Voltage Analog Input.....	3-26
Wiring Diagrams	3-28
Module Configuration.....	3-29
P2-16AD-1 Current Analog Input.....	3-30
Wiring Diagrams	3-32
Module Configuration.....	3-33
OLED Panel Display	3-34

P2-16AD-2 Voltage Analog Input.....	3-35
Wiring Diagrams	3-37
Module Configuration	3-38
OLED Panel Display	3-39
P2-16ADL-1 Current Analog Input.....	3-40
Wiring Diagrams	3-42
Module Configuration	3-43
P2-16ADL-2 Voltage Analog Input.....	3-44
Wiring Diagrams	3-46
Module Configuration	3-47
P2-06RTD Analog Input.....	3-48
Wiring Diagrams	3-51
Wiring Diagrams	3-52
Module Configuration	3-53
OLED Panel Display	3-54
P2-08THM Analog Input.....	3-55
Wiring Diagrams	3-58
Wiring Diagrams	3-59
Module Configuration	3-60
OLED Panel Display	3-61
P2-08NTC Thermistor	3-62
Wiring Diagrams	3-64
OLED Panel Display	3-65
P2-04DA Analog Output.....	3-66
Wiring Diagrams	3-68
Configuration Settings.....	3-70
OLED Panel Display	3-71
P2-04DAL-1 Analog Output.....	3-72
Wiring Diagrams	3-74
Configuration Settings.....	3-75
P2-04DAL-2 Analog Output.....	3-76
Wiring Diagrams	3-78
Configuration Settings.....	3-79

P2-08DA-1 Current Analog Output	3-80
Wiring Diagrams	3-82
Module Configuration.....	3-83
OLED Panel Display	3-84
P2-08DA-2 Voltage Analog Output	3-85
Wiring Diagrams	3-87
Module Configuration.....	3-88
OLED Panel Display	3-89
P2-08DAL-1 Current Analog Output	3-90
Wiring Diagrams	3-92
Module Configuration.....	3-93
P2-08DAL-2 Voltage Analog Output	3-94
Wiring Diagrams	3-96
Module Configuration.....	3-97
P2-16DA-1 Current Analog Output	3-98
Wiring Diagrams	3-100
Module Configuration.....	3-101
OLED Panel Display	3-102
P2-16DA-2 Voltage Analog Output	3-103
Wiring Diagrams	3-105
Module Configuration.....	3-106
LCD Panel Display	3-107
P2-16DAL-1 Current Analog Output	3-108
Wiring Diagrams	3-110
Module Configuration.....	3-111
P2-16DAL-2 Voltage Analog Output	3-112
Wiring Diagrams	3-114
Module Configuration.....	3-115
P2-8AD4DA-1 Current Analog Input/Output	3-116
Wiring Diagrams	3-119
Module Configuration.....	3-120
OLED Panel Display	3-121

P2-8AD4DA-2 Voltage Analog Input/Output	3-122
Wiring Diagrams	3-125
Module Configuration	3-126
OLED Panel Display	3-127

Chapter 4 - Specialty Module Specifications

P2-HSI High-Speed Input Module Overview	4-2
HSI LED Indicators	4-3
HSI Input Specifications	4-4
HSI Status Output Specifications	4-6
Frequency Response	4-6
HSI Wiring Examples	4-8
P2-HSO High-Speed Output Module Overview	4-11
HSI LED Indicators	4-12
HSI Output Specifications	4-13
HSO Wiring Examples	4-15
High-Speed Module Tester Utility	4-20
P2-SCM Module Overview	4-21
SCM LED Indicators	4-22
P2-SCM Module Communications	4-23
RS-232 Serial Ports	4-23
RS-232 Serial Port 1	4-24
RS-232 Serial Port 2 and 3	4-25
RS-485 Port 4	4-26

Chapter 5 - Installation and Wiring

Safety Guidelines	5-2
Plan for Safety	5-2
Three Levels of Protection	5-3
Orderly System Shutdown	5-3
System Power Disconnect	5-3
Emergency Stop Circuits	5-4
Introduction	5-5

Table of Contents

Productivity2000 Mechanical Design.....	5-5
Typical Productivity2000 System	5-5
Dimensions and Installation.....	5-6
Base Dimensions, inches [mm]	5-6
Mounting Guidelines.....	5-7
Enclosures	5-7
Mounting Position.....	5-7
Mounting Clearances	5-7
Grounding	5-7
Temperature Considerations.....	5-7
Power Considerations.....	5-7
Panel Layout.....	5-8
Other Specifications	5-9
Agency Approvals.....	5-9
Using Mounting Rails	5-10
Installing the Power Supply	5-11
Installing the CPU.....	5-12
Installing the I/O Modules.....	5-13
Wiring Guidelines	5-14
Wiring to the Power Supply	5-14
Grounding	5-14
Fuse Protection.....	5-15
I/O Module Wiring Options	5-16
ZIPLink Wiring System.....	5-16
Terminal Block With Pigtail Cable.....	5-16
Input and Output Modules ZIPLink Selections.....	5-17
Analog and Specialty Module ZIPLink Selections	5-18
Analog and Specialty Module ZIPLink Selections	5-19
Removable Terminal Blocks (Optional)	5-20
Terminal Block Removal	5-20
Planning the I/O Wiring Routes.....	5-21
System Wiring Strategies	5-22
CPU Isolation Boundaries	5-22
Sinking/Sourcing Concepts	5-23
I/O "Common Terminal" Concepts.....	5-24

DC Input Wiring Methods.....	5-25
DC Output Wiring Methods.....	5-25
Relay Outputs - Wiring Methods	5-27
Relay Outputs – Transient Suppression for Inductive Loads in a Control System.....	5-28

Chapter 6 - Communications

Communications	6-1
Communication Ports.....	6-1
Communications: Connectivity	6-8
P2-550 Port Connections	6-8
ASCII and Custom Protocol Functionality	6-13
ASCII Instructions	6-13
Custom Protocol Instructions	6-14
Communications: Ethernet	6-16
TCP and UDP Port Numbers	6-16
IP Addressing and Subnetting	6-16
PC Setup	6-17
CPU Setup.....	6-18
TCP Connection Behavior with Modbus TCP and Network Instructions	6-19
Communications Modbus Functionality	6-20
Master/Client Function Code and Data Type Support	6-20
Slave/Server Function Code and Data Type Support	6-22
Assigning Modbus Addresses to Tags	6-23
Modbus Options	6-26
Modbus Instructions.....	6-29
Network Instructions	6-31
Automatic Poll versus Manual Polling and Interlocking.....	6-32
Message Queue.....	6-34
EtherNet/IP for the Productivity Series	6-35
Terminology Definitions	6-35
Network Layer Chart	6-36
EtherNet/IP Data	6-36
Class 1 and Class 3 Connections	6-37
Setup Example: Productivity2000 as EtherNet/IP Adapter	6-37

Table of Contents

Setup Example: Productivity2000 as EtherNet/IP Scanner	6-40
Troubleshooting Tips:.....	6-43
EtherNet/IP I/O Message Troubleshooting:	6-45
EtherNet/IP Explicit Message Troubleshooting:.....	6-45
Communications: Remote I/O and GS-Drives	6-46
Things To Consider for the design of Remote I/O and GS-Drives	6-46
Configuration of Remote Slaves.....	6-47
Communications: Port Configuration	6-54
Ethernet Configuration	6-54
External Ethernet Port Settings	6-55
Local Ethernet Port Settings.....	6-56
Remote Access Configuration	6-56
Serial Configuration.....	6-57
RS-232 and RS-485 Port Settings.....	6-57
Communications: Error Codes	6-60
Productivity2000 Communication Error Codes.....	6-60
Productivity2000 EtherNet/IP Error Codes	6-61

Chapter 7 - Maintenance and Troubleshooting

Hardware Maintenance	7-2
Standard Maintenance	7-2
Air Quality Maintenance.....	7-2
CPU Battery Replacement.....	7-2
Diagnostics.....	7-3
Diagnostics.....	7-3
Critical Errors.....	7-3
Non-Critical Errors.....	7-3
Finding Diagnostic Information	7-3
Error Codes	7-3
CPU Indicators	7-4
PWR Indicator	7-5
Incorrect Base Power	7-5
Faulty CPU	7-5
Device or Module Causes the Power Supply to Shutdown	7-6

Run Indicator	7-7
CPU Indicator.....	7-7
Communications Problems	7-7
I/O Module Troubleshooting	7-8
Things to Check	7-8
Error Codes	7-8
Some Quick Steps	7-8
Testing Output Points	7-9
Noise Troubleshooting	7-10
Electrical Noise Problems.....	7-10
Reducing Electrical Noise.....	7-10
Run Time vs Stop Mode Transfer Instruction.....	7-11
Run Time Transfers.....	7-12
Stop Mode Transfers	7-12
Forcing I/O Points	7-14
Advantages of Forces.....	7-14
Enabling Forces	7-14
Forcing Tags in Your System	7-15
Identifying Forced Values	7-17
Force Value Timing Chart.....	7-18

Appendix A - European Union Directives (CE)

European Union (EU) Directives	A-2
Member Countries	A-2
Applicable Directives	A-2
Compliance.....	A-2
General Safety	A-3
Special Installation Manual	A-4
Other Sources of Information	A-4
Basic EMC Installation Guidelines	A-4
Enclosures	A-4
Mains Filters	A-5
Suppression and Fusing.....	A-5
Internal Enclosure Grounding	A-5

Table of Contents

Equipotential Grounding	A-5
Communications and Shielded Cables	A-6
Analog and RS232 Cables	A-7
Multidrop Cables.....	A-7
Shielded Cables Within Enclosures.....	A-7
Analog Modules and RF Interference	A-7
Network Isolation	A-8
Items Specific to the Productivity2000	A-9

Appendix B - Productivity2000 Error Codes

Communications Error Codes	B-2
Module Error Codes	B-3
CPU Error Codes	B-5
Project Error Codes.....	B-6
Project Error Messages	B-8